

NOT RECOMMENDED FOR NEW DESIGN **CONTACT US**



AP3983B/C/D

HIGH FREQUENCY PRIMARY SIDE POWER SWITCHER FOR OFF-LINE SMPS

Description

The DIODES™ AP3983B/C/D are series of high frequency power switcher for power supplies with better conversion efficiency, better voltage & current accuracy, and improved protection functions. Typical applications include charger, adapter for ADSL, home appliance power supply, LED lighting power supply and PC auxiliary power supplies. The AP3983B/C/D with built-in MOSFET, regulates the output voltage and current in the primary side by piece-wise Pulse Frequency Modulation (p-PFM) in discontinuous conduction mode (DCM). The system operating frequency reduces linearly from heavy load to light load in each interval of the p-PFM, and enters constant current mode when the load current equals to the maximum system output current.

The AP3983B/C/D has good transient characteristics. Typically, minimal voltage of 4.3V at PCB side can be achieved for dynamic test of 5V application system.

The AP3983B/C/D provides operating frequency dithering function to improve EMC performance of power supply. The AP3983B/C/D also has built-in fixed cable voltage drop compensation and adjustable line voltage compensation.

The AP3983B/C/D solution has fewer component number, smaller size, and lower total cost.

The AP3983B/C is packaged in SO-7. The AP3983C/D is packaged in

Features

- Primary Side Control for Eliminating Opto-Coupler
- Better Transient Characteristics
- Built-in N Channel MOSFET with 650 BVpss
- Low Start-up Current: 0.2µA (Typ.)
- Internal Output Cable Voltage Drop Compensation
- Hiccup Function to Improve Short Circuit Protection
- Better Over Voltage Protection
- Better Over Temperature Protection
- Low Total Cost Solution
- Output Power Range (Note 1):

AP3983B for 6W Adapter


AP3983C (SO-7) for 7.5W

AP3983C (PDIP-7) for 10W Adapter


AP3983D for 18W Adapter

- Totally Lead-Free & Fully RoHS Compliant (Notes 2 & 3)
- Halogen and Antimony Free. "Green" Device (Note 4)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Pin Assignments



SO-7 For AP3983B/C



PDIP-7 For AP3983C/D

Applications


- Adapters
- Set top boxes
- Auxiliary supplies
- **Appliances**
- LED drivers

Notes:

- 1. Typical continuous power in a non-ventilated enclosed adapter measured at +50°C ambient.
- 2. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 3. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and
- 4. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



Typical Applications Circuit



For AP3983B/C/D (12V/1.5A)


Item	Function	QTY	Item	Function	QTY
C1, C2	15μF/400V, electrolytic	2	U1	AP3983D, PDIP-7	1
C3	4.7μF/50V, electrolytic	1	R1, R2	2MΩ, 1206	2
C4	10nF, ceramic, 0805	1	R3	200Ω, 1206	1
C5	1nF/250V, ceramic	1	R4	150kΩ, 1206	1
C6	1nF/100V, 0805	1	R5	22kΩ, 1%, 0805	1
C7, C8	1000µF/16V, electrolytic	2	R6	47kΩ, 1%, 0805	1
C9	10pF/16V, 0805	1	R7	2Ω, 1206	1
CY1	1nF/250V _{AC} , Y1 capacitor	1	R8	30Ω, 1206	1
D1 to D6	1N4007, rectifier diode	6	R9	5.1kΩ,1206	1
D7, D8	MBR3100, Schottky diode	2	R12	1.2Ω, 1%, 1206	1
F1 •	2A/250V, fuse	1	R13	1.8Ω, 1%, 1206	1
L1	30mH, Common inductor, EE9.8	1	T1	EE20 core, PC40, transformer	1
L2	250µH/2A, Common inductor	1	_	_	_

Pin Descriptions

Pin Number	Pin Name	Function	
1	CPC	This pin connects a capacitor to GND for output cable compensation	
2	FB	voltage feedback from auxiliary winding	
3	VCC	This pin receives rectified voltage from the auxiliary winding of the transformer	
4	CS	Current sense for primary side of transformer	
5, 6	D	This pin is connected with an internal power MOSFET's drain	
7	GND	This pin is the signal reference ground	



Functional Block Diagram





Absolute Maximum Ratings (Note 5)

Symbol	Parameter Rating		Unit
Vcc	Supply Voltage	-0.3 to 30	٧
Vcs, Vcpc	Voltage on CS, CPC Pin	-0.3 to 7	V
V _{FB}	FB Input Voltage	-0.3 to 8	V
BV _{DSS}	Drain Voltage (T _J = +25°C)	700	V
lo	Drain Continuous Current (T _J = +25°C)	AP3983B 1 AP3983C 2 AP3983D 4	А
TJ	Operating Junction Temperature	-40 to +150	°C
T _{STG}	Storage Temperature	-65 to +150	°C
T _{LEAD}	Lead Temperature (Soldering, 10 sec)	+300	°C
_	ESD (Machine Model)	200	V
_	ESD (Human Body Model)	2000	V
P _D	Total Power Dissipation	AP3983B 0.7 AP3983C (SO-7) 0.85 AP3983C (PDIP-7) 1.0 AP3983D 1.8	W

Note 5: Stresses greater than those listed under "Absolute Maximum Ratings" can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "Recommended Operating Conditions" is not implied. Exposure to "Absolute Maximum Ratings" for extended periods can affect device reliability.

Recommended Operating Conditions

Symbol	Parameter	Min	Max	Unit
Vcc	Supply Voltage		25	V
T _{OP}	Operating Temperature Range	-40	+105	°C
f _{S(MAX)}	Maximum Operating Frequency		80	kHz

Thermal Impedance (Note 6)

Symbol	Parameter	Value		Unit
	Junction to Ambient	AP3983B	95	°C/W
0		AP3983C (SO-7)	85	
ALθ		AP3983C (PDIP-7)	70	
		AP3983D	40	
	Junction to Case	AP3983B	48	C/VV
0.0		AP3983C (SO-7)	43	
θις		AP3983C (PDIP-7)	35	
		AP3983D	20	

Note 6: When mounted a standard single-sided FR-4 board with $300 mm^2$ Cu (at least $35 \mu m$ thick) connected to all collectors and CS pins.



Electrical Characteristics (@V_{CC} = 15V, T_J = +25°C, unless otherwise specified.)

Symbol	Parameter	Condition	Min	Тур	Max	Unit		
STARTUP AND	STARTUP AND UVLO SECTION							
V _{TH_ST}	Turn-on Voltage	_	13	15.5	18	V		
Vopr(MIN)	Turn-off Voltage	_	6	6.8	7.6	V		
STANDBY CUR	RENT SECTION		•			•		
I _{ST}	Turn-on Current	Vcc = Vth_st-1V before startup	0	0.2	0.6	μA		
I _{CC_OPR}	Operating Current	Static current @ no load	350	500	650	μ		
OPERATING FR	REQUENCY SECTION (5% LOAD TO FULL	LOAD)			•			
f _{S(MAX)}	Operating Frequency in Full Load Condition	_		65	80	kHz		
Δf/f	Frequency Dithering	5% to 100% of full load range	4	7	10	%		
OPERATING F	REQUENCY SECTION (NO LOAD TO 5% O	F IOUT(MAX))						
fs(MIN)	Output Voltage Detection Frequency	-	1.8	2	2.2	kHz		
CURRENT SEN								
V _{CS_H}	Peak Current Sense Voltage in Heavy Load	30% to 100% of full load	828	900	972	mV		
ΔVcs/Vcs	Vcs Modulation for Frequency Dithering	- 4		2.5	_	%		
tMOD	Vcs Modulation Period	- \\\\	<i>></i>	250	_	μs		
R _{LINE}	Built-in Line Compensation Resistor	#11,	V -/	230	_	Ω		
.	Loading Edge Planking	@ V _{CS_H} and V _{CS_M}	410	500	575	ns		
tLEB	Leading Edge Blanking	@ Vcs_el	220	250	288	ns		
CONSTANT VO	LTAGE SECTION							
V _{FB}	Equivalent Feedback Voltage @ Light Load	Closed loop test of Vout	3.89	3.95	4.01	V		
R _{FB}	FB Pin Input Resistance	<i>F</i>	560	700	840	kΩ		
VCABLE/VOUT	Cable Compensation Ratio	(Vfb@fullload-Vfb)/Vfb	5.65	6.00	6.40	%		
CONSTANT CU	RRENT SECTION							
tons/tsw	Secondary Winding Conduction Duty	V _{FB} = 2V	_	4/8	_	_		
POWER MOSFE	ET SECTION							
BV _{DSS}	Drain-Source Breakdown Voltage	_	650	_	_	V		
		AP3983B	_	9	12			
Rds(ON)	On State Resistor	AP3983C	_	5	6	Ω		
		AP3983D	_	2.4	3			
PROTECTION F	UNCTION SECTION							
Vfb(OVP)	Over Voltage Protection	_	_	7.5	_	V		
VFB(SCP)	Short Circuit Protection	V _{FB} @ Hiccup	1.4	1.5	1.6	V		
Тотр	Shutdown Temperature	_	+125	+160	_	°C		
Thys	Temperature Hysteresis	_	_	+40	_	°C		



Operation Description




Figure 1. Simplified Flyback Converter Controlled by AP3983B/C/D

Constant Primary Peak Current

The primary ip(t) current is sensed by a current sense resistor Rcs as shown in Figure 1.

The current rises up linearly at a rate of:

$$\frac{di_{\rm p}(t)}{dt} = \frac{V_{\rm BULK}(t)}{L_{\rm u}} \dots (1)$$




Figure 2. Primary Current Waveform

As illustrated in Figure 2, when the current ip(t) rises up to IpK, the switch Q1 turns off. The constant peak current is given by:

$$I_{PK} = \frac{V_{CS}}{R_{CS}} \qquad (2)$$

The energy stored in the magnetizing inductance $L_{\mbox{\scriptsize M}}$ each cycle is therefore:

$$E_{\rm G} = \frac{1}{2} \cdot L_{\rm M} \cdot I_{\rm PK}^2 \cdot \dots (3)$$

So the power transferring from input to output is given by:

$$P = \frac{1}{2} \cdot L_M \cdot I_{PK}^2 \cdot f_{SW} \cdot \dots (4)$$

Where fsw is the switching frequency. When the peak current IPK is constant, the output power depends on the switching frequency fsw.

Constant Voltage Operation

The AP3983B/C/D captures the auxiliary winding feedback voltage at FB pin and operates in constant-voltage (CV) mode to regulate the output voltage. Assuming the secondary winding is master, the auxiliary winding is slave during the D1 on-time. The auxiliary voltage is given by:

$$V_{AUX} = \frac{N_{AUX}}{N_S} \cdot (V_0 + V_D)$$
....(5)



Operation Description (continued)

Where V_D is the diode forward drop voltage, N_{AUX} is the turns of auxiliary winding, and N_S is the turns of secondary winding.




Figure 3. Auxiliary Voltage Waveform

The output voltage is different from the secondary voltage in a diode forward drop voltage V_D which depends on the current. If the secondary voltage is always detected at a constant secondary current, the difference between the output voltage and the secondary voltage will be a fixed V_D. The voltage detection point is portion of to_{NS} after D1 is turned on. The CV loop control function of AP3983B/C/D then generates a D1 off-time to regulate the output voltage.

Constant Current Operation

The AP3983B/C/D is designed to work in constant current (CC) mode. Figure 4 shows the secondary current waveforms.




Figure 4. Secondary Current Waveform

In CC operation, the CC loop control function of AP3983B/C/D will keep a fixed proportion between D1 on-time tons and D1 off-time toffs by discharging or charging the built-in capacitance connected. This fixed proportion is

$$\frac{t_{ONS}}{t_{OFFS}} = \frac{4}{4} \dots (6)$$

The relation between the output constant-current and secondary peak current IPKS is given by:

$$I_{OUT} = \frac{1}{2} \cdot I_{PKS} \cdot \frac{t_{ONS}}{t_{ONS} + t_{OFFS}} \dots (7)$$

At the instant of D1 turn-on, the primary current transfers to the secondary at an amplitude of:

$$I_{PKS} = \frac{N_P}{N_S} \cdot I_{PK} \cdot \dots (8)$$

Thus the output constant current is given by:

$$I_{OUT} = \frac{1}{4} \cdot \frac{N_P}{N_S} \cdot I_{PK} \cdot \dots (9)$$



Operation Description (continued)

Leading Edge Blanking (LEB)

When the power switch is turned on, a turn-on spike on the output pulse rising edge will occur on the sense-resistor. To avoid false termination of the switching pulse, a typical 500ns leading edge blanking is built in. During this blanking period, the current sense comparator is disabled and the gate driver cannot be switched off.

The built-in LEB in AP3983B/C/D has shorter delay time from current sense terminal to output pulse than those IC solutions adopting external RC filter as LEB.

Built-in Cable Compensation

The AP3983B/C/D has built-in fixed voltage of 0.3V typical to compensate the drop of output cable when the load is changed from zero to full load. A typical 10nF external capacitor connected to the CPC pin is used to smooth voltage signal for cable compensation.


Over Temperature Protection

The AP3983B/C/D has internal thermal sensing circuit to shut down the PFM driver output when the die temperature reaches +160°C typical. When the die temperature drops about +40°C, the IC will recover automatically to normal operation.






Ordering Information



Part Number	Package	Tomporaturo Pango	Marking ID	Packing		
Fait Nullibel	Package Temperature Range		Marking ID	Qty.	Carrier	
AP3983BMTR-G1	SO-7		3983BM-G1	4000	Tape & Reel	
AP3983CMTR-G1	SO-7	40°C to +105°C	3983CM-G1	4000	Tape & Reel	
AP3983CP7-G1	PDIP-7	-40°C to +105°C	AP3983CP7-G1	50	Tube	
AP3983DP7-G1	PDIP-7		AP3983DP7-G1	50	Tube	


Marking Information





Package Outline Dimensions (All dimensions in mm (inch).)

(1) Package Type: SO-7




Note: Eject hole, oriented hole and mold mark is optional.



Package Outline Dimensions (continued) (All dimensions in mm (inch).)

(2) Package Type: PDIP-7




Note: Eject hole, oriented hole and mold mark is optional



Suggested Pad Layout

(1) Package Type: SO-7



Dimensions	Z G (mm)/(inch)	X (mm)/(inch)	Y (mm)/(inch)	E (mm)/(inch)	E1 (mm)/(inch)
Value	6.900/0.272 3.900/0.154	0.650/0.026	1.500/0.059	1.270/0.050	2.540/0.100

July 2022



IMPORTANT NOTICE

- DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their
- Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and
- Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- Diodes' 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-andconditions/important-notice

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com