

## RF 15 R - Low tactile switch, non-illuminated, gold contacts

## 3.14.100.501/0000



Recommended key grid	15.24 mm
Dimensions	
Length	15 mm
Width	15 mm
Overall height	9.7 mm
Mechanical design	
Mounting	soldering in PCB
Terminals	
Contact system	snap-action contact
Contact arrangement Contact materials	<u>1 NO</u>
	Au
Illumination	not illuminated
Mechanical characteristics	
Operating force max.	2.9 <sup>±0.6</sup> N
Switching travel	0.5 <sup>+0.2</sup> mm
Robustness max.	with through-plated PCB 100 N
Electrical characteristics	
Rated voltage min.	Au: 0.02 V, Ag: 3 V
Rated voltage max.	<u>35 V</u>
Rated current min.	Au: 0.01 mA, Ag: 0.1 mA
Rated current max.	Au: 100 mA, Ag: 250 mA
Rated power max. (ohmic load)	Au: 2 W, Ag: 12.5 W
Contact resistance when new max.	<u>100 mΩ</u>
Insulation resistance	<u>10<sup>9</sup> Ω</u>
Other specifications	
Ambient temp. operating min.	-25 °C
Ambient temp. operating max.	+70 °C
Environmental restistance	acc. to IEC 60068-2-14, -30, -33 and -78
Operating life min. (operations)	1,000,000 cycle
Solderability / solder heat resistance	according to DIN EN 60068-2-20
Wave soldering	260 °C max.
	350 °C / 5 sec. max.
Manual soldering ROHS compliant	<u>350 °C / 5 sec. max.</u> yes

Technical data are approximate and intended solely for general orientation in the selection of a product. Subject to modifications and errors. Images and other graphics may only be similar. For more information, refer to www.rafi.de chapter Imprint / Data Protection.





RF 15 R high, with 3 mm LED, green





