

SLUS125B-MAY 1999-REVISED JANUARY 2010

512 k × 8 NONVOLATILE SRAM (5 V, 3.3 V)

Check for Samples: bq4015/Y/LY

FEATURES

- Data Retention for at least 10 Years Without Power
- Automatic Write-Protection During Power-up/Power-Down Cycles
- Conventional SRAM Operation, Including Unlimited Write Cycles
- Internal Isolation of Battery before Power Application
- 5-V or 3.3-V Operation
- Industry Standard 32-Pin DIP Package

GENERAL DESCRIPTION

The CMOS bq4015/Y/LY is a nonvolatile 4,194,304-bit static RAM organized as 524,288 words by 8 bits. The integral control circuitry and lithium energy source provide reliable nonvolatility coupled with the unlimited write cycles of standard SRAM.

The control circuitry constantly monitors the single supply for an out-of-tolerance condition. When $V_{\rm CC}$ falls out of tolerance, the SRAM is unconditionally write-protected to prevent an inadvertent write operation.


At this time the integral energy source is switched on to sustain the memory until after V_{CC} returns valid.

The bq4015/Y/LY uses extremely low standby current CMOS SRAMs, coupled with small lithium coin cells to provide nonvolatility without long write-cycle times and the write-cycle limitations associated with EEPROM.

The bq4015/Y/LY requires no external circuitry and is compatible with the industry-standard 4-Mb SRAM pinout.

PIN CONNECTIONS

32-Pin DIP Module (TOP VIEW)





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



www.ti.com

DEVICE INFORMATION

Table 1. TERMINAL FUNCTIONS

Т	ERMINAL	I/O	DESCRIPTION
NAME	NUMBER	1/0	DESCRIPTION
A ₀	12	I	
A ₁	11	I	
A ₂	10	1	
A ₃	9	1	
A ₄	8	1	
A ₅	7	1	
A ₆	6	1	
A ₇	5	1	
A ₈	27	1	
A ₉	26	1	Address inputs
A ₁₀	23	1	
A ₁₁	25	1	
A ₁₂	4	1	
A ₁₃	28	1	
A ₁₄	3	1	
A ₁₅	31	1	
A ₁₆	2	1	
A ₁₇	30	1	
A ₁₈	1	I	
CE	22	1	Chip-enable input
DQ ₀	13	I/O	
DQ ₁	14	I/O	
DQ ₂	15	I/O	
DQ_3	17	I/O	Data input/output
DQ ₄	18	I/O	Δαία πηράνουιραι
DQ ₅	19	I/O	
DQ ₆	20	I/O	
DQ ₇	21	I/O	
ŌĒ	24	I	Output enable input
V _{CC}	32	I	Supply voltage input
V _{SS}	16	-	Ground
WE	29	I	Write enable input

FUNCTIONAL DESCRIPTION

When power is valid, the bq4015/Y/LY operates as a standard CMOS SRAM. During power-down and power-up cycles, the bq4015/Y/LY acts as a nonvolatile memory, automatically protecting and preserving the memory contents.

Power-down/power-up control circuitry constantly monitors the V_{CC} supply for a power-fail-detect threshold V_{PFD} . The bq4015 monitors for $V_{PFD} = 4.62$ V typical for use in 5-V systems with 5% supply tolerance. The bq4015Y monitors for $V_{PFD} = 4.37$ V typical for use in 5-V systems with 10% supply tolerance. The bq4015LY monitors for $V_{PFD} = 2.90$ V (typ) for use in 3.3-V systems.

Submit Documentation Feedback

Copyright © 1999–2010, Texas Instruments Incorporated



SLUS125B-MAY 1999-REVISED JANUARY 2010

When V_{CC} falls below the V_{PFD} threshold, the SRAM automatically write-protects the data. All outputs become high impedance, and all inputs are treated as *don't care*. If a valid access is in process at the time of power-fail detection, the memory cycle continues to completion. If the memory cycle fails to terminate within time t_{WPT} , write-protection takes place.

As V_{CC} falls past V_{PFD} and approaches V_{SO} , the control circuitry switches to the internal lithium backup supply, which provides data retention until valid V_{CC} is applied.

When V_{CC} returns to a level above the internal backup cell voltage, the supply is switched back to V_{CC} . After V_{CC} ramps above the V_{PFD} threshold, write-protection continues for a time t_{CER} (120 ms maximumin 5-V system, 85 ms maximum in 3.3-V system) to allow for processor stabilization. Normal memory operation may resume after this time.

The internal coin cells used by the bq4015/Y/LY have an extremely long shelf life and provide data retention for more than 10 years in the absence of system power.

As shipped from TI, the integral lithium cells of the MT-type module are electrically isolated from the memory. (Self-discharge in this condition is approximately 0.5% per year.) Following the first application of V_{CC} , this isolation is broken, and the lithium backup provides data retention on subsequent power-downs.

BLOCK DIAGRAM




Table 2. TRUTH TABLE

MODE	CE	WE	ΘE	I/O OPERATION	POWER
Not selected	Н	X	Х	High-Z	Standby
Output disable	┙	Н	Н	High-Z	Active
Read	L	Н	L	D _{OUT}	Active
Write	L	L	X	D _{IN}	Active



www.ti.com

ORDERING INFORMATION

For the most current package and ordering information, see the Package Option Addendum at the end of the datasheet, or see the TI website at www.ti.com.

Table 3. SELECTION GUIDE

DEVICE NUMBER	MAXIMUM ACCESS TIME (ns)	NEGATIVE SUPPLY TOLERANCE (%)	NOMINAL INPUT VOLTAGE V _{CC} (V)	TEMPERATURE (°C)
bq4015MA-70	70			
bq4015MA-85	85	-5		40 45 05
bq4015YMA-70	70			-40 to 85
bq4015YMA-85	85	-10		
bq4015LYMA-70N	70		3.3	

Table 4. PART NUMBERING

PRODUCT LINE	MEMORY DENSITY	INPUT VOLTAGE (V)	NEGATIVE SUPPLY TOLERANCE	PACKAGE	SPEED (ns)	TEMPERATURE (°C)
bq40	15	L	Y	MA	70	
	$10 = 8 k \times 8$	Blank = 5	Blank = 5%	MA = DIP	70	-40 to 85
	11 = 32 k × 8	L= 3.3	Y = 10%		85	
	13 = 128 k × 8				100	
	14 = 256 k × 8				120	
	15 = 512 k × 8				150	
	16 = 1024 k × 8				200	
	17 = 2048 k × 8					

Submit Documentation Feedback

Copyright © 1999–2010, Texas Instruments Incorporated



SLUS125B-MAY 1999-REVISED JANUARY 2010

ABSOLUTE MAXIMUM RATINGS(1)

	PARAMETER	CONDITION		VALUE	UNIT
			bq4015Y	-0.3 to 7.0	
V _{CC}	DC voltage applied on VCC relative to VS	SS	bq4015	-0.3 to 7.0	V
			bq4015LY	-0.3 to 6.0	
			bq4015Y	-0.3 to 7.0	
V_{T}	DC voltage applied on any pin excluding VCC relative to VSS	V _{VT} ≤ V _{VCC} +0.3 V	bq4015	-0.3 to 7.0	V
	voo relative to voo	bq4015LY		-0.3 to (V _{CC} + 0.3)	
T _{OPR}	Operating temperature			-40 to 85	
T _{STG}	Storage temperature			-40 to 85	°C
T _{BIAS}	Temperature under bias			-40 to 85	
T _{SOLDER}	Soldering temperature	For 10 seconds		260	

⁽¹⁾ Permanent device damage may occur if **Absolute Maximum Ratings** are exceeded. Functional operation should be limited to the Recommended DC Operating Conditions detailed in this data sheet. Exposure to conditions beyond the operational limits for extended periods of time may affect device reliability.

RECOMMENDED OPERATING CONDITIONS $(T_A = T_{OPR})$

			MIN	TYP ⁽¹⁾	MAX	UNIT
		bq4015Y	4.50	5.00	5.50	
V_{CC}	Supply voltage	bq4015	4.75	5.00	5.50	
		bq4015LY	3.00	3.30	3.60	V
V_{SS}	Supply voltage		0	0	0	V
V_{IL}	Low-level input voltage		-0.3		0.8	
V_{IH}	High-level Input voltage		2.2		$V_{CC} + 0.3$	

⁽¹⁾ Typical values indicate operation at $T_A = 25$ °C.

DC ELECTRICAL CHARACTERISTICS

 $T_A = T_{OPR}, V_{CC(min)} \le V_{CC} \le V_{CC(max)}$

	PARAMETER		TEST CONDITIONS	MIN	TYP ⁽¹⁾	MAX	UNIT
ILI	Input leakage current		V _{IN} = V _{SS} to V _{CC}			±1	
I _{LO}	Output leakage current		$\overline{CE} = V_{IH} \text{ or } \overline{OE} = V_{IH} \text{ or } \overline{WE} = V_{IL}$			±1	μA
V_{OH}	Output high voltage		I _{OH} = -1.0 mA	2.4			V
V_{OL}	Output low voltage		I _{OL} = 2.1 mA			0.4	V
I _{SB1}	Standby supply current		CE = V _{IH}		1	2	μΑ
I _{SB2}	Standby supply current		$\overline{CE} \ge V_{CC} - 0.2 \text{ V}, \text{ 0V} \le V_{IN} \le 0.2 \text{ V},$ or $V_{IN} \ge V_{CC} - 0.2$		0.1	1	mA
		bq4015				50	
I _{CC}	Operating supply current	bq4015Y	Minimum cycle, duty = 100%, $\overline{CE} = V_{IL}$, $I_{I/O} = 0$ mA			50	mA
		bq4015LY	0E = V _E , 1/0 = 0 111A			50	
		bq4015		4.55	4.62	4.75	
V_{PFD}	Power-fail-detect voltage	bq4015Y		4.30	4.37	4.50	
		bq4015LY		2.85	2.90	2.95	.,
		bq4015			3		V
V_{SO}	Supply switch-over voltage	bq4015Y			3		
		bq4015LY			2.9		

⁽¹⁾ Typical values indicate operation at T_A = 25°C, V_{CC} = 5.0 V or V_{CC} = 3.3 V.



www.ti.com


CAPACITANCE ($T_A = 25$ °C, f = 1 MHz, $V_{CC} = 5.0$ V or $V_{CC} = 3.3$ V)

	PARAMETER ⁽¹⁾	TEST CONDITIONS	MIN	TYP	MAX	UNIT
C _{I/O}	Input/output capacitance	Output voltage = 0 V			8	~F
C _{IN}	Input capacitance	Input voltage = 0 V			10	ρг

⁽¹⁾ Ensured by design. Not production tested.

AC TEST CONDITIONS

DADAMETED	TEST CON	DITIONS
PARAMETER	5 V	3.3 V
Input pulse levels	0 V to 3.0 V	0 V to V _{CC}
Input rise and fall times	5 ns	5 ns
Input and output timing reference levels	1.5 V (unless otherwise specified)	50 %
Output load (including scope and jig)	See Figure 1 and Figure 2	See Figure 3 and Figure 4



 D_{OUT} O $1.9 \text{ k}\Omega$ 5 pF

Figure 1. 5-V Output Load A

+3.3 V $1.2 \text{ k}\Omega$ $1.4 \text{ k}\Omega$ 30 pF

Figure 2. 5-V Output Load B





Figure 3. 3.3-V Output Load A

Figure 4. 3.3-V Output Load B

SLUS125B-MAY 1999-REVISED JANUARY 2010


Table 5. READ CYCLE ($T_A = T_{OPR}, V_{CC(min)} \le V_{CC} \le V_{CC(max)}$)

	PARAMETER	TEST CONDITIONS	-70)	-85		UNIT
	PARAMETER	TEST CONDITIONS	MIN	MAX	MIN	MAX	UNIT
t _{RC}	Read cycle time		70		85		
t _{AA}	Address access time			70		85	
t _{ACE}	Chip enable access time	Output load A		70		85	
t _{OE}	Output enable to output valid			35		45	
t _{CLZ}	Chip enable to output in low Z		5		5		ns
t _{OLZ}	Output enable to output in low Z	Outside In a d D	0		0		
t _{CHZ}	Chip disable to output in high Z	Output load B	0	25	0	35	
t _{OHZ}	Output disable to output in high Z	7	0	25	0	25	
t _{OH}	Output hold from address change	Output load A	10		10		



- (1) $\overline{\text{WE}}$ is held high for a read cycle.
- (2) Device is continuously selected: $\overline{CE} = \overline{OE} = V_{IL}$.

Figure 5. Read Cycle No. 1 (Address Access)




- (1) WE is held high for a read cycle.
- (2) Device is continuously selected: $\overline{CE} = \overline{OE} = V_{IL}$.
- (3) Address is valid prior to or coincident with $\overline{\text{CE}}$ transition low.

Figure 6. Read Cycle No. 2 (CE Access)

INSTRUMENTS

www.ti.com



- (1) WE is held high for a read cycle.
- (2) Device is continuously selected: $\overline{CE} = V_{IL}$.


Figure 7. Read Cycle No. 3 (OE Access)

SLUS125B-MAY 1999-REVISED JANUARY 2010

Table 6. WRITE CYCLE ($T_A = T_{OPR}, V_{CC(min)} \le V_{CC} \le V_{CC(max)}$)

	DARAMETER	TEST SOURITIONS	-70	0	-85	5	
	PARAMETER	TEST CONDITIONS	MIN	MAX	MIN	MAX	UNIT
t _{WC}	Write cycle time		70		85		
t _{CW}	Chip enable to end of write	See (1)	65		75		
t_{AW}	Address valid to end of write	See (1)	65		75		
t _{AS}	Address setup time	Measured from address valid to beginning of write. (2)	0		0		
t _{WP}	Write pulse width	Measured from beginning of write to end of write.	55		65		
t _{WR1}	Write recovery time (write cycle 1)	Measured from WE going high to end of write cycle. (3)	5		5		
t _{WR2}	Write recovery time (write cycle 2)	Measured from $\overline{\text{CE}}$ going high to end of write cycle. (3)	15		15		ns
t _{DW}	Data valid to end of write	Measured to first low-to- high transition of either $\overline{\text{CE}}$ or $\overline{\text{WE}}$.	30		35		
t _{DH1}	Data hold time (write cycle 1)	Measured from WE going high to end of write cycle. (4)	0		0		
t _{DH2}	Data hold time (write cycle 2)	Measured from $\overline{\text{CE}}$ going high to end of write cycle. (4)	10		10		
t_{WZ}	Write enbled to output in high Z	I/O pins are in output state. (5)	0	25	0	30	
t _{OW}	Output active from end of write	I/O pins are in output state. (5)	5		0		

- A write ends at the earlier transition of $\overline{\text{CE}}$ going high and $\overline{\text{WE}}$ going high. A write occurs during the overlap of a low $\overline{\text{CE}}$ and a low $\overline{\text{WE}}$. A write begins at the later transition of $\overline{\text{CE}}$ going low and $\overline{\text{WE}}$ going low. (2)
- Either t_{WR1} or t_{WR2} must be met.
- Either t_{DH1} or t_{DH2} must be met.
- If $\overline{\text{CE}}$ goes low simultaneously with $\overline{\text{WE}}$ going low or after $\overline{\text{WE}}$ going low, the outputs remain in high-impedance state.




- (1) $\overline{\text{CE}}$ or $\overline{\text{WE}}$ must be high during address transition.
- (2) Because I/O may be active (OE low) during this period, data input signals of opposite polarity to the outputs must not be applied.
- (3) If \overline{OE} is high, the I/O pins remain in a state of high impedance.

Figure 8. Write Cycle No. 1 (WE-Controlled)



www.ti.com



- (1) $\overline{\text{CE}}$ or $\overline{\text{WE}}$ must be high during address transition.
- (2) Because I/O may be active (OE low) during this period, data input signals of opposite polarity to the outputs must not be applied.
- (3) If \overline{OE} is high, the I/O pins remain in a state of high impedance.
- (4) Either t_{WR1} or t_{WR2} must be met.
- (5) Either t_{DH1} or t_{DH2} must be met.

Figure 9. Write Cycle No. 2 (CE-Controlled)

Submit Documentation Feedback



SLUS125B-MAY 1999-REVISED JANUARY 2010

Table 7. 5-V POWER-DOWN/POWER-UP ($T_A = T_{OPR}$)

	PARAMETER	TEST CONDITIONS	MIN	TYP ⁽¹⁾	MAX	UNIT
t_{PF}	V _{CC} slew, 4.75 to 4.25 V		300			μs
t_{FS}	V _{CC} slew, 4.25 to V _{SO}		10			μs
t _{PU}	V _{CC} slew, V _{SO} to V _{PFD (max.)}		0			μs
t _{CER}	Chip enable recovery time	Time during which SRAM is write-protected after V_{CC} passes V_{PFD} on power-up.	40	80	120	ms
t _{DR}	Data-retention time in absence of V _{CC}	$T_A = 25^{\circ}C^{(2)}$	10			years
t _{WPT}	Write-protect time	Delay after V _{CC} slews down past V _{PFD} before SRAM is writeprotected.	40	100	150	μs

- Typical values indicate operation at T_A = 25°C, V_{CC} = 5V. Batteries are disconnected from circuit until after V_{CC} is applied for the first time. t_{DR} is the accumulated time in absence of power beginning when power is first applied to the device.




Figure 10. 5-V Power-Down/Power-Up Timing

www.ti.com

Table 8. 3.3-V POWER-DOWN/POWER-UP ($T_A = T_{OPR}$)

	PARAMETER	TEST CONDITIONS	MIN	TYP ⁽¹⁾	MAX	UNIT
t _F	V _{CC} slew, 3 V to 0 V		300			
t_R	V _{CC} slew, V _{SO} to V _{PFD (max)}		100			μs
t _{CER}	Chip enable recovery time	Time during which SRAM is write-protected after V_{CC} passes V_{PFD} on power-up.	10		85	ms
t _{DR}	Data-retention time in absence of V _{CC}	$T_A = 25^{\circ}C^{(2)}$	10			years

- Typical values indicate operation at T_A = 25°C, V_{CC} = 3.3 V. Batteries are disconnected from circuit until after V_{CC} is applied for the first time. Data retention time (t_{DR}) is the accumulated time in absence of power beginning when power is first applied to the device.




Figure 11. 3.3-V Power-Down/Power-Up Timing

Negative undershoots below the absolute maximum rating of -0.3 V in battery-backup mode may affect data integrity.

Submit Documentation Feedback



PACKAGE OPTION ADDENDUM

31-Mar-2014

PACKAGING INFORMATION

www.ti.com

Orderable Device	Status	Package Type	Package	Pins	Package	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
BQ4015LYMA-70	LIFEBUY	DIP MODULE	MA	32		TBD	Call TI	Call TI			
BQ4015LYMA-70N	OBSOLETI	E DIP MODULE	MA	32		TBD	Call TI	Call TI	-40 to 85		
BQ4015MA-70	OBSOLETI	E DIP MODULE	MA	32		TBD	Call TI	Call TI	0 to 70		
BQ4015YMA-70	OBSOLETI	E DIP MODULE	MA	32		TBD	Call TI	Call TI	0 to 70		
BQ4015YMA-70N	OBSOLETI	E DIP MODULE	MA	32		TBD	Call TI	Call TI	-40 to 85		
BQ4015YMA-85	OBSOLETI	E DIP MODULE	MA	32		TBD	Call TI	Call TI	0 to 70		

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.



PACKAGE OPTION ADDENDUM

31-Mar-2014

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive Communications and Telecom Amplifiers amplifier.ti.com www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps

DSP **Energy and Lighting** dsp.ti.com www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical logic.ti.com Logic Security www.ti.com/security

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

RFID www.ti-rfid.com

OMAP Applications Processors www.ti.com/omap TI E2E Community e2e.ti.com/omap

Wireless Connectivity <u>www.ti.com/wirelessconnectivity</u>