
## chainflex® CF2



Control cable (Class 6.5.3.1) ● For extremely heavy duty applications ● PUR outer jacket

- Shielded Oil-resistant and coolant-resistant Flame retardant Notch-resistant
- Hydrolysis and microbe-resistant



- 1. Outer jacket: Pressure extruded PUR mixture
- 2. Overall shield: Extremely bending-resistant braiding made of tinned copper wires
- 3. Inner jacket: Pressure extruded, gusset-filling PVC
- 4. Core insulation: Mechanically high-quality TPE mixture
- 5. Conductor: Stranded conductor in especially bendresistant version consisting of bare copper wires
- Strain relief: Tensile stress-resistant centre element
- 7. 12 cores or more: Bundles with optimised pitch length and pitch direction












































Example image


For detailed overview please see design table

### Cable structure



Conductor







Inner jacket



Overall shield



Outer jacket

PVC mixture adapted to suit the requirements in e-chains®.

Extremely bending-resistant braiding made of tinned copper wires. Coverage linear approx. 70 %, optical approx. 90 %

Number of cores < 12: Cores wound in a layer with short pitch length.

Low-adhesion, halogen-free, highly abrasion resistant PUR mixture, adapted to suit the requirements in e-chains® (following DIN EN 50363-10-2)

+++ chainflex cable works +++

Stranded conductor in especially bending-resistant version consisting of bare copper

Number of cores ≥ 12: Cores wound in bundles which are then wound around a high tensile strength centre element, all with optimised short pitch lengths and directions.

Colour: Anthracite grey (similar to RAL 7016) Printing: white

RoHS-II conform

Colour code in accordance with DIN 47100.

wires (following DIN EN 60228).

Especially low-torsion structure.

Mechanically high-quality TPE mixture.

"00000 m"\*\* igus chainflex CF2.-.-Ф ---Ф 300/500V E310776 сЯ Uus

AWM Style 20317 VW-1 AWM I/II A/B 80°C 300V FT-1 EAC/CTP CE UKCA

\* Length printing: Not calibrated. Only intended as an orientation aid. ① / ② Cable identification according to Part No. (see technical table).

Example: ... chainflex CF2.01.04 (4x0.14)C 300/500 V ...

www.igus.de

# chainflex® CF2



Control cable (Class 6.5.3.1) ● For extremely heavy duty applications ● PUR outer jacket

- Shielded Oil-resistant and coolant-resistant Flame retardant Notch-resistant
- Hydrolysis and microbe-resistant

## Dynamic information



Temperature e-chain® linear -20 °C up to +80 °C flexible -40 °C up to +80 °C

flexible -40 °C up to +80 °C (following DIN EN 60811-504) fixed -50 °C up to +80 °C (following DIN EN 50305)

v max. unsupported 10 m/s gliding 5 m/s

**a max.** 80 m/s<sup>2</sup>

Travel distance Unsupported travels and up to 100 m for gliding applications, Class 5

These values are based on specific applications or tests. They do not represent the limit of what is technically feasible.

## Guaranteed service life according to guarantee conditions

| Double strokes               | 5 million           | 7.5 million         | 10 million          |
|------------------------------|---------------------|---------------------|---------------------|
| Temperature,<br>from/to [°C] | R min. [factor x d] | R min. [factor x d] | R min. [factor x d] |
| -20/-10                      | 6.8                 | 7.5                 | 8.5                 |
| -10/+70                      | 5                   | 6.8                 | 7.5                 |
| +70/+80                      | 6.8                 | 7.5                 | 8.5                 |

Minimum guaranteed service life of the cable under the specified conditions. The installation of the cable is recommended within the middle temperature range.

### **Electrical information**

Nominal voltage 300/500 V (following DIN VDE 0298-3) 300 V (following UL)

**Testing voltage** 2000 V (following DIN EN 50395)































# chainflex® CF2



Control cable (Class 6.5.3.1) ● For extremely heavy duty applications ● PUR outer jacket

- Shielded Oil-resistant and coolant-resistant Flame retardant Notch-resistant
- Hydrolysis and microbe-resistant

## Properties and approvals



UV resistance High



Oil resistance Oil-resistant (following DIN EN 50363-10-2), Class 3



Offshore MUD-resistant following NEK 606 - status 2009



Flame retardant According to IEC 60332-1-2, Cable Flame, VW-1, FT1, FT2 / Horizontal Flame



Silicone-free Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)



**UL verified**Certificate No. B129699: "igus 36-month chainflex cable guarantee and service life





UL/CSA AWM Details see table UL AWM



NFPA Following NFPA 79-2018, chapter 12.9



EAC Certificate No. RU C-DE.ME77.B.00300/19



REACH In accordance with regulation (EC) No. 1907/2006 (REACH)



Lead-free Following 2011/65/EC (RoHS-II/RoHS-III)



Cleanroom According to ISO Class 1. The outer jacket material of this series complies with CF77.

UL.05.12.D - tested by IPA according to standard DIN EN ISO 14644-1



Following 2014/35/EU



In accordance with the valid regulations of the United Kingdom (as at 08/2021)



**UL/CSA AWM Details** 

| Conductor nominal<br>cross section<br>[mm²] | Number of cores | UL style core insultation | UL style outer<br>jacket | UL Voltage<br>Rating<br>[V] | UL Temperature<br>Rating<br>[°C] |
|---|-----------------|---------------------------|--------------------------|-----------------------------|----------------------------------|
| 0.14  | 4-36            | 10493                     | 20317                    | 300                         | 80                               |
| 0.25  | 4-48            | 10493                     | 20317                    | 300                         | 80                               |





























# chainflex® CF2



Control cable (Class 6.5.3.1) ● For extremely heavy duty applications ● PUR outer jacket


- Shielded Oil-resistant and coolant-resistant Flame retardant Notch-resistant
- Hydrolysis and microbe-resistant

## Typical lab test setup for this cable series

Test bend radius R approx. 28 - 75 mm
Test travel S/S, approx. 1 - 15 m

**Test duration** minimum 2 - 4 million double strokes

Test speed approx. 0.5 - 2 m/sTest acceleration approx.  $0.5 - 1.5 \text{ m/s}^2$ 



# Guarantee (gus chainflex) 36 (sta 56 months guarantee)



























## Typical application areas

- For heaviest duty applications, Class 6
- Unsupported travels and up to 100 m for gliding applications, Class 5
- Almost unlimited resistance to oil, Class 3
- No torsion, Class 1
- Indoor and outdoor applications
- Storage and retrieval units for high-bay warehouses, machining units/packaging machines, quick handling, indoor cranes, refrigerating sector

# chainflex® CF2




Control cable (Class 6.5.3.1) ● For extremely heavy duty applications ● PUR outer jacket

- Shielded Oil-resistant and coolant-resistant Flame retardant Notch-resistant
- Hydrolysis and microbe-resistant

### Technical tables:

### Mechanical information

| Part No.     | Number of cores and conductor nominal cross section [mm²] | Outer diameter (d) max. [mm] | Copper<br>index<br>[kg/km] | Weight<br>[kg/km] |
|--------------|---|------------------------------|----------------------------|-------------------|
| CF2.01.04    | (4x0.14)C   | 6.5                          | 18                         | 49                |
| CF2.01.08    | (8x0.14)C   | 7.5                          | 31                         | 66                |
| CF2.01.12    | (12x0.14)C  | 9.5                          | 51                         | 102               |
| CF2.01.18    | (18x0.14)C  | 10.5                         | 56                         | 135               |
| CF2.01.24 3) | (24x0.14)C  | 11.5                         | 68                         | 162               |
| CF2.01.36    | (36x0.14)C  | 14.5                         | 92                         | 240               |
| CF2.02.04    | (4x0.25)C   | 7.0                          | 25                         | 59                |
| CF2.02.08    | (8x0.25)C   | 8.0                          | 43                         | 84                |
| CF2.02.18    | (18x0.25)C  | 12.0                         | 100                        | 173               |
| CF2.02.24 3) | (24x0.25)C  | 13.5                         | 124                        | 305               |
| CF2.02.48    | (48x0.25)C  | 17.5                         | 191                        | 387               |



Note: The given outer diameters are maximum values and may tend toward lower tolerance limits. G = with green-yellow earth core x = without earth core



### **Electrical information**

| Conductor nominal cross section | Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2) | •   |
|---------------------------------|--|-----|
| [mm²]                           | [Ω/km]   | [A] |
| 0.14                            | 138  | 2.5 |
| 0.25                            | 79   | 4   |

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.





























# chainflex® CF2



Control cable (Class 6.5.3.1) ● For extremely heavy duty applications ● PUR outer jacket ● Shielded ● Oil-resistant and coolant-resistant ● Flame retardant ● Notch-resistant

- Hydrolysis and microbe-resistant

| Design tab | Number of | Core design | Part No.  | Number of | Core design   |
|------------|-----------|-------------|-----------|-----------|---|
| rait No.   | cores     | Core design | rait No.  | cores     | Core design   |
| CF2.XX.04  | 4         |             | CF2.XX.24 | 6x4       | 22 23<br>23 23<br>24 23<br>25 23<br>26 23<br>27 23<br>28 23<br>26 25<br>26 25<br>26 25<br>26 25<br>26 25<br>26 25<br>26 25<br>26 25<br>26 25<br>26 26<br>26 26 26<br>26 26 26<br>26 26 26<br>26 26<br>26<br>26 26<br>26 26<br>26 26<br>26<br>26 26<br>26<br>26<br>26<br>26<br>26<br>26<br>26<br>26<br>26<br>26<br>26<br>26<br>2 |
| CF2.XX.08  | 8         |             | CF2.XX.36 | 6x6       |   |
| CF2.XX.12  | 4x3       | 30.30       | CF2.XX.48 | 8x6       |   |
| CF2.XX.18  | 6x3       | 30000       |           |           |   |
| CF2.XX.18  | 6x3       | 4           |           |           |   |

# chainflex® CF2



Control cable (Class 6.5.3.1) ● For extremely heavy duty applications ● PUR outer jacket

- Shielded Oil-resistant and coolant-resistant Flame retardant Notch-resistant
- Hydrolysis and microbe-resistant

### Colour code in accordance with DIN 47100

| Colour code in accordance with Di |                                    |  |  |  |
|-----------------------------------|------------------------------------|--|--|--|
| Conductor no.                     | Colours according to DIN ISO 47100 |  |  |  |
| 1                                 | white                              |  |  |  |
| 2                                 | brown                              |  |  |  |
| 3                                 | green                              |  |  |  |
| 4                                 | yellow                             |  |  |  |
| 5                                 | grey                               |  |  |  |
| 6                                 | pink                               |  |  |  |
| 7                                 | blue                               |  |  |  |
| 8                                 | red                                |  |  |  |
| 9                                 | black                              |  |  |  |
| 10                                | violet                             |  |  |  |
| 11                                | grey-pink                          |  |  |  |
| 12                                | red-blue                           |  |  |  |
| 13                                | white-green                        |  |  |  |
| 14                                | brown-green                        |  |  |  |
| 15                                | white-yellow                       |  |  |  |
| 16                                | yellow-brown                       |  |  |  |
| 17                                | white-grey                         |  |  |  |
| 18                                | grey-brown                         |  |  |  |
|                                   |                                    |  |  |  |

| Conductor no. | Colours according to DIN ISO 47100 |
|---------------|------------------------------------|
| 19            | white-pink                         |
| 20            | pink-brown                         |
| 21            | white-blue                         |
| 22            | brown-blue                         |
| 23            | white-red                          |
| 24            | brown-red                          |
| 25            | white-black                        |
| 26            | brown-black                        |
| 27            | grey-green                         |
| 28            | yellow-grey                        |
| 29            | pink-green                         |
| 30            | yellow-pink                        |
| 31            | green-blue                         |
| 32            | yellow-blue                        |
| 33            | green-red                          |
| 34            | yellow-red                         |
| 35            | green-black                        |
| 36            | yellow-black                       |
|               |                                    |



























