

Specification Date: Feb 27, 2018 Version: 01

COMAIR ROTRON PART NUMBER: COMAIR ROTRON MODEL NUMBER:

## A.) MOTOR:

RATED VOLTAGE:

**OPERATING VOLTAGE RANGE:** 

LOW-START VOLTAGE:

RATED CURRENT:

**OPERATING FREGUENCY:** 

INPUT POWER:

RATTED SPEED:

MOTOR TYPE:

MOTOR PROTECTION: LOCKED ROTORT PROTECTION:

POLARITY PROTECTION:

AUTOMATIC RESTART CAPABILITY:

ROTATION:

## **B.) MECHANICAL**

DIMENSIONS:

WEIGHT:

BEARING TYPE:

VENTURI:

PROPELLER:

17000657A CREC2258-3600E1B

115VAC±10% 103~126VAC 87VAC 1.13 Amps 50~60Hz 88 Watts 3600 RPM ±5% (At Free Delivery) Brushless EC By Integrated Circuit IC protected Yes By Integrated Circuit Counter Clockwise when viewed from the impeller 225mm x225mm x 80mm 1800g **Ball Bearings** Die Cast magnesium alloy, ED coating and powder coating Die Cast magnesium alloy,

ED coating and powder coating



Specification Date: Feb 27, 2018 Version: 01




Figure 1

## C.) ENVIRONMENTAL

OPERATING TEMPERATURE:

STORAGE TEMPERATURE:

-20°C to +70°C

The storage temperature will be suggested at  $-20^{\circ}$ C ~  $50^{\circ}$ C to ensure a better performance.

20 to 85% RH, non-condensing

HUMIDITY:



Specification Date: Feb 27, 2018 Version: 01

# **D.) PERFORMANCE CHARACTERISTICS**

AIR FLOW:


STATIC PRESSURE:

#### ACOUSTIC LEVEL:

685 CFM ± 5% (Measuring at zero static pressure)

1.29" Inches of H20 (Measuring at zero airflow)

71 dBA Max. at MAX. speed (Measured via Freely Suspended at 1 meter)





Specification Date: Feb 27, 2018 Version: 01

# **E.) TERMINATION**

Terminal connection:

Suit with terminal block

Blue	= Neutral wire
Brown	= Live wire
Yellow/Green	= Ground wire

# F.) RELIABILITY

Bearing type	Temperature	Hours
Ball bearing	20°C	60,000
	40°C	50,000
	60°℃	40,000
	90°C	20,000

# G.) SAFETY

UL, CUL, CE

# H.) FLAMMABILITY

The fan including all components meets a UL94V-0 rating or better.