
SPECIFICATIONS

 Model Number:
 MT24B3
 Version:02

 Part Number:
 19031843A
 Feb 26, 2021



Mechanical Drawing:



Motor:

Nominal Voltage = 24 VdcOperating Voltage Range = 12 - 28 VdcNominal Running Current = 1.70 AmpsMax. Locked Rotor Current = 3.00 Amps**Running Power** =40.8 Watts Average Speed = 3400 RPM**Bearings** = BallAir Flow = 298 CFMAcoustic = 57.1 dBA

Construction:

Venturi: Single piece diecast aluminum, black. Propeller: Injection molded of flame retardant polycarbonate, UL94V-0 rated, black.

Life Expectancy:

This fan is designed for continuous duty life of 76,000 hours at 40°C.

Additional Features:

Brushless DC Motor

Electronic Locked Rotor Protection

Reverse Polarity Protection

Automatic Restart Capability

Operating Temperature Range: -10°C to 70°C Storage Temperature Range: -40°C to 85°C

Termination:

12.0" Lead wires, 22AWG, UL 1061 Style

Red = Power(+)

Black = Return(-)

Agency Approvals:

UL, CUL, CE

PQ Curve:

