




■ Features :

- AC input range selected by switch
- Built-in passive PFC function compliance to BS EN/EN61000-3-2
- With AC ON-OFF switch
- 3 poles AC inlet with fuse holder
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Charger type can be selected (Optional)
- Charger for lead-acid batteries
- · 2 color LED loading indicator
- Open frame models available (Without safety approval)
- · Low cost, High reliability
- 2 years warranty










SPECIFICATION

MODEL		PA/PB-120□-13□	PA/PB-120 -27	PA/PB-12054		
	DC VOLTAGE	13.8V	27.6V	55.2V		
OUTPUT	RATED CURRENT	7.2A	4.3A	2.2A		
	CURRENT RANGE	0 ~ 7.2A	0 ~ 4.3A	0 ~ 2.2A		
DUTPUT	RATED POWER	99.36W	118.68W	121.44W		
	LED INDICATED	PA series voltage 105%±1% ↓: RED / 105%±1% ↑: GREEN				
	LED INDICATED	PB series load 46%±10% ↓: GREEN / 46%±10% ↑:RED				
	VOLTAGE RANGE	88 ~ 132VAC / 176 ~ 264VAC select	88 ~ 132VAC / 176 ~ 264VAC selected by switch 248 ~ 370VDC			
	FREQUENCY RANGE	47 ~ 63Hz				
	POWER FACTOR (Typ.)	>0.65 (with PFC series)				
NPUT	EFFICIENCY (Typ.)	73%	79%	79%		
	AC CURRENT (Typ.)	3A/115VAC 1.5A/230VAC				
	INRUSH CURRENT (Typ.)	COLD START 25A/115VAC 50A/230VAC				
	LEAKAGE CURRENT	<1.5mA/240VAC				
		90 ~ 110% rated output power				
	OVERLOAD	Protection type: Constant current limiting, recovers automatically after fault condition is removed				
		15 ~ 17V	30 ~ 35V	60 ~ 66V		
PROTECTION	OVER VOLTAGE	Protection type: Hiccup mode, recovers automatically after fault condition is removed				
	OVER TEMPERATURE	RTH2≧70°C ±10°C detect on RTH2 thermistor				
	OVER TEMPERATURE	Protection type: Shut down o/p voltage, recovers automatically after temperature goes down				
	WORKING TEMP.	-10 ~ +45°C (Refer to "Derating Curve")				
	WORKING HUMIDITY	20 ~ 90% RH non-condensing				
ENVIRONMENT	STORAGE TEMP., HUMIDITY	-20 ~ +85°C, 10 ~ 95% RH				
	TEMP. COEFFICIENT	±0.05%/°C (0~45°C)				
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes				
	SAFETY STANDARDS	UL60950-1, LVD BS EN/EN62368-1, EAC TP TC 004 approved				
SAFETY &	WITHSTAND VOLTAGE	I/P-O/P:3KVAC I/P-FG:2.0KVAC O/P-FG:0.5KVAC				
EMC	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH				
(Note 4)	EMC EMISSION	Compliance to BS EN/EN55032 (CISPR32) Class B, BS EN/EN61000-3-2,-3, EAC TP TC 020				
	EMC IMMUNITY	Compliance to BS EN/EN61000-4-2,3,4,5,6,8,11, BS EN/EN55024, light industry level, criteria A, EAC TP TC 020				
	MTBF	149.6K hrs min. MIL-HDBK-217F (25°C)				
OTHERS	DIMENSION	PCB Type:144*90*33mm External case type:180*96*49mm (L*W*H)				
	PACKING	External case type: 1.1Kg; 16pcs / 17.9Kg / 1.56CUFT(without PFC) 1.24Kg; 16pcs / 20.1Kg / 1.56CUFT(with PFC)				
		PCB Type : 0.36Kg; 36pcs	/ 14Kg / 0.99CUFT(without PFC)	0.5Kg; 36pcs / 19Kg / 0.99CUFT(with PFC)		

- 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor.
- 3. Tolerance : includes set up tolerance, line regulation and load regulation.
- 4. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives.
- 5. With PFC I/P range: 95~132VAC/190~264VAC.
- 6. For open P.C.B. WITH 17.8CFM min. Forced air.
- 7. The ambient temperature derating of 3.5° C/1000m with fanless models and of 5° C/1000m with fan models for operating altitude higher than 2000m(6500ft). ** Product Liability Disclaimer: For detailed information, please refer to https://www.meanwell.com/serviceDisclaimer.aspx





Case No. PS-120A Unit:mm

3 pin XLR

0 0



CASE:

Pin No. Assignment DC OUTPUT +V 2.3 DC OUTPUT -V	cm±5c	
Pin No.	Assignment	
1	DC OUTPUT +V	
2,3	DC OUTPUT -V	

PCB:

AC Input Connector (CN1): JST B3P-VH or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1	AC/L	JST VHR or equivalent	JST SVH-21T-P1.1 or equivalent
2	No Pin		
3	AC/N		

DC Output Connector (CN3): JST B4P-VH or equivalent


Pin No.	Assignment	Mating Housing	Terminal
1,2	-V	JST VHR	JST SVH-21T-P1.1
3,4	+V	or equivalent	or equivalent


12VDC FAN Output Connector (CN4): JST B2B-XH or equivalent

		` '	
Pin No.	Assignment	Mating Housing	Terminal
1	+V	JST XHP	JST SXH-001T-P0.6
2	-V	or equivalent	or equivalent

115/230V selected by switch Connector (CN5): JST B2P-VH or equivalent


Switch	Assignment	Mating Housing	Terminal
115V	Short		JST SVH-21T-P1.1
230V	Open	or equivalent	or equivalent






■ Charging Curve

■ Derating Curve





Red

Type B:Current detecter,2 voltage section

Green