
# HCMOS/TTL COMPATIBLE, J LEADED, PLASTIC MOLDED SMD CRYSTAL CLOCK OSCILLATOR

**ASM SERIES** 

Pb in high temperature solder (exempt per RoHS 2002/95/EC Annex (7)).

RoHS **Compliant** 



The 14x9.8mm plastic package oscillator is not recommended for new designs. Please consider our reduced size ceramic or plastic molded SMD packages. Recommended series include ASL, ASV, ASVM, ASFL, ASFLM, ASE, ASEM. For 5.0V please use ASL series. Product Life Cycle: Declining, Planned EOL/Obsolescence pending 12/31/2011

#### **FEATURES:**

- Industry standard J-Leaded terminals.
- HCMOS and TTL compatible
- Plastic molded SMD
- Tristate Enable/ Disable.
- Extended temperature -40°C to 85°C option Suitable for RoHS compliant reflow


#### > APPLICATIONS:

• Wide range of applications in dialing communication equipment, AV / OA equipment, Measuring equipment.

### **STANDARD SPECIFICATIONS:**

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range:		1.0		125.0	MHz	
Operating Temperature:		0		+70	°C	See options
Storage Temperature:		-55		+125	°C	
Overall Frequency Stability:		-100		+100	ppm	See options
Supply Voltage (Vdd):		4.5	5.0	5.5	V	
Supply Current (I <sub>dd</sub> ):				20	mA	F ≤ 20 MHz
				40		F≤70 MHz
				80		F ≤ 125 MHz
Output Load				50	рF	
				10	TTL	
Output Voltage:	$ m V_{OH}$	0.9*Vdd			V	
	$ m V_{OL}$			0.1*Vdd	V	
Tri-state function:		"1" (VIH≥ 2.2V) or Open: Oscillation "0" (VIL<0.8V): Hi Z				
Aging:		-5.0		+5.0	ppm	@+25°C First year
Symmetry:		40		60	%	@1/2Vdd CMOS(See options)
Start-up Time :				10	ms	
Rise/Fall Time (Tr/Tf):				10	ns	
Period jitter one sigma:				25	ps	

### **OPTIONS & PART IDENTIFICATION:**







# HCMOS/ TTL COMPATIBLE, J LEADED, PLASTIC MOLDED SMD CRYSTAL CLOCK OSCILLATOR

**ASM SERIES** 


Pb in high temperature solder (exempt per RoHS 2002/95/EC Annex (7)).


RoHS Compliant



14.0 x 8.95 x 4.7 mm

#### **OUTLINE DRAWING:**






4 Vdd


Note: Recommend using an approximately 0.01uF bypass capacitor between pin 2 and 4.

#### **PACKAGING:**

Dimension: Inch (mm)



## **REFLOW PROFILE:**



**ATTENTION:** Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.



