

# Metal Composite Power Inductor (Thin Film) **Specification Sheet**



# CIGT201206EH1R0MNE (2012 / EIA 0805)


Smart phones, Tablet, Wearable devices, Power converter modules, etc.

Small power inductor for mobile devices

Low DCR structure and high efficiency inductor for power circuits. Monolithic structure for high reliability Free of all RoHS-regulated substances Halogen free







	Unit : mm
TYPE	2012
А	0.8
В	0.8
С	1.3

TYPE	Dimension [mm]							
TIFE	L W		Т	D				
2012	2.0±0.2	1.25±0.2	0.6 max	0.5±0.2				

Part no.	Size	Thickness	Inductance tolerance	DC Resistance [mΩ]		Rated DC Current (Isat) [A]		Rated DC Current (Irms) [A]		
	[inch/mm] [mm] (max)	[uH]	(%)	Max.	Тур.	Max.	Тур.	Max.	Тур.	
CIGT201206EH1R0MNE	0805/2012	0.6	1.0	±20	110	90	2.4	2.7	1.8	2

\* Inductance : Measured with a LCR meter 4991A(Agilent) or equivalent (Test Freq. 1MHz, Level 0.1V)

\* DC Resistance : Measured with a Resistance HI-TESTER 3541(HIOKI) or equivalent

\* Maximum allowable DC current : Value defined when DC current flows and the initial value of inductance has decreased by 30% or

when current flows and temperature has risen to 40 °C whichever is smaller. (Reference: ambient temperature is 25 °C±10) (Isat) : Allowable current in DC saturation : The DC saturation allowable current value is specified when the decrease of

the initial inductance value at 30% (Reference: ambient temperature is 25 °C±10)

(Irms) : Allowable current of temperature rise : The temperature rise allowable current value is specified when temperature of the inductor is raised 40 °C by DC current. (Reference: ambient temperature is 25 °C±10)

\* Absolute maximum voltage : Absolute maximum voltage DC 20V.


\* Operating temperature range : -40 to +125°C (Including self-temperature rise)

<u>CIG</u>	I	<u>2012</u>	<u>06</u>	<u>EH</u>	<u>1R0</u>	M	<u>N</u>	<u>E</u>
		(3)						

<sup>(1)</sup> Power Inductor

- (3) Dimensior (2012: 2.0mm × 1.25mm )
- (5) Remark (Characterization Code)
- (7) Toleranc (M:±20%)
- (8) Internal Code
- (9) Packaging (C:paper tape, E:embossed tape)

RECOMMENDED SOLDERING CONDITION



## PACKAGING

Packaging Style	Quantity(pcs/reel)
Embossed Taping	3000 pcs

(T: Metal Composite Thin Film Type) (2) Type (4) Thicknes (06: 0.6mm)

(6) Inductan((1R0: 1.0 uH)

Item	Specified Value	Test Condition				
Solderability	More than 90% of terminal electrode should be soldered newly.	After being dipped in flux for $4\pm 1$ seconds, and preheated at $150 \sim 180^{\circ}$ for $2 \sim 3$ min, the specimen shall be immersed in solder at $245\pm 5^{\circ}$ for $4\pm 1$ seconds.				
Resistance to Soldering	No mechanical damage. Remaining terminal Electrode: 75% min. Inductance change to be within ±20% to the initial.	After being dipped in flux for $4\pm1$ seconds, and preheated at $150 \sim 180$ °C for $2 \sim 3$ min, the specimen shall be immersed in solder at $260\pm5$ °C for $10\pm0.5$ seconds.				
Thermal Shock (Temperature Cycle test)	No mechanical damage Inductance change to be within ±20% to the initial.	Repeat 100 cycles under the following conditions. -40±3 ℃ for 30 min → 85±3 ℃ for 30 min				
High Temp. Humidity Resistance Test	No mechanical damage Inductance change to be within ±20% to the initial	85±2°C, 85%RH, for 500±12 hours. Measure the test items after leaving at normal temperature and humidity for 24 hours.				
Low Temperature Test	No mechanical damage Inductance change to be within ±20% to the initial.	Solder the sample on PCB. Exposure at -55 $\pm 2^{\circ}$ for 500 $\pm 12$ hours. Measure the test items after leaving at normal temperature and humidity for 24hours.				
High Temperature Test	No mechanical damage Inductance change to be within ±20% to the initial.	Solder the sample on PCB. Exposure at 125±2°C for 500±12 hours. Measure the test items after leaving at normal temperature and humidity for 24hours.				
High Temp. Humidity Resistance Loading Test	No mechanical damage Inductance change to be within ±20% to the initial	$85\pm2$ °C, 85%RH, Rated Current for 500±12 hours. Measure the test items after leaving at normal temperature and humidity for 24 hours.				
High Temperature Loading Test	No mechanical damage Inductance change to be within ±20% to the initial	85±2°C, Rated Current for 500±12 hours. Measure the test items after leaving at normal temperature and humidity for 24 hours.				
Reflow Test	No mechanical damage Inductance change to be within ±20% to the initial	Peak 260±5℃, 3 times				
Vibration Test	No mechanical damage Inductance change to be within ±20% to the initial.	Solder the sample on PCB. Vibrate as apply 10~55Hz, 1.5mm amplitude for 2 hours in each of three(X,Y,Z) axis (total 6 hours).				
	No mechanical damage	Bending Limit; 2mm Test Speed; 1.0mm/sec. Keep the test board at the limit point in 5 sec. PCB thickness : 1.6mm				
Bending Test		20 Unit :mm R340 +2 45				
	No indication of peeling shall occur on the terminal electrode.	W(kgf) TIME(sec)				
		0.5 10±1				
Terminal Adhesion Test		77772 ★ ₩ 77772				
Drop Test	No mechanical damage Inductance change to be within ±20% to the initial.	Random Free Fall test on concrete plate. I. 1 meter, 10 drops				
lpeak (AC+DC Load Life)	No mechanical damage Inductance change to be within ±20% to the initial	85±2°C, 85%RH, Load(Ipeak) for 120 hours. (Frequncy:1MHz, Load(Ipeak):1.5hr on / 0.5hr off) Measure the test items after leaving at normal temperature and humidity for 24 hours. * Load(Ipeak) = Irms(max)×1.4				



**Data Sheet** 



# 1. Model : CIGT201206EH1R0MNE

## 2. Description

Part no.	Size	Thickness	Inductance	tance Inductance tolerance	DC Resistance [mΩ]		Rated DC Current (Isat) [A]		Rated DC Current (Irms) [A]	
	[inch/mm] [mm] (max)	[uH]	(%)	Max.	Тур.	Max.	Тур.	Max.	Тур.	
CIGT201206EH1R0MNE	0805/2012	0.6	1.0	±20	110	90	2.4	2.7	1.8	2

\* Inductance : Measured with a LCR meter 4991A(Agilent) or equivalent (Test Freq. 1MHz, Level 0.1V)

\* DC Resistance : Measured with a Resistance HI-TESTER 3541(HIOKI) or equivalent

\* Maximum allowable DC current : Value defined when DC current flows and the initial value of inductance has decreased by 30% or

when current flows and temperature has risen to 40°C whichever is smaller. (Reference: ambient temperature is 25°C±10) (Isat) : Allowable current in DC saturation : The DC saturation allowable current value is specified when the decrease of

the initial inductance value at 30% (Reference: ambient temperature is 25°C±10)

(Irms) : Allowable current of temperature rise : The temperature rise allowable current value is specified when temperature of


the inductor is raised 40  $^\circ$  by DC current. (Reference: ambient temperature is 25  $^\circ$ ±10)

\* Absolute maximum voltage : Absolute maximum voltage DC 20V.


\* Operating temperature range : -40 to +125°C (Including self-temperature rise)

### 3. Characteristics data


1) Frequency characteristics (Ls) Agilent E4294A +E4991A , 1MHz to 1,000MHz








4)Temperature characteristics (Typ.)



3) DC Bias characteristics (Typ.)



Any data in this sheet are subject to change, modify or discontinue without notice The data sheets include the typical data for design reference only. If there is any question regarding the data sheets, please contact our sales personnel or application engineers