Alkaline Zinc-Manganese Dry Battery Technology Specification

Customer			_
Part name	Alkaline	Zinc-Manganese Dry	Battery
Model No	6LR61	9V	- -
Serial No			_
Produce No			

Approved by	Drafted by	Wenfei liang
Checked by	Signed by	Xiaojun nie
Prepared by	Valid Date	2018-08-15

Company address: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China

(Tel): +86-755-86670672 (Fax): +86-755-86670609

E-mail: pkcell@pkcell.com
Website: http://www.pkcell.com

1 Scope

This specification defines the technical requirements for 9V 6LR61Alkaline cells distributed by Pkcell. If not otherwise specified, the technical requirements and dimensions for cells should meet or exceed the requirements of GB/T 8897.1-2008, GB 8897.2-2008

2 Reference documents

GB8897.1-2008(IEC60086-1:2000, IDT) Primary batteries-Part 1:General GB8897.2-2008(IEC60086-2:2001, MOD) Primary batteries-Part 2:Physical and technological specifications


GB8897.5-2006(IEC 60086-5:2005, MOD) Primary batteries-Part 5:Safety of batteries with aqueous electrolyte

3 Chemical systems, voltages and designation

- 3.1 Chemical systems: Alkaline manganese battery Zinc-Manganese dioxide
- 3.2 Nominal voltage:9V
- 3.3 Designation

IEC&GB(China): 6LR61;

4 LR61 Battery Dimensions



The batteries	6LR61		
Measure No	Max	Min ₋₂₋	
Н1	48.5	46.5	
Н2	46.4	45	
L	26.5	24.5	
W	17.5	15.5	
D	12.95	12.45	

5 Voltage and Short current

Item	OCV (V)	CCV (V)	SCC (A)
Initial	9. 2≤0CV≤9. 8	≥8.5	≥3.0
After 12 months	≥9.2	≥8.0	≥2.7

OCV measurment:The inner resistance of Voltage Metre is above $1M\Omega$

C.C.V. measurment: After 0.2 \pm 0.01sec by R=180 Ω

SCC measurment: $\pm 0.5\%$

6 6LR61 discharge performance

Discharge conditions			Averge Minimun Discharge time	
Load	Daily period	E. P. (V)	Initial	Delayed discharge performance after 12 months
180 Ω	24h/d	5. 4	12Н	11H
620 Ω	2h/day	5. 4	43h	40h
270 Ω	1h/day	5. 4	19. 5h	18h

- 3 -

Initial:60 days after pruduction

Test condition: $20^{\circ}\text{C} \pm 2^{\circ}\text{C}$ and $60 \pm 15\%\text{RH}$

7 Leakage Resistance

<i>i</i> Leakage Re	esistance			
Item	Test conditions	Sample size	Requirements	Acceptanc e
Overdischarge	60Ω 24h/d for 48h at 20 °C ± 2 °C,	n=9pcs	No leakage;Max of 0.35 mm height increase	Ac=0, Re=1

High Temperature and humidity storage	exposed to a temperature of 60℃± 2℃ and RH90±5% for a period of 3 weeks.	n=20pcs	No leakage	Ac=0, Re=1
45℃ Dry Storage	Stored for 12 weeks at 45℃	n=20pcs	No leakage	Ac=0, Re=1

8 Safety Requirement

Item	Test conditions	Sample size	Requirements of IEC60086-5:2005& GB8897.5-2006	Acceptanc -e ⁴ -
Partial Use	Stored at 45°C±2°C for 30days after undischarged batteries were test discharged 180Ω 24h/d, EPV=6.0V.	n=5pcs	No leakage;No explosion	Ac=0, Re=1
Thermal shock	See the following note 1, Total 10 Cycles	n=5pcs	No explosion	Ac=0, Re=1
Incorrect installation(3 + 1 anti- charge test)	Place three undischarged and unconditioned batteries in a series with one	n=5pcs	No explosion	Ac=0, Re=1

SHENZHEN PKCELL BATTERY CO.,LTD

ADD: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China. 518110

	1			
	test sample battery reversed, Complete the circuit until vent activation or until the temperature of the reversed battery returns to ambient.			
Item	Test conditions	Sample size	Requirements of IEC60086-5:2005& GB8897.5-2006	Acceptanc e
Free fall	Drop each undischarged battery Two times, oriented in each of three mutually perpendicular face (six total) from a height 1 meter, onto a concrete surface, see the following note 2	n=5pcs	No explosion	Ac=0; Re=1





SHENZHEN PKCELL BATTERY CO.,LTD

- 6 -


ADD: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China. 518110

Overdischarge	Discharge one test sample battery(C1) with 258Ω resistance load until EPV is 3.6V, Connect three undischarged batteries and the sample battery in series with a 45Ω resistance load(R1)as shown in note 3, Maintain the circuit until the CCV of the	n=5pcs	No explosion	Ac=0, Re=1





Note 2 : Free fall



9 Inspection rules

10.1 Deliver inspection: Depending on GB2828

- 6 - If manufacturer want to modify the product technology specification, we won't inform you additionally)



Number	Test	Item	IL	AQL
1	Dimensions	5	S-2	0. 4
2	Appearance		II	1. 0
3	Discharge capacity	7		
4	Open-circuit voltage	4.5	II	1. 0

Routine inspection: Depending on GB2829 and QB/T2389

10 Inspection for service output:

- 10.1 9 samples shall be tested for service output
- 10.2 If the average value is equal to or more than the value of table 1, and if the number of batteries showing a value less than 80% of the value of table 1 is 1 or less. The batteries are considered to conform to the requirement.
- 10.3 If the average value is less than the value of table 1, or if the number of batteries
- showing a value less than 80% is 2 or more, the test shall be repeated with other 9 pieces. At the second test, if the average value is equal to or more than the value of table 1, and if the number of batteries showing a value less than 80% of the value of table 1 is 1 or less, these batteries are considered to conform to the requirement.
- 10.4 At above second test, if the average value is less than the value of table 1, or if the number of batteries showing a value less than 80% of the value of table 1 is 2 or more, the batteries are considered not to conform to the requirement. third test shall not be performed.

11 Instructions for use

- 11.1 Always select correct size and grade of battery most suitable fot intended use.
- 11.2 Replace all batteries of a set at the same time
- 11.3 Clean the battery contacts and also those of the equipment prior to battery installation

- 11.4 Ensure that batteries are installed correctly with regard polarity(+ and -);
- 11.5 Remove batteries from equipment which is not be used for an extend period of time;
- 11.6 Remove exhausted batteries promptly..

12. Disply and storage

- 12.1 Batteries shall be stored in well-ventilateddry and cool conditions
- 12.2 Battery cartons should not be piledup in severa layers, or should not exceed a specified height;
- 12.3 Batteries should not be exposed to direct sun ray for a long time or placed in areas where they get wet by rain.;

- 8 -

12.4 Do not mix unpacked batteries so as to avoid mechanical damage and/or short circuit among each other


13 Storage life

Storage life of batteries are ten years long at $20\,^{\circ}\!\!\mathrm{C} \pm 2\,^{\circ}\!\!\mathrm{C}$ and RH $60\pm15\%$

14 Marks

- 15.1 Designation;
- 15.2 Polarity of terminals;
- 15.3 Nominal voltage;
- 15.4 Mercury content;
- 15.5 Name or trade mark, manufacturer or supplier;
- 15.6 Cautionary advice

Schematic diagram of discharge:



discharge Load: 180 Ω (24h/D)

.....END......