# **193A True-RMS Auto Ranging** Automotive DMM

#### LCD Display

40000 count with 42 segment bar graph.

# **REC (Record Mode)**

Store minimum, maximum, and average readings over a measurement period.

# RANGE

Manually select the appropriate range

# AC/DC

Manually select AC or DC measurement functin.

#### FUNCTION

Toggle between functions on Ohm, TEMP, and IG modes

# Hz (Frequency)

Measure the frequency of sensors and signals.

# $\Omega$ (Ohms, Resistance)

Measure the resistance of spark plug wires, coils, sensors, and continuity of wiring.

# ACmV and DCmV Ranges

Additional 40 millivolt DC range with 0.01mV resolution for improved accuracy when performing low voltage measurements.

# DCV, ACV (DC Volts, AC Volts)

Measure the voltage of circuits and sensors. Measure the voltage of ABS wheel sensors.

#### **REL (Relative Mode)**

Factor out lead resistance for improved low ohm measurements or compare readings to a known standard. Can also be used for differential measurements.

#### CYL (Cylinder)

Selects the number of cylinders in IG mode.

#### HOLD

Lock the reading on the display for hard to read locations or future reference.

# PEAK-H (Peak Hold)

Capture signals spikes as fast as 1mS to diagnose intermittant events.

#### **TEMP** (Temperature)

Measure temperature with included temperature probe.

#### **AC/DC Current Functions**

Measure the parasitic draw from the battery.

# **True-RMS Auto Ranging Automotive DMM**



# **⊣**€ (Capacitance)

Measure the capacitance of condensors or capacitors found in today's hybrid automobiles.

# **IP, IG (Automotive Functions)**

Measure RPM, Duty, Dwell, mS pulse width, Frequency.

#### **Built in Tilt Stand**

The tilt stand in built into the instrument housing adding strength and integrity to the design.

#### **Quickly Test Condition of Internal Fuses**

You can determine the status of the internal fuses before you open the battery/fuse compartment. Simply set the instrument to the diode test function, plug the black test lead into the "V $\Omega$ " input jack and touch the prod end of the black lead to the metal inside the "A" or "UAmA" input lack. If the meter reads "OL, the fuse is blown. If there is a reading on the LCD besides "OL", the fuse is good.

#### Separate Fuse/Battery Compartment

Easily replace fuses and batteries in this separate compartment. Fuses are clearly labeled with replacement part number.

> CULUS LISTED UL61010-1

CAT II-1000V, CAT III-600V POLLUTION DEGREE 2


Safety! cULus 61010-1 Listed Meets CE and IEC61010-1 safety standards.

# **193a** True-RMS Auto Ranging Automotive DMM

# www.testproductsintl.com

Function	Range	Resolution	Accuracy	Impedance
DC Volts	40mV	0.001V		
	400mV	0.01mV		10M ohm
	4V	0.0001V	±(0.1% + 5 digits)	
	40V	0.001V		
	400V	0.01V		
	1000V	1V		
AC Volts	400mV	0.01mV		
(45Hz to 2KHz)	4V	0.0001V		10M ohm
	40V	0.001V	±(0.75% + 40 digit)	
	400V	0.01V		
	750V	1V		
Function	Range	Resolution	Accuracy	Overload Protection
DC Amps	400uA	0.01uA		
	4000uA	0.1uA		
	40mA	0.001mA	±(0.3% + 10 digits)	Fuse*(fast blow)
	400mA	0.01mA		F600V, .5A, 31CM
	4A	0.0001A	±(0.75% + 10 digits)	Fuse*(fast blow)
	10A	0.001A		F600V, 10A, 31CM
AC Amps	400uA	0.01uA		
	4000uA	0.1uA	±(0.75% + 10 digits)	
	40mA	0.001mA		Fuse*(fast blow)
	400mA	0.01mA		F600V, .5A, 31CM
	4A	0.0001A	±(1.5% + 10 digits)	Fuse*(fast blow)
	10A	0.001A		F600V, 10A, 31CM
онм	400	0.01		600V DC or AC Peak
	4k	0.0001k	]	
	40k	0.001k	±(0.1% + 5 digits)	
	400k	0.01k		
	4M	0.0001M	1	
	40M	0.001M	±(0.75% + 15 digits)	
Capacitance	40nF	0.01nF		
	400nF	0.1nF	1	
	4uF	0.001uF	±(3.0% + 10 digits)	
	40µF	0.01µF	_(	600V DC or Peak AC
	400µF	0.1µF	1	
	4mF	0.001mF	1	
	10mF	0.01mF	±(5.0% + 10 digits)	
Frequency	40Hz	0.001Hz		
ricquency	400Hz	0.01Hz	1	
	4kHz	0.0001kHz	±(0.05% + 2 digits)	
	40kHz	0.001kHz		600V DC or Peak AC
	400kHz	0.01kHz	1	
	4MHz	0.00001MHz	1	
	10MHz	0.001MHz	1	
Temperature	-40° to 2,462°F	1°F	±(3°F +1 digit) (-4° to 572°F) ±39	6 of reading rest of range
	-40° to 1,350°C	1°C	$\pm$ (1.5°C +1 digit) (-20 to 300°C) $\pm$ 39	
Diode Test	3V Test Voltage		A Max Test Current	600 V DC or Peak AC
Continuity	3V Test Voltage	< 70  ohms		600 V DC or Peak AC
IG				
RPM	60 to 12,000	1 RPM	±2 RPM	
Duty Cycle	0.0 to 99.9%	0.1%	±2% per kHz, +0.1% (pulse wid	1th >0.5mS)
Dwell	0.0 to 356.4°	0.1%	pulse width $> 0.5$ mS	
DWell	(30 to 19999 RPM)	0.1		
Pulse Width	0.2 to 199.9mS	0.1mS	±2% per kHz, ±0.1% ±1 digit (p	uleo width>2ue
		0.1115	±2 /0 per km2, ±0.1% ±1 digit ()	uise wiutii>2µ5)
Frequency	(30 to 19999 RPM)	0.14-7	10.05% of reading . 0 digits	
riequency	1Hz to 1999.9Hz	0.1Hz	±0.05% of reading, ±2 digits	
IP				
RPM	60 to 12 0000 DM			
	60 to 12,000RPM	1 RPM	±2 RPM	

General Specifications			
Max. Volt. between any Input and Ground	1000V		
Fuse Protection mA: A:	,		
	40,000 Count, 4x per second update 2x41 segments, 20x per sec. update		
Operating Temp.	-0° to 45°C (32° to 113°F)		
Storage Temp.	-40° to 60°C (-40° to 140°F)		
Relative Humidity			
0% to 80%:	(0° - 35°C/32° - 95°F)		
0% to 70%:	(35° - 55°C/95° - 131°F)		
Temp. Coefficient	0.1 x (Specified Accuracy) per °C		
	for temperature <18°C to >28°C		
Power Supply	9 Volt Battery		
Battery Life	100 hrs. Alkaline		
Size (H x W x L)	61mm x 97mm x 203mm (2.4in x 3.8in x 8.0in)		
Weight	680g (24oz)		



Test the TPI Advantage: Value, Performance, Service, Safety