

# Dialight

## Micro LED® SMD LED


### “598 SERIES” 1208 PACKAGE (3.2mm X 1.5mm X 1.0mm) Bi-Color Right Angle



## FEATURES / BENEFITS

- ▲ Compatible with automatic placement equipment
- ▲ RoHS compliant
- ▲ Packaged in 8mm tape, 7” reel and 20 per strip
- ▲ Meets EIA-481-1 pkg. std.

### Package Outline Drawing:



Notes 1. All dimensions are in mm [inches];  
2. Tolerances are ±0.1mm [0.004inch] unless noted.

## ORDERING INFORMATION

5 9 8 - 8 5 1 0 - 2 0 7 F

Packaging Option

2	20 pieces on tape
7	7” reel 3000pcs / reel

## PART NUMBERS

Dialight P/N	EMITTED COLOR	MATERIAL	LENS COLOR	LUMINOUS INTENSITY			DOMINANT WAVELENGTH			FORWARD VOLTAGE			VIEWING ANGLE ° DEGREES	PINOUT
				If = 20 ma			If = 20 ma			If = 20 ma				
				MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX		
598-8510-207F	RED	AllInGaP	Water Clear	40	60	80	630	635	645	1.8	2	2.4	160	4-R <sub>3</sub> 2-G <sub>1</sub>
	GREEN	AllInGaP	Water Clear	30	40	50	560	565	570	1.8	2	2.4	160	4-R <sub>3</sub> 2-G <sub>1</sub>
598-8520-207F	RED-ORANGE	AllInGaP	Water Clear	80	110	150	620	625	630	1.8	2	2.4	160	4-R <sub>3</sub> 2-G <sub>1</sub>
	GREEN	AllInGaP	Water Clear	30	40	50	560	568	570	1.8	2	2.4	160	4-R <sub>3</sub> 2-G <sub>1</sub>
598-8530-207F	ORANGE	AllInGaP	Water Clear	80	100	150	600	605	610	1.8	2	2.4	160	4-R <sub>3</sub> 2-G <sub>1</sub>
	GREEN	AllInGaP	Water Clear	30	45	60	560	568	570	1.8	2	2.4	160	4-R <sub>3</sub> 2-G <sub>1</sub>
598-8540-207F	YELLOW	AllInGaP	Water Clear	90	110	150	587	590	592	1.8	2	2.4	160	4-R <sub>3</sub> 2-G <sub>1</sub>
	GREEN	AllInGaP	Water Clear	30	40	60	560	565	570	1.8	2	2.4	160	4-R <sub>3</sub> 2-G <sub>1</sub>
598-8550-207F	YELLOW	AllInGaP	Water Clear	80	-	100	587	590	592	1.8	2	2.2	160	4-R <sub>3</sub> 2-G <sub>1</sub>
	GREEN	InGaN	Water Clear	90	-	120	520	525	530	2.7	3.2	3.5	160	4-R <sub>3</sub> 2-G <sub>1</sub>
598-8560-207F	YELLOW	AllInGaP	Water Clear	120	135	150	587	590	592	1.8	2.2	2.4	160	4-R <sub>3</sub> 2-G <sub>1</sub>
	RED	AllInGaP	Water Clear	40	50	60	630	635	645	1.8	2.2	2.4	160	4-R <sub>3</sub> 2-G <sub>1</sub>
598-8570-207F	RED	AllInGaP	Water Clear	40	60	80	630	635	640	1.8	2.2	2.4	160	4-R <sub>3</sub> 2-G <sub>1</sub>
	YELLOW-GREEN	AllInGaP	Water Clear	30	40	50	565	570	575	2.8	3.2	3.4	160	SEE EXAMPLE
598-8580-207F	BLUE	InGaN	Water Clear	60	70	80	470	473	475	3	3.2	3.4	160	4-B <sub>3</sub> 2-G <sub>1</sub>
	GREEN	InGaN	Water Clear	200	220	240	520	523	525	2.7	3.2	3.5	160	4-B <sub>3</sub> 2-G <sub>1</sub>

## ABSOLUTE RATINGS (@ Ta = 25°C)

Dialight P/N	Power Dissipation	Forward Current	Reverse Voltage	Operating Temperature Range	Storage Temperature Range	Peak Pulse Forward Current	Electrostatic Discharge
	(mW)	(mA)	(V)	(°C)	(°C)	(mA)	(HBM)
598-8510-207F	48	20	5	-40~+100	-40~+100	100	1000
	48	20	5	-40~+100	-40~+100	100	1000
598-8520-207F	48	20	5	-40~+100	-40~+100	100	1000
	48	20	5	-40~+100	-40~+100	100	1000
598-8530-207F	72	30	5	-40~+85	-40~+100	100	1000
	72	30	5	-40~+85	-40~+100	100	1000
598-8540-207F	48	20	5	-40~+100	-40~+100	100	1000
	48	20	5	-40~+100	-40~+100	100	1000
598-8550-207F	72	30	5	-30~+85	-30~+100	100	1000
	105	30	5	-30~+85	-30~+100	100	1000
598-8560-207F	72	30	5	-30~+85	-30~+100	100	1000
	72	30	5	-30~+85	-30~+100	100	1000
598-8570-207F	72	30	5	-40~+85	-40~+100	100	1000
	102	30	5	-40~+85	-40~+100	100	1000
598-8580-207F	102	30	5	-30~+85	-30~+100	100	1000
	105	30	5	-30~+85	-30~+100	100	1000



A4703



ISO 9001



Dialight Corporation





1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com



MDEI5981208BI\_A

### MECHANICAL DIMENSIONS




REFLOW SOLDERING		HAND SOLDERING	
Pre-heat	160~180°C	Temperature	300°C Max.
Pre-heat time	120 seconds Max.		
Peak temperature	260°C Max.	Soldering time	3 second Max (one time only)
Soldering time	10 seconds Max.		
Condition	Refer to temperature -profile		


### OPTICAL AND ELECTRICAL CHARACTERISTICS CURVES

RED 630-642NM, RED-ORANGE 620-630NM, ORANGE 600-610NM, YELLOW 590-595NM, YELLOW 583-590NM, YELLOW GREEN 570-575NM, GREEN 562-570NM


FORWARD VOLTAGE VS FORWARD CURRENT (Ta=25°C)




RELATIVE INTENSITY VS FORWARD CURRENT (Ta=25°C)



DERATING




RELATIVE INTENSITY VS AMBIENT TEMPERATURE




GREEN 520-525NM, BLUE 470-475NM


FORWARD VOLTAGE VS FORWARD CURRENT (Ta=25°C)




RELATIVE INTENSITY VS FORWARD CURRENT (Ta=25°C)



DERATING



RELATIVE INTENSITY VS AMBIENT TEMPERATURE



A4703



ISO 9001

Dialight Corporation



Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com



MDEI5981208BI\_A