

# ARTESYN AVD75B SERIES

75 Watt 1/16" brick DC/DC Converter



Advanced Energy's Artesyn AVD75B series sixteenth-brick isolated DC-DC converter provides a fully regulated single output at 3.3V, 5V or 12V that is capable of delivering up to 75Watts. It has a wide 2:1 input range of 36 to 75 Vdc and is designed primarily for use with standard 48 V telecommunications equipment supplies. Rated at 75 watts, the converter employs an open-frame construction, offers up to 93% efficiency and accommodates an ambient operating temperature range of -40 to 85°C. A baseplate option is available for enhanced thermal performance. SMT bullet pin with reel tape package is available for reflow processing . The converter uses fixed frequency switching to minimize the need for external EMI filtering.

#### **SPECIAL FEATURES**

- 75 W continuous power
- Ultra high efficiency up to 93%
- Low ripple and noise
- Telecom DC input range
- Baseplate optimised for contact cooling
- Open frame optimized for air cooling
- Through hole and surface mount termination option
- Fixed switching frequency

- High capacitive load capability
- Pre-bias startup capability
- High reliability
- RoHS 6 compliant
- UL94 V-0 materials
- 2-year warranty (consult factory for extended terms)

#### SAFETY

- TUV/CE 62368-1
- UL/cUL 60950-1

# DATA SHEET

#### **Total Power:**

75 Watts (12 V @ 6.25 A) (5 V @ 15 A) (3.3 V @ 23 A)

#### **Input Voltage:**

36 - 75 Vdc

#### Single Output:

12 V, 5 V, 3.3 V

©2020 Advanced Energy Industries, Inc.


# **ELECTRICAL SPECIFICATIONS**

Input	12 V	5 V	3.3 V
Input range	36 - 75 Vdc		
Input surge	100 V / 100 mSec		
Efficiency	93.3% (100% load)	91.5% (100% load)	91.5% (100% load)
I/O insulation	Basic insulation		
I/O isolation	2250 Vdc 1500 Vdc 1500 Vdc		1500 Vdc
Output	12 V	5 V	3.3 V
Output voltage	12 V nominal	5 V nominal	3.3 V nominal
Output current maximum	6.25 A	15 A	23 A
Noise & ripple	64 mV pk-pk typ.	40 mV pk-pk typ.	50 mV pk-pk typ.
Overtemperature protection	Baseplate: 110 °C Open frame: 120 °C hot spot		
Overvoltage protection method / OCP operation	Auto restart / 130% Vout		
Overcurrent protection method / OCP operation	Hiccup 150% lout		
Control	12 V	5 V	3.3 V
Enable	TTL compatible (negative logic)		
Trim function	80% to 110% Vout		
Remote sense	Sense connections provided		
Switching frequency	350 KHz		




# **MECHANICAL DRAWINGS**


### MODEL: AVD75B-48S05-6L



Model: AVD75B-48S05B-6L



#### SIDE VIEW





Notes:

- Different output voltage AVD75B products have slight differences in the mechnical drawing. Please check the specified product's Technical Reference Note for more details
- 2. All specifications are subject to change without notice. Mechanical drawings are for reference only.

6-φ2.0±0.1 2-φ2.3±0.1

SIDE VIEW

L=3.80±0.25mm


UNIT: mm[inch] TOLERANCE: XXmm +0.5mm[X.XX in +0.02in] X.XXmm +0.25mm[X.XXX in +0.01]




# MECHANICAL DRAWINGS (CONTINUED)

#### MODEL: AVD50B-48S05TL

## BOTTOM VIEW





#### UNIT: mm[inch] TOLERANCE: XXmm +0.5mm[X.XX in +0.02in] X.XXmm +0.25mm[X.XXX in +0.01]

#### Notes:

- 1. Different output voltage AVD75B products have slight differences in the mechnical
- drawing. Please check the specified product's Technical Reference Note for more details 2. All specifications are subject to change without notice. Mechanical drawings are for reference only.

# **PIN DESIGNATIONS**

Pin Number	Name	Name
1	Vin+	Positive input terminal
2	Remote ON/OFF	ON/OFF control terminal
3	Vin-	Negative input terminal
4	Vo-	Negative output terminal
5	S-	Negative remote sense
6	Trim	Output voltage trim
7	S+	Positive remote sense
8	Vo+	Positive output terminal





## AVD75B

## **PIN LENGTH OPTIONS**

Device Code Suffix	L		
-4	4.8 mm +0.25 mm		
-6	3.8 mm +0.25 mm		
-8	2.8 mm +0.25 mm		
None	5.8 mm +0.25 mm		

## **ENVIRONMENTAL SPECIFICATIONS**

Operating ambient temperature	-40 °C to +85 °C
Storage temperature	-55 °C to +125 °C
MTBF	2 Million hours

# **ORDERING INFORMATION**

Model Number	Input Voltage	Output Voltage	Output Current	Structure
AVD75B-48S12-6L	36 - 75 Vin	12 Vdc	6.25 A	Open frame
AVD75B-48S12B-6L	36 - 75 Vin	12 Vdc	6.25A	Baseplate
AVD75B-48S12TL	36 - 75 Vin	12 Vdc	6.25A	SMT pin with reel tape package
AVD75B-48S05-6L	36 - 75 Vin	5 Vdc	15 A	Open frame
AVD75B-48S05B-6L	36 - 75 Vin	5 Vdc	15 A	Baseplate
AVD75B-48S05TL	36 - 75 Vin	5 Vdc	15 A	SMT pin with reel tape package
AVD75B-48S3V3-6L	36 - 75 Vin	3.3 Vdc	23 A	Open frame
AVD75B-48S3V3B-6L	36 - 75 Vin	3.3 Vdc	23 A	Baseplate
AVD75B-48S3V3TL	36 - 75 Vin	3.3 Vdc	23 A	SMT pin with reel tape package

Notes:

Standard version is negative enable

-6 = 3.8 mm pin length -T = Surface mount, reel tape package

-L = RoHS 6 compliance

-P = Positive enable





Advanced Energy (AE) has devoted more than three decades to perfecting power for its global customers. AE designs and manufactures highly engineered, precision power conversion, measurement and control solutions for mission-critical applications and processes.

Our products enable customer innovation in complex applications for a wide range of industries including semiconductor equipment, industrial, manufacturing, telecommunications, data center computing, and medical. With deep applications know-how and responsive service and support across the globe, we build collaborative partnerships to meet rapid technological developments, propel growth for our customers, and innovate the future of power.

#### PRECISION | POWER | PERFORMANCE

Specifications are subject to change without notice. Not responsible for errors or omissions. ©2020 Advanced Energy Industries, Inc. All rights reserved. Advanced Energy®, AE® and Artesyn™ are U.S. trademarks of Advanced Energy Industries, Inc.



For international contact information, visit advancedenergy.com.

powersales@aei.com (Sales Support) productsupport.ep@aei.com (Technical Support) +1 888 412 7832