

Warning

This product has been manufactured to your company's specifications as a part for use in your company's general electronic products. It is guaranteed to perform according to delivery specifications. For any other use apart from general electronic equipment, we cannot take responsibility if the product is used in medical devices, nuclear power control equipment, aerospace equipment, fire and security systems, or any other applications in which there is a direct risk to human life and where extremely high levels of reliability are required. If the product is to be used in any of the above applications, we will need to enter into a separate product liability agreement.

- 1) We cannot accept responsibility for any defect, which may arise from additional manufacturing of the product (including disassembly and reassembly), after product delivery.
- 2) We cannot accept responsibility for any defect, which may arise after the application of strong external force to the product.
- 3) We cannot accept responsibility for any defect, which may arise due to the application of static electricity after the product has passed your company's acceptance inspection procedures.
- 4)When the product is in CFL models, CFL service life and brightness will vary according to the performance of the inverter used, leaks, etc. We cannot accept responsibility for product performance, reliability, or defect, which may arise.
- 5) We cannot accept responsibility for intellectual property of a third party, which may arise through the application of our product to your assembly with exception to those issues relating directly to the structure or method of manufacturing of our product.
- 6) We will not be held responsible for any quality guarantee issue for defect products judged As KYOCERA-origin in 2 (two) years from our production or 1(one) year from KYOCERA Group delivery whichever is shorter.

However, priority is given to the contents of the "part (product) basic contract document" concluded in both.





Spec No.	Part No.	Page
	T-55343GD035JU-LW-AIN	3

	-	ICC	VISIOII	record		
Date	Designed	d by :	Engineering	dept.	Confirmed by	v∶QA dept.
2400	Prepar	red	Checked	Approved	Checked	Approved
Rev No Date	Page			Descripti	ons	



Spec No.	Part No.	Page
	T-55343GD035JU-LW-AIN	4

1. Application

This specification applies to TFT-LCD module (T-55343GD035JU-LW-AIN).

2. <u>General Specifications</u>

Screen Size	:	3.5 inches (8.9cm) Diagonal
Active Area	:	70.08(W) x 52.56(H) mm
Display Format	:	320(W) x 3[R.G.B] x 240(H)
Pixel Size	:	0.073 x 3[R.G.B](W) x 0.219(H) mm
Pixel Arrangement	:	RGB-Stripe
Color Depth	:	16M colors
Display Mode	:	Normally White
Viewing Direction	:	12 O'clock (1 Angle of Least Color Inversion)
Surface Treatment	:	AG Coating
Interface	:	24-bit Digital RGB interface(8-bit / color)
Outline Dimension	÷	79.0(W) x 65.0(H) x 3.2Max*(D) mm *Without FPC and Component Area
Weight	·	29.5gmax
Backlight	:	LED Backlight / White
RoHS regulation	:	To our best knowledge, this product satisfies material requirement of RoHS regulation. Our company is doing the best efforts to obtain the equivalent
		certificate from our suppliers.

3. <u>Operating Conditions</u>

Item	Conditions	Temperature range	Remark
Operating temperature range	Panel surface	–20 ~ 70°C	Note1
Storage temperature range	Panel surface	−30 ~ 80°C	

Note1: Operating temperature range defines the operation only and the contrast, response time and other display optical characteristics are set at Ta=+25°C.

Spec No.	Part No.	Page
	T-55343GD035JU-LW-AIN	5

4. <u>Block Diagram</u>



5. <u>I/O Terminal</u>

5.1 CN1 Pin Assignment

Used FPC : P0.5mm, 40pin,T=0.3mm Corresponding Connector : 6240 Series (ELCO)

No.	Symbol	Functional Description
1	RL	Input to select Source driver Datashift direction
2	ТВ	Input to select Gate driver Datashift direction
3	DOTCLK	Clock Signal
4	VSYNC	Vertical Sync Input
5	HSYNC	Horizontal Sync Input
6	ENABLE	Input Data Enable Control
7	DB23	Data Signal Graphic Display Data Red-data (MSB)
8	DB22	Data Signal Graphic Display Data Red-data
9	DB21	Data Signal Graphic Display Data Red-data
10	DB20	Data Signal Graphic Display Data Red-data
11	DB19	Data Signal Graphic Display Data Red-data
12	DB18	Data Signal Graphic Display Data Red-data
13	DB17	Data Signal Graphic Display Data Red-data
14	DB16	Data Signal Graphic Display Data Red-data (LSB)
15	GND	Power Supply (0V, GND)
16	DB15	Data Signal Graphic Display Data Green-data (MSB)
17	DB14	Data Signal Graphic Display Data Green-data
18	DB13	Data Signal Graphic Display Data Green-data
19	DB12	Data Signal Graphic Display Data Green-data
20	DB11	Data Signal Graphic Display Data Green-data
21	DB10	Data Signal Graphic Display Data Green-data
22	DB9	Data Signal Graphic Display Data Green-data
23	DB8	Data Signal Graphic Display Data Green-data (LSB)
24	GND	Power Supply (0V, GND)
25	DB7	Data Signal Graphic Display Data Blue-data (MSB)
26	DB6	Data Signal Graphic Display Data Blue-data
27	DB5	Data Signal Graphic Display Data Blue-data
28	DB4	Data Signal Graphic Display Data Blue-data
29	DB3	Data Signal Graphic Display Data Blue-data
30	DB2	Data Signal Graphic Display Data Blue-data
31	DB1	Data Signal Graphic Display Data Blue-data
32	DB0	Data Signal Graphic Display Data Blue-data (LSB)



			Spec No.		Part No.	Page
					T-55343GD035JU-LW-AIN	7
33	SDI	Serial Inter	face Data			
34	SCL	Serial Inter	face Clock			
35	CS	Serial Inter	face Chip Select	L : Act	tive	
36	RESET	System RES	SET L:Reset			
37	SDO	Serial Inter	face Data			
38	GND	Power Supp	oly (0V, GND)			
39	VCC	Power Supp	oly for System			
40	VCC	Power Supp	oly for System			

5.2. CN2 Pin Assignment

Used FPC : P0.5mm, 3pin,T=0.2mm Corresponding Connector : 6298 Serie

	Corresp	conding Connector : 6298 Series (ELCO)
No.	Symbol	Functional Description
1	LED A	LED Anode Terminal
2	NC	Non Connection
3	LED K	LED Cathode Terminal

6. <u>Electrical Specifications</u>

6.1 Absolute Maximum Ratings

	Ta=-20~70°C, GND=0V				
Parameter	Symbol	Conditions	Min.	Max.	Units
Supply Voltage	VCC	-	-0.3	4.0	V
Input Voltage	VIN		GND-0.3	4.0	V

6.2 DC Characteristics

Ta=-20~70°C, GND=0V

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Supply Voltage for System	VCC	-	3.0	3.3	3.6	V
"High" Level Input Voltage	VIH	-	0.8VCC	-	VCC	V
"Low" Level Input Voltage	VIL	-	0	-	0.2VCC	V
High Level Output Voltage	VOH	-	0.9VCC	-	VCC	V
Low Level Output Voltage	VOL	-	0	-	0.1VCC	V
Opeating mode Current	ICC	VCC-GND=3.3V	-	11.0	16.5	mA



6.3 AC Characteristics

6.3.1 Serial Interface Timing Characteristics

$Ta=-20\sim70^{\circ}C, GND=0V$						
Parameter	Symbol	Min.	Тур.	Max.	Units	
Serial Clock Cycle Time	tclk	50	-	-	ns	
Clock Low Width	tsl	25	-		ns	
Clock High Width	tsh	25	-	ŀ	ns	
Clock Rising Time	trs	-	-	30	ns	
Clock falling Time	tfl			30	ns	
Chip Select Setup Time	tcss	0	-	-	ns	
Chip Select Hold Time	tcsh	10	-	-	ns	
Chip Select High Delay Time	tcsd	20	-	-	ns	
Data Setup Time	tds	5	-	-	ns	
Data Hold Time	tdh	10	-	-	ns	



Spec No.	Part No.	Page
	T-55343GD035JU-LW-AIN	9

6.3.2 Digital RGB Interface Timing Characteristics

		-	Ta=-20	~70°C, GI	ND=0V
Parameter	Symbo	Min.	Тур.	Max.	Units
DOTCLK Frequency	fdotclk	-	6.5	10	MHz
DOTCLK Cycle Time	tdotclk	100	154		ns
Vertical Sync Setup Time	tvsys	20	-	-	ns
Vertical Sync Hold Time	tvsyh	20	-	-	ns
Horizontal Sync Setup Time	thsys	20			ns
Horizontal Sync Hold Time	thsyn	20	-	-	ns
Phase difference of Sync Signal Falling Edge	thv	1		240	tdotclk
DOTCLK Low Width	tckl	50	-	-	ns
DOTCLK High Width	tскн	50	-	-	ns
Data Setup Time	tos	12	-	-	ns
Data Hold Time	ton	12	-	-	ns





Spec No.	Part No.	Page
	T-55343GD035JU-LW-AIN	10





	Spec No.		Part No.	rt No.					
			T·55343GD035JU-LW-AIN						
6.3.5 Reset Timing Charact	teristics								
				Ta=-20	~70°C, GN	D=0V			
Parameter		Symbol	Min.	Тур.	Max.	Units			
Reset "L" Pulse Width		t rw	10	-	-	μs			
RESET	VIL	tres	↓ VIL						
6.4 Power ON Sequence 6.4.1 Data Transfer of SPI					7				
CS CS				Trancfer	Ends				
CS CS SCL			16 17 18 19 20	Trancfer	Ends				

6.4.2 Power ON Procedure (Recommended Sequence)





Spec No.	Part No.	Page
	T-55343GD035JU-LW-AIN	12

Setting Item	Index	Value
Driver Output	0001 h	6300 h
LCD Driver AC Control	0002 h	0200 h
Power Control (1)	0003 h	6064 h
Data and Color Filter Control	0004 h	0447 h
Function Control	0005 h	B084 h
Contrast/ Brightness Control	000A h	4008 h
Frame Cycle Control	000B h	D400 h
Power Control (2)	000D h	423D h
Power Control (3)	000E h	3140 h
Gate Scan Starting Position	000F h	0000 h
Horizontal Porch	0016 h	9F80 h
Virtical Porch	0017 h	2212 h
Power Control (4)	001E h	00DB h
Gamma Control 1	0030 h	0000 h
Gamma Control 2	0031 h	0607 h
Gamma Control 3	0032 h	0006 h
Gamma Control 4	0033 h	0307 h
Gamma Control 5	0034 h	0107 h
Gamma Control 6	0035 h	0001 h
Gamma Control 7	0036 h	0707 h
Gamma Control 8	0037 h	0703 h
Gamma Control 9	003A h	0C00 h
Gamma Control 10	003B h	0006 h

6.4.3 Command List for Power ON (Recommended Setting)



Spec No.	Part No.	Page
	T-55343GD035JU-LW-AIN	13

6.4.4 Color Data Asignment

1) 8-bit / color

					R D	ATA							G DA	ATA							B D	ATA	4		
COLOR	INPUT	MSI	B(DB	23)			LS	B(DI	316)	MSB	(DB1	5)				LSB()	DB8)	MS	B(D	B7)			LS	B(D	В
	DATA	DB 23	DB 22	DB 21	DB 20	DB 19	DB 18	DB 17	DB 16	DB 15	DB 14	DB 13	DB 12	DB 11	DB 10	DB 9	DB 8	$\frac{\mathrm{DB}}{7}$	DB 6	DB 5	DB 4	DB 3	$\frac{\text{DB}}{2}$	DB 1]
	BLACK	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	
	RED (255)	1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	
	GREEN (255)	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	
BASIC	BLUE (255)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	_
COLOR	CYAN	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	
	MAGENTA	1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	
	YELLOW	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	
	WHITE	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	
	RED (0)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	
	RED (1)	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	-
	RED (2)	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	
RED																									
								•																	
	RED (254)	1	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	Ī
	RED (255)	1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	-
	GREEN (0)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	
	GREEN (1)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	
	GREEN (2)	0	0	0	0	0	0	0	0	• 0	0	0	0	0	0	1	0	0	0	0	0	0	0	0	-
GREEN																									+
	GREEN	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	0	0	0	0	0	0	0	0	·····
	GREEN (255)	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	
	BLUE (0)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	+
	BLUE (1)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	+
	BLUE (2)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	+
BLUE									.																+
	BLUE (254)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	
	BLUE (255)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	

[Note]

1) Definition of gray scale

Color (n) --- n indicates gray scale level.

Higher n means brighter level.

2) Data 1:High, 0: Low

Spec No.

T-55343GD035JU-LW-AIN

Part No.

2)	6-bit / colo	r																	
				RΙ	DATA	A		G DATA						B DATA					
COLOR	INPUT	MSB LSB((DB2: DB18	3))				MSB(I LSB(D	DB15) 0B10)					MSE LSB	8(DB7 (DB2)				
	DATA	DB23	DB2 2	DB2 1	DB2 0	DB19	DB18	DB15	DB14	DB13	DB12	DB11	DB10	DB7	DB6	DB5	DB4	DB3	DB2
	BLACK	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	RED (63)	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0
	GREEN (63)	0	0	0	0	0	0	1	1	1	1	1	1	0	0	0	0	0	0
BASIC	BLUE (63)	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1
COLOR	CYAN	0	0	0	0	0	0	1	1	1	1	1	1	1	1	1	1	1	1
	MAGENTA	1	1	1	1	1	1	0	0	0	0	0	0	1	1	1	1	1	1
	YELLOW	1	1	1	1	1	1	1	1	1	1	1	1	0	0	0	0	0	0
	WHITE	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	RED (0)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	Q	0	0	0
	RED (1)	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0
	RED (2)	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0
RED																			
	RED (62)	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0
	RED (63)	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0
	GREEN (0)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	GREEN (1)	0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0
	GREEN (2)	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0
GREEN																			
		•																	
	GREEN (62)	0	0	0	0	0	0	1	1	1	1	1	0	0	0	0	0	0	0
	GREEN (63)	0	-0	0	0	0	0	1	1	1	1	1	1	0	0	0	0	0	0
	BLUE (0)	0	0	0	-0-	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	BLUE (1)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1
	BLUE (2)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0
BLUE																			
	BLUE (62)	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	0
	BLUE (63)	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1
INT 1																			

INOt

1) Definition of gray scale

Color (n) --- n indicates gray scale level.

Higher n means brighter level.

2) Data 1:High, 0: Low

3) In case of 6bit / color Lower 2bit at each color (DB17, DB16, DB9, DB8, DB1, DB0) must be connected to GND.



Spec No.	Part No.	Page
	T-55343GD035JU-LW-AIN	15

6.5 Power OFF Sequence

6.5.1 Power OFF Procedure (Recommended Sequence)



6.5.2 Command List for Power OFF (Recommended Setting)

Setting Item	Index	Value
Power Control (1)	0003 h	0100 h

6.6 Inverted Scan Capability

This module has the capability of inverting scan direction by signaling from controller. Note: Scan direction cannot be changed during operation.

The following drawing shows the relationship between the viewing direction and the scan direction.

Normal scan (TB: H RL: H)

Reverse scan (TB: L RL: L)







Spec No.	Part No.	Page
	T-55343GD035JU-LW-AIN	16

6.7 Lighting Specifications

6.7.1 Absolute Maximum Ratings

						Ta=25°C
Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Forward Current	$\mathbf{I}\mathbf{F}$	Note 2	-	-	35	mA
Allowable Reverse Current	Ir	-	-	-	50	μA
LED Power Dissipation	Pd	-	-	-	0.77	W

Note 1: This value is for each 1 line.

Note 2: Refer to the forward current derating curve.



6.7.2 Operating Characteristics

Ta=25°C

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Forwrad Current	If	Note1	-	-	20	mA
Forward Voltage	VF	IF=20mA / 1	-	19.2	-	V
Power	PL				0.39	W

Note1: Current of LED par chip must be lower than 15mA at 70 degC.

The current of LED must be tuned to satisfy as Forword Current Derating Curve mentioned relationship

7. Optical Specifications

7.1 Optical Characteristic

T		0	Co	nditi	ons	Sta	ndard Va	alue	TT. 1	Method of		
Item		Symbol	θ	φ	С	Min.	Тур.	Max.	Unit	Measure	Remark	
(1)Brightness		В	0°	0°		-	400		Cd/m^2		Note1	
(2)Contrast		CR	Optin Viev An	mum ving gle		400	700	-	-			
	D. 1	Rx	0°	0°		0.58	0.63	0.68	-			
	Red	Ry	0°	0°		0.31	0.36	0.41	-			
	Croop	Gx	0°	0°		0.30	0.35	0.40		(Fig.1)		
(3)Color	Green	Gy	0°	0°		0.55	0.60	0.65	-			
Coordinates	Dhuo	Bx	0°	0°		0.10	0.15	0.20	-			
	Diue	By	0°	0°		0.05	0.10	0.15				
	1171 .	Wx	0°	0°		0.28	0.33	0.38	-			
	White	Wy	0°	0°		0.30	0.35	0.40	-			
(4)Brightness		-	0°	0°		70	-		%	(F : 0)		
Uniformity	7									(F1g.2)		
(5)Vertical	Up	θυ	-	0°	≥ 5	-	80	-	Degree			
Viewing Ang	le _{Down}	θD	-	0°	≥ 5	-	80	-	Degree			
(6)Horizontal	Left	φL	0°	-	≥5	-	80	-	Degree	(Fig.3)		
Viewing Ang	^{le} Right	фr	0°	-	≥ 5	-	80	-	Degree			
(7)Response	Rise	τr	0°	0°		-	8	-	ms	(E' ()		
Time	Decay	τd	0°	0°		-	15	-	ms	(Fig.4)		

Note1:Under the condition of maximum brightness

Conditions for Measuring

Environment: Dark room with no light or close to no light.

 \bigcirc Temperature: 25 \pm 5°C

♦ Humidity: 40~70%RH

• Optimal viewing angle (The angle of Least Color

Inversion)



18Method of Brightness Measurement (Fig.1) (1) Measuring Device TOPCON BM-5, Measuring Field: 1° (2) Measuring Point Center of Display $\theta=0^{\circ}, \phi=0^{\circ}$ On condition θ : A vertical angle from measuring direction to perpendicular. ϕ : A horizontal angle from measuring direction to perpendicular. (3) Method of Measuring Apply signal voltage (displayed in white) to maximize brightness and measure brightness B (cd/m²). The distance between BM-5's front lens to surface panel is 500mm. Measured after backlight has been lit for more than 30 minutes. Center (Pixel) (X, Y)=(120,160) LCD Module Distance: 500mm **TOPCON BM-5** <u>Fig. 1</u>





Part No.

◆ Method of Viewing Angle Measurement (Fig.3)

- (1) Measuring Device ELDIM EZ : CONTRAST
- (2) Measuring Point Center of display: Same as Method of Brightness Measurement
- (3) Angle of Measuring
 - $\boldsymbol{\theta}$: An angle vertical to perpendicular line from the viewing direction.
 - $\boldsymbol{\phi}$: An angle horizontal to perpendicular from the viewing direction.
- (4) Method of Measuring

Set the module on the rotation table and measure a vertical axis direction in the state that fixed $\varphi=0$ degrees horizontal axis direction to $\theta=90$ degrees. (Viewing angle is measured automatically by EZ CONTRAST).



- ◆ Measuring Response Time (Fig.4)
- Measuring Device
 TOPCON BM-5, Measuring Field: 1°
 Tektronix Digital Oscilloscope
- (2) Measuring Point Center of display, same as Method of Brightness Measurement
- (3) Method of Measuring
 - * Set LCD panel to $\theta=0^{\circ}$, and $\phi=0^{\circ}$.
 - Input white \rightarrow black \rightarrow white to display by switching signal voltage.
 - If the luminance is 0% and 100% immediately before the change of signal voltage, then τr is optical response time during the change from 90% to 10% immediately after rise of signal voltage, and τd is optical response time during the change from 10% to 90% immediately after decay of signal voltage.



Spec No.	Part No.	Page
	T-55343GD035JU-LW-AIN	22

7.2 Definition of Viewing Angle and Optimum Viewing Area

*Point • shows the point where contrast ratio is measured. : θ = 0°, ϕ = -° *Driving condition: Ff=60Hz



8. <u>Test</u>

No abnormal function and appearance are found after the following tests.

Conditions: Unless otherwise specified, tests will be conducted under the following condition. Temperature: 20 ± 5 °C Humidity : 65 ± 5 %RH

tests will be not conducted under functioning state.

No.	Parameter	Conditions	Notes	
1	High Temperature Operating	70°C±2°C, 96hrs (operation state)		
2	Low Temperature Operating	-20°C±2°C, 96hrs (operation state)	1	
3	High Temperature Storage	80°C±2°C, 96hrs	2	
4	Low Temperature Storage	-30°C±2°C, 96hrs	1,2	
5	Damp Proof Test	40°C±2°C,90~95%RH, 96hrs	1,2	
6	Vibration Test	Total fixed amplitude: 1.5mm Vibration Frequency : 10~55Hz One cycle 60 seconds to 3 directions of X, Y, Z each 15 minutes	3	
7	Shock Test	To be measured after dropping from 60cm the concrete surface in packing state. Dropping method corner dropping A corner : once Edge dropping B,C,D edge : once Face dropping E,F,G face : once		
		Concrete Surface /////////////////////////////////		

Note 1 :No dew condensation to be observed.

Note 2 : The function test shall be conducted after 4 hours storage at the normal

Temperature and humidity after removed from the test chamber.

Note 3 :Vibration test will be conducted to the product itself without putting it in a container.



9. <u>Appearance Standards</u>

9.1 Inspection conditions

The distance between the eyes and the sample shall be more than 30cm. All directions for inspecting the sample should be within 45° against perpendicular line.





Spec No.	Part No.	Page
	T-55343GD035JU-LW-AIN	25

9.3 Standards

No.	Parameter			Criteria		
1	G Line	Nothing				
2	S Line	Nothing				
3	Leak	Nothing				
4	Bright and					
	Dark dot	Zone	Acc	eptable Nu	mber	
		А	Brigh	t Dot	0	
			Dark	x Dot	2	
		В	Brigh	t Dot	2	
			Dark	a Dot	4	
		С		Disregare	1 <u> </u>	
		Definition of	Bright dot	ζ		
		Anything the	at can be se	een through	10% tran	emission ND filte
		black Signal	is inputted	l.	Ť	
		Adjacent Dot	: Horizonta	al and Verti	cal Contin	uous Bright dots.
		\rightarrow Nothing				
5	Contrast Variation	Not to be cons	picuous del	fects.		
6	Black and White	(1) Round Sha	ре	~		
	Spots, Foreign		Zone	Acc	eptable Nu	mber
	Material in Polarizer	Dimension(m	nm)	А	В	С
	and LR/AR Coat	$D \leq 0.5$		Disre	gard	
	Bright point	$0.15 < D \le 0$	0.5	4	L	Disregard
		0.5 < D		1	-	
		D = (Long	+ Short) /	2		
		(2) Line Shape	<u>,</u>			
			Zone	Acc	eptable Nu	mber
		X(mm) V (mm)	А	В	С
		1 I Y				
		_	W≤0.05	Disre	gard	_
		_ L≤2.0	W≤0.05 W≤0.02	Disre 2	gard 2	_
		- L≤2.0 L≤1.0	W≤0.05 W≤0.02 W≤0.03	Disre 2 1	gard	Disregard
		- L≤2.0 L≤1.0 L>2.0	W≤0.05 W≤0.02 W≤0.03 −	Disre 2 1 0	gard	Disregard
		- L≤2.0 L≤1.0 L>2.0 -	W≤0.05 W≤0.02 W≤0.03 - W>0.03	Disre 2 1 0 0	gard 2 -))	Disregard
		- L≤2.0 L≤1.0 L>2.0 - X∶Length	W≤0.05 W≤0.02 W≤0.03 - W>0.03 Y : Width	Disre 2 1 ((gard 2)	Disregard
		$-$ $L \le 2.0$ $L \le 1.0$ $L > 2.0$ $-$ $X : Length$ $Total defects s$	W≤0.05 W≤0.02 W≤0.03 - W>0.03 Y: Width hall not exe	Disre	gard 2 	Disregard



		Spec No.	Part	No. T-55343GD0356	JU-LW-AIN	Page 26
<u>No.</u> 8	Parameter Air Bubbles (between glass & polarizer)	Zone Dimension (mm) D ≤0.10 0.10 < D ≤0.15 0.15 < D ≤0.20	Crite: A Di	ria Acceptable Nu B sregard 1 1	mber C Disregard	20
		< D ≤0.20 The polarizer edge has	not float	ed.		
9	Polarizer Scratches	Not to be conspicuous de	fects.			
10	Polarizer Dirts	If the stains are removed defective.	d easily i	rom LCDP su	rface, the mod	lule

10. Lot number identification

The lot number shall be indicated on the back of the backlight case of each LCD.



No①. - No⑤. above indicate
①Data matrix(For internal control purpose only)
(The item from parts No. to Version No. is included in data matrix.)
②Module product name
③Manufacturing Date
④Version Number
⑤Country of origin (Japan or China)

③Manufacturing Date :

Year 0~9,for 2020~2029 Month 1~9, X~Z, for Jan. ~ Dec. Day 01~31,for 1st to 31th

11. <u>Applying Precautions</u>

Please contact us when questions and/or new problems not specified in this Specifications arise.



27

The Following precautions will guide you in handling our product correctly.

Spec No.

- 1) Liquid crystal display devices
- 1. The liquid crystal display panel used in the liquid crystal display module is made of plate glass. Avoid any strong mechanical shock. Should the glass break handle it with care.
- 2. The polarizer adhering to the surface of the LCD is made of a soft material. Guard against scratching it.
- 2) Care of the liquid crystal display module against static electricity discharge.
- 1. When working with the module, be sure to ground your body and any electrical equipment you may be using. We strongly recommend the use of anti static mats (made of rubber), to protect worktables against the hazards of electrical shock.
- 2. Avoid the use of work clothing made of synthetic fibers. We recommend cotton clothing or other conductivity-treated fibers.
- 3. Slowly and carefully remove the protective film from the LCD module, since this operation can generate static electricity.
- 3) When the LCD module must be stored for long periods of time:
 - 1. Protect the modules from high temperature and humidity.
 - Conditions:
 - Temperature: 0°C~40°C : Less than 60%RH Humidity
 - No dew condensation to be observed.

2.Keep the modules out of direct sunlight or direct exposure to ultraviolet rays.

- 3. Protect the modules from excessive external forces.
- 4.After a long period storage of the product (or LCD) under the low temperature and the dark, it might take a longer time to turn on the CCFL than normal.
- 4) Use the module with a power supply that is equipped with an overcurrent protector circuit, since the module is not provided with this protective feature.
- 5) Do not ingest the LCD fluid itself should it leak out of a damaged LCD module. Should hands or clothing come in contact with LCD fluid, wash immediately with soap.
- 6) Conductivity is not guaranteed for models that use metal holders where solder connections between the metal holder and the PCB are not used. Please contact us to discuss appropriate ways to assure conductivity.
- 7) For models which use CFL:
 - 1. High voltage of 1000V or greater is applied to the CFL cable connector area. Care should be taken not to touch connection areas to avoid burns.
 - 2. Protect CFL cables from rubbing against the unit and thus causing the wire jacket to become worn.
 - 3. The use of CFLs for extended periods of time at low temperatures will significantly shorten their service life.
 - 4. After storing the product (or LCD) under low temperature and/or in dark atmosphere for a long period of time, CCFL may take longer time to reach its specified brightness.



- 8) For models which use touch panels:
- 1.Do not stack up modules since they can be damaged by components on neighboring modules.
- 2.Do not place heavy objects on top of the product. This could cause glass breakage.
- 9) For models which use COG,TAB,or COF:
- 1. The mechanical strength of the product is low since the IC chip faces out unprotected from the rear. Be sure to protect the rear of the IC chip from external forces.
- 2. Given the fact that the rear of the IC chip is left exposed, in order to protect the unit from electrical damage, avoid installation configurations in which the rear of the IC chip runs the risk of making any electrical contact.
- 10) Models which use flexible cable, heat seal, or TAB:1.In order to maintain reliability, do not touch or hold by the connector area.2.Avoid any bending, pulling, or other excessive force, which can result in broken connections.
- 11) In case of buffer material such as cushion / gasket is assembled into LCD module, it may have an adverse effect on connecting parts (LCD panel-TCP / HEAT SEAL / FPC / etc., PCB-TCP / HEAT SEAL / FPC etc., TCP-HEAT SEAL, TCP-FPC, HEAT SEAL-FPC, etc.,) depending on its materials. Please check and evaluate these materials carefully before use.
- 12) In case of acrylic plate is attached to front side of LCD panel, cloudiness (very small cracks) can occur on acrylic plate, being influenced by some components generated from polarizer film. Please check and evaluate those acrylic materials carefully before use.

