

PC3H71xNIP0F Series

*4-channel package type is also available. (model No. **PC3Q71xNIP0F Series**)

Mini-flat Half Pitch Package High CMR, Low Input Current Photocoupler



■ Description

PC3H71xNIP0F Series contains a IRED optically coupled to a phototransistor.

It is packaged in a 4-pin mini-flat, half pitch type. Input-output isolation voltage(rms) is 2.5kV.

Collector-emitter voltage is 80V, CTR is 100% to 700% at input current of 0.5mA and CMR is MIN. $10kV/\mu s$.

■ Features

- 1. 4-pin Mini-flat Half pitch package (Lead pitch : 1.27mm)
- 2. Double transfer mold package (Ideal for Flow Soldering)
- 3. Low input current type (I_F=0.5mA)
- 4. High collector-emitter voltage (V_{CEO}: 80V)
- 5. High noise immunity due to high common mode rejection voltage (CMR : MIN. 10kV/μs)
- 6. Isolation voltage between input and output ($V_{iso(rms)}$: 2.5kV)
- 7. Lead-free and RoHS directive compliant

■ Agency approvals/Compliance


- 1. Recognized by UL1577 (Double protection isolation), file No. E64380 (as model No. **PC3H71**)
- 2. Package resin: UL flammability grade (94V-0)

■ Applications

- 1. Programmable controllers
- 2. Facsimiles
- 3. Telephones




■ Internal Connection Diagram



- 1 Anode
- ② Cathode
- ③ Emitter
- 4 Collector

■ Outline Dimensions

(Unit: mm)



Plating material: SnCu (Cu: TYP. 2%)



Data code (2 digit)

1st digit				2nd digit		
Year of production				Month of production		
A.D.	Mark	A.D	Mark	Month	Mark	
1990	A	2002	P	January	1	
1991	В	2003	R	February	2	
1992	С	2004	S	March	3	
1993	D	2005	T	April	4	
1994	Е	2006	U	May	5	
1995	F	2007	V	June	6	
1996	Н	2008	W	July	7	
1997	J	2009	X	August	8	
1998	K	2010	A	September	9	
1999	L	2011	В	October	0	
2000	M	2012	С	November	N	
2001	N	:	:	December	D	

repeats in a 20 year cycle

Country of origin Japan

Rank mark
Refer to the Model Line-up table



■ Absolute Maximum Ratings

Absolute Maximum Ratings $(T_a=25^{\circ}C)$							
	Parameter	Symbol	Rating	Unit			
	Forward current	I_F	10	mA			
Input	*1 Peak forward current	I_{FM}	200	mA			
Inf	Reverse voltage	V_R	6	V			
	Power dissipation	P	15	mW			
	Collector-emitter voltage	V_{CEO}	80	V			
Output	Emitter-collector voltage	V _{ECO}	6	V			
Out	Collector current	I_{C}	50	mA			
	Collector power dissipation	P_{C}	150	mW			
Total power dissipation		P _{tot}	170	mW			
Operating temperature		Topr	-30 to +100	°C			
Storage temperature		T _{stg}	-40 to +125	°C			
*2 Isolation voltage		V _{iso (rms)}	2.5	kV			
*3 Soldering temperature		T_{sol}	260	°C			

^{*1} Pulse width≤100µs, Duty ratio : 0.001 *2 40 to 60%RH, AC for 1 minute, f=60Hz *3 For 10s

■ Electro-optical Characteristics

 $(T_a=25^{\circ}C)$

	-							(1a-25 C)
Parameter			Symbol	Conditions	MIN.	TYP.	MAX.	Unit
	Forward voltage		V_F	$I_F=10mA$	_	1.2	1.4	V
Input	Reverse current		I_R	$V_R=4V$	-	-	10	μΑ
	Terminal capacitance		C_t	V=0, f=1kHz	_	30	250	pF
	Collector dark current		I_{CEO}	$V_{CE}=50V, I_{F}=0$	_	_	100	nA
Output	Collector-emitter brea	Collector-emitter breakdown voltage		$I_{C}=0.1 \text{ mA}, I_{F}=0$	80	-	_	V
	Emitter-collector breakdown voltage		BV_{ECO}	$I_{E}=10\mu A, I_{F}=0$	6	-	-	V
	Collector current		I_{C}	$I_F=0.5$ mA, $V_{CE}=5$ V	0.5	_	3.5	mA
	Collector-emitter saturation voltage		V _{CE (sat)}	$I_F=10mA$, $I_C=1mA$	_	-	0.2	V
	Isolation resistance		$R_{\rm ISO}$	DC500V, 40 to 60%RH	5×10 ¹⁰	1×10 ¹¹	_	Ω
Transfer	Floating capacitance		C_{f}	V=0, f=1MHz	-	0.6	1.0	pF
charac- teristics	Response time	Rise time	t_r	V 2V I 2m A D 1000	_	4	18	μs
		Fall time	$t_{\rm f}$	$V_{CE}=2V$, $I_{C}=2mA$, $R_{L}=100\Omega$	_	3	18	μs
	Common mode rejection voltage		CMR	T_a =25°C, R_L =470 Ω , V_{CM} =1.5kV(peak) I_F =0, V_{CC} =9V, V_{np} =100mV	10	-	-	kV/μs




■ Model Line-up


Package	Taping 3 000pcs/reel	Rank mark	I _C [mA] (I _F =0.5mA, V _{CE} =5V, T _a =25°C)	
Model No.	PC3H710NIP0F	with or without	0.5 to 3.5	
	PC3H711NIP0F	A	0.7 to 1.75	
	PC3H712NIP0F	В	1.0 to 2.5	
	PC3H715NIP0F	A or B	0.7 to 2.5	

Please contact a local SHARP sales representative to inquire about production status.



Fig.1 Test Circuit for Common Mode Rejection Voltage





capacitance between primary and secondary side.

Fig.2 Forward Current vs. Ambient **Temperature**




Fig.3 Diode Power Dissipation vs. Ambient **Temperature**




Fig.4 Collector Power Dissipation vs. **Ambient Temperature**





Fig.5 Total Power Dissipation vs. Ambient **Temperature**



Sheet No.: D2-A02502EN



Fig.6 Peak Forward Current vs. Duty Ratio




Fig.8 Current Transfer Ratio vs. Forward Current




Fig.10 Relative Current Transfer Ratio vs.
Ambient Temperature




Fig.7 Forward Current vs. Forward Voltage




Fig.9 Collector Current vs. Collector-emitter Voltage




Fig.11 Collector - emitter Saturation Voltage vs. Ambient Temperature






Fig.12 Collector Dark Current vs. Ambient Temperature




Fig.14 Response Time vs. Load Resistance (Saturation region)




Fig.16 Frequency Response




Fig.13 Response Time vs. Load Resistance (active region)






Fig.15 Test Circuit for Response Time



Please refer to the conditions in Fig.13 and Fig.14

Fig.17 Collector-emitter Saturation Voltage vs. Forward Current



Remarks: Please be aware that all data in the graph are just for reference and not for guarantee.



■ Design Considerations

Design guide

While operating at I_F<0.5mA, CTR variation may increase.

Please make design considering this fact.

In case that some sudden big noise caused by voltage variation is provided between primary and secondary terminals of photocoupler some current caused by it is floating capacitance may be generated and result in false operation since current may go through IRED or current may change.

If the photocoupler may be used under the circumstances where noise will be generated we recommend to use the bypass capacitors at the both ends of IRED.


This product is not designed against irradiation and incorporates non-coherent IRED.

Degradation

In general, the emission of the IRED used in photocouplers will degrade over time.

In the case of long term operation, please take the general IRED degradation (50% degradation over 5 years) into the design consideration.

Recommended Foot Print (reference)



(Unit:mm)

[☆] For additional design assistance, please review our corresponding Optoelectronic Application Notes.



■ Manufacturing Guidelines


Soldering Method

Reflow Soldering:

Reflow soldering should follow the temperature profile shown below.

Soldering should not exceed the curve of temperature profile and time.

Please don't solder more than twice.



Flow Soldering:

Due to SHARP's double transfer mold construction submersion in flow solder bath is allowed under the below listed guidelines.

Flow soldering should be completed below 260°C and within 10s.

Preheating is within the bounds of 100 to 150°C and 30 to 80s.

Please don't solder more than twice.

Hand soldering

Hand soldering should be completed within 3s when the point of solder iron is below 400°C.

Please don't solder more than twice.

Other notices

Please test the soldering method in actual condition and make sure the soldering works fine, since the impact on the junction between the device and PCB varies depending on the tooling and soldering conditions.



Cleaning instructions

Solvent cleaning:

Solvent temperature should be 45°C or below Immersion time should be 3 minutes or less

Ultrasonic cleaning:

The impact on the device varies depending on the size of the cleaning bath, ultrasonic output, cleaning time, size of PCB and mounting method of the device.

Therefore, please make sure the device withstands the ultrasonic cleaning in actual conditions in advance of mass production.

Recommended solvent materials:

Ethyl alcohol, Methyl alcohol and Isopropyl alcohol

In case the other type of solvent materials are intended to be used, please make sure they work fine in actual using conditions since some materials may erode the packaging resin.

Presence of ODC

This product shall not contain the following materials.

And they are not used in the production process for this product.

Regulation substances: CFCs, Halon, Carbon tetrachloride, 1.1.1-Trichloroethane (Methylchloroform)

Specific brominated flame retardants such as the PBBOs and PBBs are not used in this product at all.

This product shall not contain the following materials banned in the RoHS Directive (2002/95/EC).

•Lead, Mercury, Cadmium, Hexavalent chromium, Polybrominated biphenyls (PBB), Polybrominated diphenyl ethers (PBDE).

Sheet No.: D2-A02502EN



■ Package specification

● Tape and Reel package


Package materials

Carrier tape : PS

Cover tape: PET (three layer system)

Reel: PS

Carrier tape structure and Dimensions





Dimensions List

(Unit	:	mm)

A	В	С	D	Е	F	G
12.0±0.3	5.5 ^{±0.1}	$1.75^{\pm0.1}$	8.0 ^{±0.1}	2.0 ^{±0.1}	4.0 ^{±0.1}	φ1.5 ^{+0.1}
Н	I	J	K	L		
7.5 ^{±0.1}	$0.3^{\pm0.05}$	2.3 ^{±0.1}	3.1 ^{±0.1}	φ1.6 ^{+0.1}		


Reel structure and Dimensions






Dimensio	ns List	(Unit: mm)		
a	b	С	d	
330	13.5±1.5	100±1.0	13 ^{±0.5}	
e	f	g		
23±1.0	2.0±0.5	2.0 ^{±0.5}		

Direction of product insertion





[Packing: 3 000pcs/reel]



■ Important Notices

- · The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- · Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- · Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:
- (i) The devices in this publication are designed for use in general electronic equipment designs such as:
 - --- Personal computers
 - --- Office automation equipment
 - --- Telecommunication equipment [terminal]
 - --- Test and measurement equipment
 - --- Industrial control
 - --- Audio visual equipment
 - --- Consumer electronics
- (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection

with equipment that requires higher reliability such as:

- --- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
- --- Traffic signals
- --- Gas leakage sensor breakers
- --- Alarm equipment
- --- Various safety devices, etc.
- (iii) SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:
 - --- Space applications
 - --- Telecommunication equipment [trunk lines]
 - --- Nuclear power control equipment
 - --- Medical and other life support equipment (e.g., scuba).
- · If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- · Contact and consult with a SHARP representative if there are any questions about the contents of this publication.

[E190] Sheet No.: D2-A02502EN