


Vishay Siliconix

Power MOSFET

PRODUCT SUMMARY						
V _{DS} (V)	100					
R _{DS(on)} (Ω)	V _{GS} = 5.0 V 0.27					
Q _g (Max.) (nC)	12					
Q _{gs} (nC)	3.0					
Q _{gd} (nC)	7.1					
Configuration	Single					



S N-Channel MOSFET

FEATURES

- Dynamic dV/dt Rating
- Repetitive Avalanche Rated
- Surface Mount (IRLR120, SiHLR120)
- Straight Lead (IRLU120, SiHLU120)
- Available in Tape and Reel
- Logic-Level Gate Drive
- $R_{DS(on)}$ Specified at $V_{GS} = 4 V$ and 5 V
- Material categorization: For definitions of compliance please see <u>www.vishav.com/doc?99912</u>

DESCRIPTION

Third generation power MOSFETs from Vishay provide the designer with the best combination of fast switching, ruggedized device design, low on-resistance and cost-effectiveness.

The DPAK is designed for surface mounting using vapor phase, infrared, or wave soldering techniques. The straight lead version (IRLU, SiHLU series) is for through-hole mounting applications. Power dissipation levels up to 1.5 W are possible in typical surface mount applications.

ORDERING INFORMATI	ON				
Package	DPAK (TO-252)	DPAK (TO-252)	DPAK (TO-252)	DPAK (TO-252)	IPAK (TO-251)
Lead (Pb)-free and Halogen-free	SiHLR120-GE3	SiHLR120TRL-GE3	SiHLR120TR-GE3	SiHLR120TRR-GE3	SiHLU120-GE3
Lood (Db) free	IRLR120PbF	IRLR120TRLPbF ^a	IRLR120TRPbF ^a	IRLR120TRRPbF ^a	IRLU120PbF
Lead (Pb)-free	SiHLR120-E3	SiHLR120TL-E3 ^a	SiHLR120T-E3 ^a	SiHLR120TR-E3a	SiHLU120-E3

Note

a. See device orientation.

ABSOLUTE MAXIMUM RATINGS (T _C	= 25 °C, unl	ess otherwis	se noted)		
PARAMETER			SYMBOL	LIMIT	UNIT
Drain-Source Voltage		V _{DS}	100	v	
Gate-Source Voltage			V _{GS}	± 10	v
Continuous Drain Current		7.7			
Continuous Drain Current	Ι _D	4.9	А		
Pulsed Drain Current ^a			I _{DM}	31	
Linear Derating Factor			0.33	W/°C	
Linear Derating Factor (PCB Mount) ^e				0.020	W/ C
Single Pulse Avalanche Energy ^b			E _{AS}	210	mJ
Repetitive Avalanche Current ^a			I _{AR}	7.7	А
Repetitive Avalanche Energy ^a			E _{AR}	4.2	mJ
Maximum Power Dissipation	25 °C	D	42	14/	
Maximum Power Dissipation (PCB Mount)e	PD	2.5	W		
Peak Diode Recovery dV/dt ^c	dV/dt	5.5	V/ns		
Operating Junction and Storage Temperature Range	е		T _J , T _{stg}	- 55 to + 150	*0
Soldering Recommendations (Peak Temperature) ^d	for	10 s		260	- °C

Notes

a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).

b. V_{DD} = 25 V, starting T_J = 25 °C, L = 5.3 mH, R_g = 25 Ω , I_{AS} = 7.7 A (see fig. 12).

c. $I_{SD} \leq 9.2$ A, dl/dt ≤ 110 A/µs, $V_{DD} \leq V_{DS}, \, T_J \leq 150$ °C.

d. 1.6 mm from case.

e. When mounted on 1" square PCB (FR-4 or G-10 material).

S13-0167-Rev. D, 04-Feb-13





www.vishay.com

Vishay Siliconix

THERMAL RESISTANCE RATINGS							
PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT		
Maximum Junction-to-Ambient	R _{thJA}	-	-	110			
Maximum Junction-to-Ambient (PCB Mount) ^a	R _{thJA}	-	-	50	°C/W		
Maximum Junction-to-Case (Drain)	R _{thJC}	-	-	3.0			

Note

a. When mounted on 1" square PCB (FR-4 or G-10 material).

PARAMETER	SYMBOL	TES	T CONDITIONS	MIN.	TYP.	MAX.	UNIT
Static		<u>.</u>					
Drain-Source Breakdown Voltage	V _{DS}	V _{GS} :	= 0 V, I _D = 250 μA	100	-	-	V
V _{DS} Temperature Coefficient	$\Delta V_{DS}/T_J$	Reference	e to 25 °C, I _D = 1 mA	-	0.13	-	V/°C
Gate-Source Threshold Voltage	V _{GS(th)}	V _{DS} =	= V _{GS} , I _D = 250 μΑ	1.0	-	2.0	V
Gate-Source Leakage	I _{GSS}		V _{GS} = ± 10 V	-	-	± 100	nA
		V _{DS} =	= 100 V, V _{GS} = 0 V	-	-	25	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 80 V	, V _{GS} = 0 V, T _J = 125 °C	-	-	250	μA
	_	$V_{GS} = 5.0 V$	I _D = 4.6 A ^b	-	-	0.27	
Drain-Source On-State Resistance	R _{DS(on)}	V _{GS} = 4.0 V		-	-	0.38	Ω
Forward Transconductance	9 _{fs}	V _{DS} =	= 50 V, I _D = 4.6 A ^b	4.4	-	-	S
Dynamic		•		I	I	I	
Input Capacitance	C _{iss}		$V_{GS} = 0 V,$	-	490	-	1
Output Capacitance	C _{oss}		$V_{DS} = 25 V,$	-	150	-	pF
Reverse Transfer Capacitance	C _{rss}	f = 1	.0 MHz, see fig. 5	-	30	-	
Total Gate Charge	Qg			-	-	12	
Gate-Source Charge	Q _{gs}	V _{GS} = 5.0 V	I _D = 9.2 A, V _{DS} = 80 V, see fig. 6 and 13 ^b	-	-	3.0	nC
Gate-Drain Charge	Q _{gd}		see lig. 6 and 15	-	-	7.1	
Turn-On Delay Time	t _{d(on)}		•	-	9.8	-	
Rise Time	t _r	- V_D :	= 50 V, I _D = 9.2 A,	-	64	-	- ns
Turn-Off Delay Time	t _{d(off)}		$R_D = 5.2 \Omega$, see fig. 10^{b}	-	21	-	
Fall Time	t _f			-	27	-	
Internal Drain Inductance	L _D	Between lead 6 mm (0.25")	from	-	4.5	-	
Internal Source Inductance	L _S	package and die contact ^c	center of	-	7.5	-	nH
Drain-Source Body Diode Characteristic	s	- -					
Continuous Source-Drain Diode Current	I _S	MOSFET sym showing the		-	-	7.7	Α
Pulsed Diode Forward Current ^a	I _{SM}	integral revers p - n junction		-	-	31	
Body Diode Voltage	V_{SD}	T _J = 25 °C	$I_{\rm S}$ = 7.7 A, $V_{\rm GS}$ = 0 V ^b	-	-	2.5	V
Body Diode Reverse Recovery Time	t _{rr}	т ос «о н	0.0.4 dl/dt 100.4/b	-	110	140	ns
Body Diode Reverse Recovery Charge	Q _{rr}	$I_{\rm J} = 25$ °C, $I_{\rm F}$	= 9.2 A, dl/dt = 100 A/µs ^b	-	0.80	1.0	μC
Forward Turn-On Time	t _{on}	Intrinsic tu	Irn-on time is negligible (turn	-on is dor	ninated b	y L _S and	L _D)

Notes

a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).

b. Pulse width $\leq 300~\mu s;$ duty cycle $\leq 2~\%.$



Vishay Siliconix

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Fig. 1 - Typical Output Characteristics, T_C = 25 °C





Fig. 2 - Typical Output Characteristics, $T_C = 150$ °C






Fig. 4 - Normalized On-Resistance vs. Temperature

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay Siliconix






Fig. 5 - Typical Capacitance vs. Drain-to-Source Voltage








Fig. 6 - Typical Gate Charge vs. Gate-to-Source Voltage




Fig. 8 - Maximum Safe Operating Area



Vishay Siliconix




Fig. 9 - Maximum Drain Current vs. Case Temperature




Fig. 10a - Switching Time Test Circuit




Fig. 10b - Switching Time Waveforms




Fig. 11 - Maximum Effective Transient Thermal Impedance, Junction-to-Case



Vishay Siliconix




Fig. 12a - Unclamped Inductive Test Circuit




Fig. 12b - Unclamped Inductive Waveforms





Fig. 12c - Maximum Avalanche Energy vs. Drain Current









Fig. 13b - Gate Charge Test Circuit

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay Siliconix





a. $V_{GS} = 5$ V for logic level devices


Fig. 14 - For N-Channel

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?91324.

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000







E1

TO-252AA Case Outline

	MILLIN	IETERS	INCHES		
DIM.	MIN.	MAX.	MIN.	MAX.	
А	2.18	2.38	0.086	0.094	
A1	-	0.127	-	0.005	
b	0.64	0.88	0.025	0.035	
b2	0.76	1.14	0.030	0.045	
b3	4.95	5.46	0.195	0.215	
С	0.46	0.61	0.018	0.024	
C2	0.46	0.89	0.018	0.035	
D	5.97	6.22	0.235	0.245	
D1	4.10	-	0.161	-	
E	6.35	6.73	0.250	0.265	
E1	4.32	-	0.170	-	
Н	9.40	10.41	0.370	0.410	
е	2.28	BSC	0.090	BSC	
e1	4.56	BSC	0.180 BSC		
L	1.40	1.78	0.055	0.070	
L3	0.89	1.27	0.035	0.050	
L4	-	1.02	-	0.040	
L5	1.01	1.52	0.040	0.060	
ECN: T13- DWG: 534	0359-Rev. O, 7	03-Jun-13			

.....

Notes

• Dimension L3 is for reference only.

• Xi'an, Mingxin, and GEM SH actual photo.



Revision: 03-Jun-13

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

1



Vishay Siliconix

TO-251AA (HIGH VOLTAGE)



	MILLI	METERS	INC	HES		MILLI	METERS	INC	HES
DIM.	MIN.	MAX.	MIN.	MAX.	DIM.	MIN.	MAX.	MIN.	MA
А	2.18	2.39	0.086	0.094	D1	5.21	-	0.205	-
A1	0.89	1.14	0.035	0.045	E	6.35	6.73	0.250	0.2
b	0.64	0.89	0.025	0.035	E1	4.32	-	0.170	-
b1	0.65	0.79	0.026	0.031	е	2.29	BSC	2.29	BSC
b2	0.76	1.14	0.030	0.045	L	8.89	9.65	0.350	0.3
b3	0.76	1.04	0.030	0.041	L1	1.91	2.29	0.075	0.0
b4	4.95	5.46	0.195	0.215	L2	0.89	1.27	0.035	0.0
с	0.46	0.61	0.018	0.024	L3	1.14	1.52	0.045	0.0
c1	0.41	0.56	0.016	0.022	θ1	0'	15'	0'	15
c2	0.46	0.86	0.018	0.034	θ2	25'	35'	25'	35
D	5.97	6.22	0.235	0.245		•	•	•	

Notes

- 1. Dimensioning and tolerancing per ASME Y14.5M-1994.
- 2. Dimension are shown in inches and millimeters.
- 3. Dimension D and E do not include mold flash. Mold flash shall not exceed 0.13 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body.
- 4. Thermal pad contour optional with dimensions b4, L2, E1 and D1.
- 5. Lead dimension uncontrolled in L3.
- 6. Dimension b1, b3 and c1 apply to base metal only.
- 7. Outline conforms to JEDEC outline TO-251AA.



Vishay Siliconix

RECOMMENDED MINIMUM PADS FOR DPAK (TO-252)



Recommended Minimum Pads Dimensions in Inches/(mm)

Return to Index



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.