# Phase-Cut Dimmable Flyback or Buck-Boost Current Control with Active PFC for LED lighting

# DESCRIPTION

ONDUCTOR

The TS19320CS is a phase-cut (TRIAC) dimmable constant current control IC with active power factor correction isolated or non-isolated AC-DC LED lighting control. The TS19320CS is configurable as an isolated, primary-side-regulated Flyback controller or non-isolated Buck-Boost converter. It is compatible with many types of TRIAC dimmers including leadingedge and trailing-edge. The IC achieves a high power factor and low total harmonic distortion (THD) and guarantees constant current accuracy to < $\pm$ 5% using Boundary Conduction Mode (BCM) operation. The TS19320CS has built-in protection circuits such as gate voltage clamping, over temperature protection by current degeneration, V<sub>CC</sub> overvoltage protection and system output open/short circuit protection.

#### FEATURES

- Constant current accuracy <±5%
- Flyback or Buck-Boost w/o photocoupler
- Good dimmer compatibility for 120/230V<sub>AC</sub> Lamps
- Boundary-mode PFC operation
- Built-in active power factor correction
- High voltage (500V) startup circuit
- Open-LED demagnetization (DMG) protection
- V<sub>CC</sub> over-voltage protection (OVP)
- Over-temperature protection (OTP)
- Shorted-LED Protection
- Cycle-by-cycle current limit
- Gate drive voltage clamping
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC.
- Halogen-free according to IEC 61249-2-21


# APPLICATION

- LED lighting
  - Down lights, Tube lamps, PAR Lamps, Bulbs


Pin Definit	ion:
1. HV	8. GND
2. RT	7. OUT
3. CS	6. V <sub>CC</sub>
4. COM	5. DMG

Notes: MSL 3 (Moisture Sensitivity Level) per J-STD-020

# TYPICAL APPLICATION CIRCUIT



Flyback Converter



Buck-Boost Converter




TS19320CS Taiwan Semiconductor

PARAMETER	SYMBOL	LIMIT	UNIT
HV Pin Voltage to GND	V <sub>HV</sub>	600	V
Power Supply Pin	V <sub>cc</sub>	40	V
DMG voltage to GND	V <sub>DMG</sub>	-0.3 to 40	V
OUT voltage to GND	V <sub>OUT</sub>	-0.3 to 40	V
RT voltage to GND	V <sub>CS</sub>	-0.3 to 5.5	V
CS voltage to GND	V <sub>CS</sub>	-0.3 to 5.5	V
COM voltage to GND	V <sub>COM</sub>	-0.3 to 5.5	V
Junction Temperature Range	TJ	-40 to +150	°C
Storage Temperature Range	T <sub>STG</sub>	-65 to +150	°C
Lead Temperature (Soldering 10 sec)	T <sub>LEAD</sub>	260	°C
Power Dissipation @ T <sub>A</sub> =50 °C	P <sub>D</sub>	0.4	W
ESD Rating (Human Body Mode) (Note 2)	НВМ	2	kV
ESD Rating (Machine Mode) (Note 2)	MM	200	V

THERMAL PERFORMANCE (Note 3)			
PARAMETER	SYMBOL	LIMIT	UNIT
Thermal Resistance Junction to Ambient	R <sub>eja</sub>	160	°C/W

<b>RECOMMENDED OPERATING CONDITION</b> (T <sub>A</sub> = 25°C unless otherwise specified) (Note 4)			
PARAMETER	SYMBOL	LIMIT	UNIT
HV Pin Voltage to GND	V <sub>HV</sub>	-0.3 to 450	V
Power Supply Pin	V <sub>cc</sub>	33	V
DMG voltage to GND	V <sub>DMG</sub>	-0.3 to 10	V
OUT voltage to GND	V <sub>OUT</sub>	-0.3 to 13	V
RT voltage to GND	V <sub>CS</sub>	-0.3 to 5	V
CS voltage to GND	V <sub>CS</sub>	-0.3 to 5	V
COM voltage to GND	V <sub>COM</sub>	-0.3 to 5	V
Operating Junction Temperature Range	TJ	-40 to +150	°C
Operating Ambient Temperature Range	T <sub>OPA</sub>	-40 to +85	°C





Taiwan Semiconductor

PARAMETER	SYMBOL	CONDITION	MIN	TYP	MAX	UNIT
Supply Voltage						
Supply current from HV pin	I <sub>HV</sub>	V <sub>DC</sub> =120V 10µF@V <sub>CC</sub> Pin		2.4		mA
Turn-on Voltage	V <sub>CC_ON</sub>		14.3	15.3	16.3	V
Turn-off Voltage	V <sub>CC_OFF</sub>		7.3	7.8	8.3	V
Quiescent Current 1	I <sub>Q1</sub>	V <sub>CC</sub> =12V, @ V <sub>CC</sub> off		68	100	μA
Quiescent Current 2	I <sub>Q2</sub>	Start-up @ 4.5kHz		570	770	μA
Operation Supply Current	I <sub>CC</sub>			1.5	2.5	mA
Protection						
V <sub>CC</sub> voltage protection	V <sub>OVPA</sub>		32	33.5	35	V
Output voltage protection	V <sub>OVPS</sub>		9.5	10	10.5	V
CS limit voltage	V <sub>OCP</sub>		1.2	1.3	1.4	V
CS limit voltage (start-up)	V <sub>OCP_STR</sub>			0.4		V
Short circuit protection (Note 5)	V <sub>SCP</sub>			3.0		V
Oscillator			7	ı.		
Maximum on Time	t <sub>ON_MAX</sub>		14	15	16	μs
GM Amplifier						
Internal reference voltage	V <sub>REF</sub>		362.6	370	377.4	mV
Transconductance	G <sub>m</sub>			95		μA/V
Sink Current	I <sub>COMP_SINK</sub>			32		μA
Source Current	ICOMP_SOU			32		μA
Driver		·				
Dreneut veltage	V <sub>OH</sub>	I <sub>0</sub> = 10mA		0.68		V
Dropout voltage	V <sub>OL</sub>	I <sub>O</sub> = -10mA		0.18		V
Rise time	tr	V <sub>CC</sub> =20V, C <sub>O</sub> =1nF		60		ns
Fall time	t <sub>f</sub>	V <sub>CC</sub> =20V, C <sub>O</sub> =1nF		80		ns
Output clamp voltage	V <sub>O CLAMP</sub>			13	15	V
Leading edge blanking time (Note 5)	LEBt			0.5		ns
Thermal Section (Note 5, 6)		•				
Thermal Shutdown				120		°C

Note:

1. Stresses listed as the above "Absolute Maximum Ratings" may cause permanent damage to the device. Functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


- 2. Devices are ESD sensitive. Handling precautions are recommended.
- 3. Thermal resistance is specified with the component mounted on a test board in free air with low effective thermal conductivity at  $T_A=25^{\circ}C$ .
- 4. The device is not guaranteed to function outside its operating conditions.
- 5. Guaranteed by design.
- 6. Linear degeneration type.



# **ORDERING INFORMATION**

PART NO.	PACKAGE	PACKING
TS19320CS RLG	SOP-8	2,500pcs / 13"Reel

# **FUNCTION BLOCK**



# **PIN DESCRIPTION**

PIN NO.	NAME	FUNCTION
1	HV	Pull high to line voltage for startup
2	RT	Maximum on time setting
3	CS	Input current sense pin.
4	COM	Output pin of error amplifier.
5	DMG	Zero current demagnetization sensing.
6	Vcc	Power supply pin for all internal circuitry.
7	ΟυΤ	Power MOS output pin.
8	GND	Ground return for all internal circuitry.



# **CHARACTERISTICS CURVES**






Figure 6 -  $V_{\text{OCP}}$  vs. Junction Temperature



20

#### **APPLICATION INFORMATION**

#### **PSR Function Description**

As a constant current primary-side controller with phase-cut dimmable and PFC function for LED lighting applications, the controller operates in boundary conduction mode (BCM) with constant on-time based regulation designed to achieve high power factor performance. The TS19320 has built-in high voltage (500V) startup circuit,  $V_{CC}$  over voltage protection, open LED protection, short LED protection, over temperature protection, primary-side current limit, and gate clamp function.

The average output current can be expressed as below.

$$I_{OUT\_avg} = \frac{N_P}{N_S} \times \frac{0.370 * \eta}{2 \times R_S}$$

Where:

- I<sub>OUT\_avg</sub> is the average output current
- N<sub>P</sub> is the primary-side turn ratio
- N<sub>s</sub> is the secondary-side turn ratio
- $\bullet \quad \eta \text{ is the efficiency} \\$
- Rs is the sensing resistor connected between the MOSFET source and the GND

#### **Pin Definitions**

#### **HV** Pin

Connect this pin to positive terminal of bulk capacitor to provide the startup current for the controller during  $V_{CC_ON}$  trigger on before.

#### **RT Pin**

This pin is to program the maximum on time by connecting a resistor to ground. Reference formula as below.

$$T_{ON} = \frac{14\,\mu}{300k} \times \left(R_T - 100k\right) + 1\mu$$

#### CS Pin

MOSFET current signal sensing for multiplication and current limit setting function.

$$I_{CS(LIMIT)} = \frac{1.3}{R_{c}}$$

Where:

• I<sub>CS(LIMIT)</sub> is the input current sence

R<sub>s</sub> is the sensing resistor connected between the MOSFET source and GND

#### COM Pin

This is the output of the  $g_m$  amplifier. Connect with a suitable RC network to ground.

#### V<sub>cc</sub> Pin

Power supply for the controller during normal operation. The controller will start up when  $V_{CC}$  reaches 15.3V (typical) and will shut-down when  $V_{CC}$  voltage is below 7.8V (typical). A decoupling capacitor should be connected between the  $V_{CC}$  and GND pin as close as possible.

The TS19320 performs V<sub>CC</sub> over voltage protection though V<sub>CC</sub> pin. Once V<sub>CC</sub> pin exceeds in 33.5V, TS19320 turns off and latchs out the MOSFET switcher until V<sub>CC</sub> goes below V<sub>CC OFF</sub>.



### **APPLICATION INFORMATION**


#### Pin Definitions (Continue)

#### DMG

The Output voltage is reflected by the auxiliary winding ( $N_{AUX}$ ) voltage of fly-back transformer, the DMG pin can sense output information to depart from start up voltage ( $V_{O_{_{_{O}STR}}}$ ) and protect voltage ( $V_{O_{_{_{O}OVP}}}$ ).

When the DMG sense voltage under V<sub>O STR</sub>, the circuit will work on short circuit protection,  $f_{STR}=1/t_{STR}$ .

When the DMG sense voltage over  $V_{O_{OVP}}$ , the circuit will work on over voltage protection, it will latch out until  $V_{CC}$  goes below  $V_{CC_{OFF}}$ .



- V<sub>OVPS</sub> is the over voltage protection signal
- V<sub>O\_STR</sub> is the start-up timer
- N<sub>AUX</sub> is the number of auxiliary-winding turns
- N<sub>SEC</sub> is the number of secondary-winding turns

#### **OUT Pin**

Gate drive for external MOSFET switch and is built-in gate clamp function.

#### **GND** Pin

GND is the reference node of internal circuit.






# PACKAGE OUTLINE DIMENSIONS (Unit: Millimeters)

TAIWAN

MICONDUCTOR

**9**h

SOP-8







# Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.