

Features

- Universal Input 100~240VAC 50/60Hz
- IEC/EN/ANSI/AAMI ES 60601-1 (ED 3.1)
- EMC: IEC60601-1-2:2014(ED 4.0)
- Safety Approvals: cULus / UKCA / CB / PSE / FCC / CE / TUV / RoHS / REACH
- Means of Protection: 2 X MOPP
- Touch Current: < 100μA
- Single Output to 36W
- Regulated Output with Low Ripple Noise
- Safety Agency Requirements and EMI/EMS Certified
- Meets DoE Level VI, Energy Star, ErP Stage 2
- No Load Power Consumption Less Than 0.075W
- IEC C14 Connector
- Dimensions: L 100 x W 50 x H 33 (mm)
- Weight: 210g



The purpose of the document is to specify a Single-phase AC input, single output switching power supply. This specification is for: Desktop Power Supplies 25W~36W Series. This product is suitable for use in medical applications. This Specification defines the input, output, performance characteristics, environment, noise and safety requirements.

| Models | | | |
|----------------|----------------|----------------|--------------|
| Model Number | Output Voltage | Output Current | Output Power |
| 44ATM036T-P050 | 5V DC | 5A | 25W |
| 44ATM036T-P090 | 9V DC | 4A | 36W |
| 44ATM036T-P120 | 12V DC | 3A | 36W |
| 44ATM036T-P180 | 18V DC | 2A | 36W |
| 44ATM036T-P240 | 24V DC | 1.5A | 36W |

General Specification

| Туре | Switched Mode Power Supply |
|-------------------------|--|
| Input Connector | IEC 320-C14 |
| Output Connection | 2.5x5.5x11.0mm +ve inner/centre |
| Number of Outputs | 1 |
| Energy Efficiency Level | VI |
| Mounting Style | Desktop |
| MTBF | 300,000 hours calculated at 25°C, by Telcoria SR-332 |
| Power Indicator | LED Indicator for power on |
| Cable Length | 1500mm(±30mm) |
| Cable Type | 16AWG/18AWG/20AWG (Depending on model) |
| Medical Approved | Yes |



44ATM036T-P 36W Desktop Series

Mechanical Specifications

| Housing Material | Fully Enclosed Plastic Case |
|--------------------|-----------------------------|
| Overall Dimensions | 100mm x 50mm x 33mm |
| Overall Length | 100mm |
| Overall Depth | 50mm |
| Overall Width | 33mm |
| Weight | 210g |

Input Specifications

| Rated Input Voltage | 100~240Vac (±10%) |
|---------------------|---|
| Rated Frequency | 50/60Hz |
| Efficiency Level VI | Level VI / Efficiency (EU) 2019/1782 |
| Input Current | 1.0A-0.45A |
| Inrush Current | 70A Max. / 230Vac (Cold Start At 25°C, Full Load) |
| Touch Current | Less than 100μA |
| Input Protection | Internal Primary Current Fuse |

Output Specifications

| Output Regulation | ±5% |
|---------------------------|---|
| Ripple & Noise (max.) | 2% Vp-p Max. for Output Voltage @ Full Load |
| Voltage Tolerance | ±5% |
| Load Regulation | ±5% |
| No Load Power Consumption | <0.075W |
| Hold-up Time | 10mS @ Full Load |
| Transient Response | 0.5mS for 50% Load Change(Typical) |
| Number of Outputs | 1 |
| Insulation Class | 1 |
| Dielectric Strength | Primary to Secondary 4,000Vac for 1 Minutes |
| Isolation Resistance | 10MΩ for 500Vdc |
| Over Circuit Protection | Auto-recovery |
| Over Voltage Protection | V out * 200% MAX., latch off |
| Over Current Protection | I out * 200% MAX., auto-recovery |

Protection Category

| Means of Protection | 2 X MOPP | | |
|---------------------|----------|--|--|

Approvals

| Compliance/Certifications | CB / cULus/ FCC / CE / UKCA / T-mark / TUV / PSE | |
|---------------------------|--|--|
| Safety Standard | IEC/EN/ANSI/AAMI ES 60601-1 | |
| EMC Emission: | Directive 93/42/EEC (EN 60601-1-2) | |



