

SPECIFICATION FOR APPROVAL

CUSTOMER

DESCRIPTION

DC BRUSHLESS FAN

DIMENSIONS

60X60X25 mm

MODEL

KD1206PTS2

P/N

 \mathbf{H}

APPROVED NO

APPROVED BY

(AUTHORIZED)

Chiahui 1/15 CHKD. CHKD. APPD. MINISTER DATE 01.15.2001 EDITION 0 REVISE DATE E.SPEC ED60219

建準電機工業股份有限公司

DAWN.

SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.

12FL., 120 CHUNG CHENG 1ST RD.,

TEL:886-7-7163069(41 LINES)

KAOHSIUNG, TAIWAN, R. O. C. FAX:886-7-7163086~89

DC BRUSHLESS FAN

MODEL: KD1206PTS2

P/N : H

CHARACTERISTICS

1. Motor Design

Patented single-coil DC brushless 4 poles motor

design.

2. Insulation Resistance

More than 500M ohm between internal stator and

lead wire(+) measured by DC 500V.

3. Dielectric Strength

Applied AC 500V for one minute or AC 600V for

2 seconds between housing and lead wire(+)

4. Noise Level

Measured in an semi-anechoic chamber

with background noise level below 15

dB(A). The fan is running in free air with

microphone at a distance of one meter

from the fan intake.

5. Input power, Current & Speed

Measured after continuous 30 minutes

operation at rated voltage in clean air

at ambient temperature of 25 degrees C.

6. Tolerances

±15% on rated power and current.

7. Motor Protection

Locked rotor protected.

8. Air Performance

Measured by a double chamber. The value

are recorded when the fan speed is stabilized

at rated voltage.

建準電機工業股份有限公司	SPEC.NO	D
•	ISSUE DATE	01.
MACHINE INDUSTRY CO., LTD.	PAGE	2

TOCKITE TO A TOTAL OF THE TOTAL	.2
ISSUE DATE 01. 15. 2001 E D I T I ON OF 4-	三
PAGE 2 OF 6 製打	书

SPECIFICATIONS

MODEL: KD1206PTS2

P/N : H

1-1. Rated Voltage : 12 VDC

1-2. Operating Voltage Range : 5-13.8 VDC

1-3. Starting Voltage : 5 VDC

1-4. Rated Speed : $3700 \text{ RPM} \pm 400 \text{ RPM}$

1-5. Air Delivery : 18 CFM

1-6. Static Pressure : 0.15 Inch-H2O

1-7. Rated Current : 0.11 AMP

1-8. Rated Power : 1.3 WATTS

1-9. Noise Level : 29 dB(A)

1-10. Direction of Rotation : Counter-clockwise viewed front fan blade

1-11. Operating Temperature : -10 to +70 Deg.C

1-12. Storage Temperature : -40 to +70 Deg.C

1-13. Bearing System : Lubricated sleeve bearing system

1-14. Weight : 59 g

1-15. Safety : UL/CSA/TUV/CE Approvals

1-16. Vibration : Vibration of acceleration 1.5G and

Frequency 5~50~5Hz is applied in the

3 directions(X,Y,Z) for 30 minutes, each

Direction at the cycle of 1 ming


				广 参析 银 二十
建準電機工業股份有限公司	SPEC.NO	D601066	REVISE DAT	E 90.22
SUNONWEALTH ELECTRIC	ISSUE DATE	01. 15. 2001	EDITIO	NOX仁音
MACHINE INDUSTRY CO., LTD.	PAGE	3 OF 6		(教行子)

MODEL: KD1206PTS2

P/N: H

PERFORMANCE CURVES

STATIC PRESSURE



建準電機工業股份有限公司
SUNONWEALTH ELECTRIC
MACHINE INDUSTRY CO., LTD.

SPEC.NO	D601066	REVISE
ISSUE DATE	01. 15. 2001	EDIT
PAGE	4 OF 6	

MATERIAL


2-1. Frame : Thermoplastic PBT of UL 94V-0

2-2. Impeller : Thermoplastic PBT of UL 94V-0

2-3. Bobbin : Thermoplastic PBT of UL 94V-0

2-4. Lead Wire : UL1007,26AWG,+RED;-BLACK

DIMENSIONS



Air Flow Direction: Label side.

			UNITS: mm
		•	· · · · · · · · · · · · · · · · · · ·
 			大人 大人 股

建準電機工業股份有限公司	SPEC.NO	D601066	REVISE D	(TE
	ISSUE DATE	01. 15. 2001	EDITI	O N
MACHINE INDUSTRY CO., LTD.	PAGE	5 OF 6		-

Notes |-

- 1. SUNON will not guarantee the products if the application of our products is exceeded the limitation which is specified on this specification.
- 2. In case of change of the specification specified on this document, a written notice is requested in advance.
- 3. Please do not touch the impeller with pressure and never bring the fan with lead wire. The bearings and lead wire may be damaged.
- 4. No guarantee on the products against the safety problem or failure caused by powder dust, drop of water or insect.
- 5. If there is any data or related documentation different from this data sheet, this data sheet is the principal reference.
- 6. For the purpose of MIS, please indicate SPEC No. on every order.
- 7. In case of the fan has no polarity protection function, wires with same color (electrode) must be connected together during the assembly. (i.e. red + red, black + black) or the fan will be damaged immediately.
- 8. Please do not use the fan in the environment of corrosive gas or liquid or any detrimental gas.
- 9. Please do not store the fan in the environment of high / low temperature, high humidity or any detrimental gas. Please store the fan within 6 months, every 6 months, there shall be a linkage of electric current to the fan, even though the fan is stored in room temperature.
- 10. While the fan is in operation, please do not lock the fan intentionally for a long period of time, since the continuous stoppage will result in over-heat and damage of the fan.
- 11. During the installation of the fan, please pay substantial attention to possible noise cause by resonance vibration and vibration.
- 12. During the testing of the fan, please be sure to use finger guard to insure safety.
- 13. Unless otherwise specified, if there is any doubt in the judgement, the temperature and relative humidity range of environment will be take in according to the sandard temperature and condition as 25°C and 65%.

建準電機工業股份有限公司	SPEC.NO	D601066	REVISE DAGE
		01. 15. 2001	EDITION
MACHINE INDUSTRY CO., LTD.	PAGE	6 OF 6	