MPSA28, MPSA29

MPSA29 is a Preferred Device

Darlington Transistors

NPN Silicon

Features

• Pb–Free Packages are Available*

MAXIMUM RATINGS

Rating		Symbol	Value	Unit
Collector – Emitter Voltage	MPSA28 MPSA29	V _{CES}	80 100	Vdc
Collector – Base Voltage	MPSA28 MPSA29	V _{CBO}	80 100	Vdc
Emitter-Base Voltage		V _{EBO}	12	Vdc
Collector Current – Continuous	5	Ι _C	500	mAdc
Total Device Dissipation @ T_A Derate above 25°C	= 25°C	PD	625 5.0	mW mW/°C
Total Device Dissipation @ $T_C = 25^{\circ}C$ Derate above 25°C		P _D	1.5 12	W mW/°C
Operating and Storage Junctio Temperature Range	n	T _J , T _{stg}	-55 to +150	°C

THERMAL CHARACTERISTICS


Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Ambient	R_{\thetaJA}	200	°C/W
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	83.3	°C/W

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.




ON Semiconductor®

http://onsemi.com







WW = Work Week

= Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping
MPSA28	TO-92	5,000 Units/Box
MPSA28G	TO–92 (Pb–Free)	5,000 Units/Box
MPSA28RLRP	TO-92	2,000/Ammo Pack
MPSA28RLRPG	TO-92 (Pb-Free)	2,000/Ammo Pack
MPSA29	TO-92	5,000 Units/Box
MPSA29G	TO–92 (Pb–Free)	5,000 Units/Box
MPSA29RLRP	TO-92	2,000/Ammo Pack
MPSA29RLRPG	TO–92 (Pb–Free)	2,000/Ammo Pack

*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

Preferred devices are recommended choices for future use and best overall value.

MPSA28, MPSA29

ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}C$ unless otherwise noted)

Symbol	Min	Тур	Max	Unit
-	80 100			Vdc
-	80 100			Vdc
V _{(BR)EBO}	12	-	-	Vdc
			100 100	nAdc
-			500 500	nAdc
I _{EBO}	-	_	100	nAdc
÷				
h _{FE}	10,000 10,000			-
V _{CE(sat)}		0.7 0.8	1.2 1.5	Vdc
V _{BE(on)}	-	1.4	2.0	Vdc
		•	•	
fT	125	200	-	MHz
Cobo	-	5.0	8.0	pF
	8 V(BR)CES 8 V(BR)CBO 8 V(BR)CBO 9 V(BR)EBO 10 ICBO 11 ICBO 11 ICBO 12 ICES 13 ICES 14 ICES 15 ICES 16 ICES 17 ICES 17 ICES	$\begin{array}{c c c c c c c c c c c c c c c c c c c $	$\begin{array}{c c c c c c c c c c c c c c c c c c c $	$\begin{array}{c c c c c c c c c c c c c c c c c c c $

1. Pulse Test: Pulse Width \leq 300 µs, Duty Cycle \leq 2.0%. 2. f_T = h_{fe} • f_{test}.

MPSA28, MPSA29






Figure 5. Active Region – Safe Operating Area



PACKAGE DIMENSIONS

TO-92 (TO-226) CASE 29-11 **ISSUE AL**







NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI 1. Y14.5M, 1982.
- 2
- TI4-3M, 1962. CONTROLLING DIMENSION: INCH. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED. LEAD DIMENSION IS UNCONTROLLED IN P AND 3.
- 4. BEYOND DIMENSION K MINIMUM.

	INCHES		MILLIN	MILLIMETERS	
DIM	MIN	MAX	MIN	MAX	
Α	0.175	0.205	4.45	5.20	
В	0.170	0.210	4.32	5.33	
С	0.125	0.165	3.18	4.19	
D	0.016	0.021	0.407	0.533	
G	0.045	0.055	1.15	1.39	
Η	0.095	0.105	2.42	2.66	
J	0.015	0.020	0.39	0.50	
Κ	0.500		12.70		
L	0.250		6.35		
Ν	0.080	0.105	2.04	2.66	
Ρ		0.100		2.54	
R	0.115		2.93		
۷	0.135		3.43		

STYLE 1: PIN 1. EMITTER

BASE 2. 3.

COLLECTOR

ON Semiconductor and 💷 are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT

Literature Distribution Center for ON Semiconductor P.O. Box 61312, Phoenix, Arizona 85082-1312 USA Phone: 480-829-7710 or 800-344-3860 Toll Free USA/Canada Fax: 480–829–7709 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center 2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051 Phone: 81-3-5773-3850

ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative.