

Fiber optic coupling - FOC-ADAPTER:SCD/SCD-OSA - 1208088

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fiber optic coupling, degree of protection: IP20, number of positions: 2, material: Plastic, connection method: Coupling, cable outlet: straight, color: green

Your advantages

- ✓ High reliability with comprehensive quality assurance measures
- ✓ Optimized precision (stability) with the use of ceramic sleeves
- ✓ Versatile range of applications with an extended temperature range and various mounting options
- ✓ Optimum compatibility with the FDX20 series splice boxes
- ✓ Future-proof with RoHS 2 conformity



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	6 pc
GTIN	 4 063151 277017
GTIN	4063151277017
Custom tariff number	85367000
Country of origin	China

Technical data

Mechanical characteristics

Connection method	Coupling
Number of slots	2
Insertion/withdrawal cycles	≥ 500
Number of positions	2
Cable outlet	straight

Fiber optic coupling - FOC-ADAPTER:SCD/SCD-OSA - 1208088

Technical data

Mechanical characteristics

Weight	9.04 g
Flammability rating according to UL 94	V0

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (assembly)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Material data

Housing material	Plastic
Width	34.7 mm
Height	9.4 mm
Length	27.4 mm

Standards and Regulations

Flame resistance	yes
Resistance to oil	no

Classifications

eCl@ss

eCl@ss 10.0.1	27440392
eCl@ss 11.0	27440390
eCl@ss 9.0	27440392

ETIM

ETIM 7.0	EC001121
----------	----------

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Fiber optic coupling - FOC-ADAPTER:SCD/SCD-OSA - 1208088

Approvals

EAC		B.01687
-----	-----------------------------------------------------------------------------------	---------