

SUNON

SPECIFICATION FOR APPROVAL

:	Sunon Inc.
:	MAGLev® Fan & Blower by SUNON
:	MagLev Motor Fan
:	12X12X3 mm
:	UF3C3-500
:	D01001051F-02
:	UF3C3-500 TC
:	
	:

								SPEC.NO	D01001051F-02	
	Alice-					ISSUE DATE	10.17.2018			
DRAWN	chang	CHECKED	Chin-jung	Chin-jung A	Chin-jung APPROV	APPROVED Chin-	APPROVED	• 8	EDITION	0
	10/17								REVISION DAT	Е
				E.SPEC	E30900399					
建準電	機工業股份	有限公司								
SUNON	WEALTH	I ELECT	RIC MACHI	NE INDU	STRY CO.,	LTD.				
NO. 30,	LN. 296, X	XINYA RI	D., QIANZHE	N DIST.,	TEL:88	86-7-8135888				
KAOH	KAOHSIUNG CITY 80673, TAIWAN (R.O.C) FAX:886-7-8230505/8230606/8231010									
URL:ht	URL:http://www.sunon.com E-mail: sunon@email.sunon.com.tw									

DC BRUSHLESS FAN MODEL : UF3C3-500

₩^{工業}後 D.C.C. [¬]

章

SUNON1

發行

CHARACTERISTICS

1. Motor Design	: Single phase, 6-poles Brushless DC motor.
2. Insulation Resistance	: More than 20M ohm between internal stator and
3 Dialastria Strongth	lead wire(+) measured at DC 100V.
3. Dielectric Strength	: Applied AC 500V for one minute or AC 600V for 2 seconds between housing and lead wire(+)
4. Noise Level	: Measured in a semi-anechoic chamber
	with background noise level below 15
	dB(A). The fan is running in free air with the
	microphone at a distance of 20 centimeter
	from the fan intake.
5. Input Power, Current & Speed	: Measured after continuous 10 minute
	operation at rated voltage in clean air, and
	at ambient temperature of 25 degrees C.
6. Tolerance	: +15% / -30% on rated power and current.
7. Air Performance	: Measured by a double chamber. The values
	are recorded when the fan speed has stabilized
	at rated voltage.
建準電機工業股份有限公司	SPEC.NO D01001051F-02 REVISION DATE


建準電機工業股份有限公司	SPEC.NO	D01001051F-02	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.17.2018	ΕΟΙΤΙΟΝ	0
MACHINE INDUSTRY CO., LTD.	PAGE	2 OF 12		

SPECIFICATIONS

MODEL : UF3C3-500

1-1. Rated Voltage	: 3 VDC					
C C						
1-2. Operating Voltage Range	: 2.0~3.5 VDC					
1-3. Starting Voltage	: 2.0 VDC (25 deg. C POWER ON/OFF)					
1-4. Rated Speed	: 16500 RPM ± 30%					
1-5. Air Delivery	: 5.95 l/min					
1-6. Static Pressure	: 18.91 Pa					
1-7. Rated Current	: 97 mA					
1-8. Rated Power	: 0.3 WATTS					
1-9. Noise Level	: 14.0 dB(A) @ 1M 28.3 dB(A) @ 0.2M					
1-10. Direction of Rotation	: Counter-clockwise viewed from front of fan blade					
1-11. Operating Temperature	: -10 to +70 deg. C					
1-12. Storage Temperature	: -40 to +70 deg. C					
1-13. Bearing System	: Vapo bearing system					
1-14. Weight	: 0.7 g					
1-15. Safety	: CE Approvals					
1-16. Protection	: ☑Automatic Restart Capability Note: In a situation where the fan is locked by an external force while the electricity is on, an increase in coil temperature will be prevented by temporarily turning off the electrical power to the motor. The fan will automatically restart when the locked rotor condition is released. ☑Polarity Protection					
1-17. IP Class : IP55	 According to IEC 60529 (or IEC 34-5) IP standard, the average temperature is 23~24°C and humidity is 67% RH for Dust Water Test. The fan needs to be test and Spray Put in dust box for 8 hours for Dust Test and be sprayed low pressure jets of water from all directions for Spray Water Test. After these 2 tests, which executing by regular standard, the fan will be measured the performance is normal or not. PS. There are different applicative environments and systems by different customers, so please put the product in the most suitable environment to measure the performances. 					
建準電機工業股份有限公司	SPEC.NO D01001051F-02 REVISION DATE					
SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.	ISSUE DATE 10.17.2018 E D I T I O N 0					
The moost co., LID.	PAGE 3 OF 12					

<u>D.C.C.</u> SUENON1 發行章




MATERIAL

2-1. Frame:Thermoplastic LCP of UL 94V-02-2. Impeller:Thermoplastic LCP of UL 94V-02-3. Lead Wire:UL10064,32 awg,+RED,-BLACKUL10064,32 awg,YELLOW:3rd WireDIMENSIONSNote: SUNON recommends the screw and torque as below. P


Note: SUNON recommends the screw and torque as below. Please contact SUNON, if any new requirement is requested.

D.C.C.

Screw Type (Pan head)	Torque	Screw Spec		
	0.3~0.5 Kgf-cm	Size	Standard	
Machine screw		M1.4	JIS B1111-1974	



建準電機工業股份有限公司	SPEC.NO	D01001051F-02	REVISION DATE			
SUNONWEALTH ELECTRIC	ISSUE DATE	10.17.2018	ΕΟΙΤΙΟΝ	0		
MACHINE INDUSTRY CO., LTD.	PAGE	5 OF 12				



● D.C.C. SUNON1 發行章

D.C.C. 2018.) NO1 發 行 FAN 3rd WIRE SIGNAL F Type (Frequency Generator) USER SYSTEM F A N (+) \bigcirc Vcc V+Ιf Ra FG Output (-)Fan Operation Current Vн FG Output Voltage OFF RUN LOCKED

業(股

★Electrical Characteristics : (at Ta = 25° C, V_{CC}=3V)

Parameter		Ratings	Unit	
Farameter	min	typ.	max	Omt
FG Supply Voltage(V+)			3.5	Voltage
FG Output Current (If)			4	mA
FG Output (VL)			0.5	Voltage
FG Output (VH)		V+		Voltage

建準電機工業股份有限公司	SPEC.NO	D01001051F-02	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.17.2018	ΕΟΙΤΙΟΝ	0
MACHINE INDUSTRY CO., LTD.	PAGE	7 OF 12		

● **SUNON**1 發行章

Notes

I .SAFETY

- 1. DO NOT use or operate this fan in excess of the limitations set forth in this specification. SUNON is not responsible for the non-performance of this fan and/or any damages resulting from its use, if it is not used or operated in accordance with the specifications.
- 2. SUNON recommends adding a protection circuit to the product or application in which this fan is installed, such as a thermo-fuse, or current-fuse or thermo-protector. The failure to use such a device may result in smoke, fire, electric shock by insulation degradation in cases of motor lead short circuit, overload, or over voltage, and/or other failure.
- 3. SUNON recommends installing a protection device to the product or application in which this fan is installed if there is a possibility of reverse-connection between VDC (+) and GND (-). The failure to install such a device may result in smoke, fire, and/or destruction, although these conditions may not manifest immediately.
- 4. This fan must be installed and used in compliance with all applicable safety standards and regulations.
- 5. Use proper care when handling and/or installing this fan. Improper handling or installation of this fan may cause damage that could result in unsafe conditions.
- 6. Use proper care during installation and/or wiring. Failure to use proper care may cause damage to certain components of the fan including, but not limited to, the coil and lead wires, which could result in smoke and/or fire.
- 7. DO NOT use power or ground PWM to control the fan speed. If the fan speed needs to be adjusted, please contact SUNON to customize the product design for your application.
- 8. For critical or extreme environments, including non stop operation, please contact SUNON and we will gladly provide assistance with your product selection to ensure an appropriate cooling product for your application.

建準電機工業股份有限公司	SPEC.NO	D01001051F-02	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.17.2018	ΕΟΙΤΙΟΝ	0
MACHINE INDUSTRY CO., LTD.	PAGE	8 OF 12		

Notes



- 1. SUNON offers engineering assistance on fan installation and cooling system design.
- 2. All changes, modifications and/or revisions to the specifications, if any, are incorporated in the attached specifications.
- 3. No changes, modifications and/or revisions to these specifications are effective absent agreement, by both SUNON and the customer, in writing.
- 4. This fan will be shipped in accordance with the attached specification unless SUNON and the customer have agreed otherwise, in writing, as specified in Paragraph 3, above.

III. OTHER

- 1. When building your device, please examine thoroughly any variation of EMC, temperature rise, life data, quality, etc. of this product by shock/drop/vibration testing, etc. If there are any problems or accidents in connection with this product, it should be mutually discussed and examined.
- 2. Use proper care when handling this fan. Components such as fan holders or bearings may be damaged, if touched with fingers or other objects. Additionally, static electricity (ESD) may damage the internal circuits of the fan.
- **3.** DO NOT operate this fan in proximity to hazardous materials such as organic silicon, cyanogens, formalin, phenol, or corrosive gas environments including, but not limited to, H₂S, SO₂, NO₂, or Cl₂.
- 4. SUNON recommends that you protect this fan from exposure to outside elements such as dust, condensation, humidity or insects. Exposure of this fan to outside elements such as dust, condensation, humidity or insects may affect its performance and may cause safety hazards. SUNON does not warrant against damage to the product caused by outside elements.

Re: The term can be excluded, if the fan has been with IP design and meets customer's IP requirement.

建準電機工業股份有限公司	SPEC.NO	D01001051F-02	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.17.2018	ΕΟΙΤΙΟΝ	0
MACHINE INDUSTRY CO., LTD.	PAGE	9 OF 12		

Notes

- 5. This fan must be installed properly and securely. Improper mounting may cause harsh resonance, vibration, and noise.
- 6. Fan guards may prevent injury during handling or installation of the fan and are available for sale with this fan.
- 7. Unless otherwise noted, all testing of this fan is conducted at 25°C ambient temperature and sixty-five percent (65%) relative humidity.
- 8. DO NOT store this fan in an environment with high humidity. This fan must be stored in accordance with the attached specifications regarding storage temperature. If this fan is stored for more than 6 months, SUNON recommends functional testing before using.
- 9. SUNON reserves the right to use components from multiple sources at its discretion. The use of components from other sources will not affect the specifications as described herein.
- 10.The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy Test Reports (L10 and MTTF Report) that relate to this fan are only for reference.

VI. WARRANTY

This fan is warranted against all defects which are proved to be fault in our workmanship and material for one year from the date of our delivery. The sole responsibility under the warranty shall be limited to the repair of the fan or the replacement thereof, at SUNON's sole discretion. SUNON will not be responsible for the failures of its fans due to improper handing, misuse or the failure to follow specifications or instructions for use. In the event of warranty claim, the customer shall immediately notify SUNON for verification. SUNON will not be responsible for any consequential damage to the customer's equipment as a result of any fans proven to be defective.

建準電機工業股份有限公司	SPEC.NO	D01001051F-02	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.17.2018	ΕΟΙΤΙΟΝ	0
MACHINE INDUSTRY CO., LTD.	PAGE	10 OF 12		

Declaration of Restricted Materials

MACHINE INDUSTRY CO., LTD.

Control declaration of environment- related substances/ materials

1. In accordance with the Restriction of Hazardous Substances (RoHS) Directive 2011/65/EU and specific market requirements, Sunon Halogen-Free Product have complied with law and discipline not to employ the forbidden substances, and restrict the allowable concentration of some limited substances deliberately in our components.

D.C.C.

行

SUN0.N.01

發

No	Substance					Criteria	
1	CFCs & HCFCs (ozone depleting substances)					Forbidden	
2	Chlorinated Organic Solv	rent				Forbidden	
	~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~	Plastic (Frame, Impeller, wire harness, etc.)		<100ppm			
		Solder			<1000ppm		
3	Lead and its compounds	Steel alloy			<3500ppm		
		Aluminium alloy			<4000ppm		
		Copper alloy			<4wt%		
	Cadmium and its compounds	Solder			<20ppm		
4		Parts composed of metals containing zinc			<100ppm		
4		(e.g. brass, zinc for die casting)					
	-	Plastic			<5ppm		
5	PBBs and PBDEs					Forbidden	
6	PCB and PCT				Forbidden		
7	CP, Short-chain Chlorinated paraffins C10-13, Cl ≥48 wt%				Forbidden		
8	Mirex				Forbidden		
9	PCN					Forbidden	
10	Hexavalent Chromium compounds					<100ppm	
11	Mercury and its compounds				Forbidden		
12	Asbestos					Forbidden	
13	Organic Tin compounds					Forbidden	
14	Azo compounds					Forbidden	
15	TBBP-A in external case plastic parts of products (PCB is exempted)					<1000ppm	
16	Nickel in external case parts, which are likely to result in prolonged skin exposure					<1000ppm	
17	Hexabromocyclododecane (HBCDD)					<1000ppm	
18	Di-butyl Phthalate (DBP)					<1000ppm	
19	Benzyl butyl Phthalate (BBP)					<1000ppm	
20	Di-ethylhexyl Phthalate (DEHP)					<1000ppm	
21	Di-isobutyl Phthalate (DIBP)					<1000ppm	
22	Brominated/chlorinated flame retardants (other than PBBs or PBDEs),					Br<900ppm	
	applicatable item: frame, bobbin, impeller, lear wire, connector, mylar					Cl<900ppm	
	insulator.					Br+Cl<1500ppm	
22	PAHs and its 16 compounds in unusual contact material					BaP < 20ppm	
23						Total <200ppm	
	PCB and electroplating material, PFOS content complianced with 2006/122/EC					PFOS <u>&lt;</u> 1000ppm	
24						coating material	
						$PFOS \le 1 \mu g/m^2$	
			SPEC.NO	D01001051F-02	REVISIO		
NON	WEALTH ELECTRIC		<b>ISSUE DATE</b>	10.17.2018	EDIT	ΙΟΝ	0

PAGE

11 OF 12

