UbiBot®Wireless Muti-Sensor Device Series



Soil Temp & Moisture Probe

The soil temperature and moisture probe measures soil moisture content based on frequency domain reflection method. It can connect with WS1 Pro and GS1 series. It is widely used in homes, offices, farms and other places where soil temperature and moisture need to be measured.

Technical specifications Measuring Temperature Bang

Measuring Temperature Range $:-40^{\circ}C \sim 85^{\circ}C$ Measuring Moisture Range $:0 \sim 100\%$ Accuracy $:<\pm 0.4^{\circ}C$ $\pm 3\% (0-50\%) ; \pm 5\% (>50\%)$

Connector : Micro USB, 3.5mm Audio Measuring Theory : Frequency Domain (FDR) Output Interface : RS485 Communications Protocol : Modbus

Physical specifications

Materials : ABS + Stainless steel Steel Point Length : 80mm Cable Length : 3 meters

Working Voltage ∶ DC 5-12V Standby Current : ≤20mA