## Harvatek Surface Mount Phototransistor Data Sheet B1501PT--H9C000213U1930

| Official Product  | HT Part No. B1501PTH9C000213U1930 | Customer Part No. | Data Sheet No. |           |
|---|-----------------------------------|-------------------|----------------|-----------|
| Tentative Product   | *****                             | ****              | -              |           |
| Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved. |                                   | 01/03/2019        | Version 1.4    | Page 1/14 |

| DISCLAIMER   | 3  |
|--|----|
| LIFE SUPPORT POLICY  | 3  |
| PRODUCT SPECIFICATIONS   | 4  |
| ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION                    | 4  |
| LABEL SPECIFICATIONS   | 5  |
| ELECTRICAL OPTICAL CHARACTERISTICS                                     | 6  |
| PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW |    |
| Soldering  | 7  |
| CHARACTERISTICS OF B1501PT   | 8  |
| PACKAGING  | 10 |
| TAPE DIMENSION   | 10 |
| REEL DIMENSION   | 11 |
| PACKING  | 11 |
| Dry Pack   | 12 |
| BAKING   | 12 |
| PRECAUTIONS  | 12 |
| REFLOW SOLDERING   | 13 |
| Reworking  | 13 |
| CLEANING   | 13 |
| CAUTIONS OF PICK AND PLACE   | 14 |
| Revise History   | 14 |

| Official Product  | HT Part No. B1501PTH9C000213U1930 | Customer Part No. | Data Sheet No. |           |
|---|-----------------------------------|-------------------|----------------|-----------|
| Tentative Product   | *****                             | *****             | -              |           |
| Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved. |                                   | 01/03/2019        | Version 1.4    | Page 2/14 |

#### DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

#### Life Support Policy

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.

2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

| Official Product  | HT Part No. B1501PTH9C000213U1930 | Customer Part No. | Data Sheet No. |           |
|---|-----------------------------------|-------------------|----------------|-----------|
| Tentative Product   | *****                             | ****              | -              |           |
| Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved. |                                   | 01/03/2019        | Version 1.4    | Page 3/14 |

#### **Product Specifications**

| Item                    | Specification  | Material                          | Quantity         |
|-------------------------|--|-----------------------------------|------------------|
| Spectral Bandwidth      | 400nm~1100nm   |                                   |                  |
| λ <sub>D</sub>          | @ V <sub>CE</sub> =5V / T <sub>S</sub> = 25 $^{\circ}$ C |                                   |                  |
| Peak Sensitivity        | 940nm  |                                   |                  |
| λ <sub>P</sub>          | @ V <sub>CE</sub> =5V / T <sub>S</sub> = 25 $^{\circ}$ C |                                   |                  |
| Collector Light Current | 0.1~0.8mA  |                                   |                  |
| Ic                      | $@E_e = 1mW/cm2;\lambda_P=940nm, V_{CE}=5V$              |                                   |                  |
| Resin                   | Clear  | Ероху                             |                  |
| Carrier tape            | EIA 481-1A specs   | Conductive black tape             | 4000ea/reel      |
| Reel                    | EIA 481-1A specs   | Conductive black                  |                  |
| Label                   | HT standard  | Paper                             |                  |
| Packing bag             | 220x240mm  | Aluminum laminated bag/ no-zipper | One reel per bag |
| Carton                  | HT standard  | Paper                             | Non-specified    |
| 01                      | -  |                                   |                  |

Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin

combinations of Iv, CIE and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

Note : This is shipped test conditions

%Remarks: This product should be operated in forward bias. If a reverse voltage is continuously applied to the product,

such operation can cause migration resulting in LED damage.

#### ATTENTION: Electrostatic Discharge (ESD) protection




The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlInGaP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must

be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.


| Official Product  | HT Part No. B1501PTH9C000213U1930 | Customer Part No. | Data Sheet No. |           |
|---|-----------------------------------|-------------------|----------------|-----------|
| Tentative Product   | ******                            | *****             | -              |           |
| Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved. |                                   | 01/03/2019        | Version 1.4    | Page 4/14 |

### **Label Specifications**



■Harvatek P/N:





#### Lot No.:

| 1            | 2          | 3         | 4              | 5         | 6         | 7         | 8      | 9           | 10      |  |
|--------------|------------|-----------|----------------|-----------|-----------|-----------|--------|-------------|---------|--|
| E            | 1          | Α         | 1              | Α         | 2         | 2         | L      | 1           | 2       |  |
| Cod          | e 1 2      | Code 3    | Code 4         | Code 5    | Code 6    | Code 7    | Code 8 | Code 9      | Code 10 |  |
|              |            | Mfg. Year | Mfg. Month     | Mfg. Date | Consecuti | ve number | 1      | Special cod | e       |  |
|              |            | 2010-A    |                | 1:A       |           |           |        |             |         |  |
|              |            | 2011-B    |                | 2:B       |           |           |        |             |         |  |
|              |            | 2012-C    | 1:Jan.         | 3:C       |           |           |        |             |         |  |
|              |            |           | 2:Feb.         |           |           |           |        |             |         |  |
| Internal Tre | aning Code | 2018-I/J  |                | 26:Z      | 01.       | -ZZ       |        | 000~ZZZ     |         |  |
| internal ina | acing Code | 2019-K    | A:Oct.         | 27:7      | 01-       | -22       |        | 000~222     |         |  |
|              |            |           | B:Nov.         | 28:8      |           |           |        |             |         |  |
|              | 2022-N     | C:Dec.    | 29:9           |           |           |           |        |             |         |  |
|              |            | 2023-P    | 12160303034834 | 30:3      |           |           |        |             |         |  |
|              |            | 200       |                | 31:4      |           |           |        |             |         |  |

| Official Product  | HT Part No. B1501PTH9C000213U1930 | Customer Part No. | Data She    | et No.    |
|---|-----------------------------------|-------------------|-------------|-----------|
| Tentative Product   | *****                             | ****              | -           |           |
| Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved. |                                   | 01/03/2019        | Version 1.4 | Page 5/14 |

### Absolute Maximum Rating at 25℃

| Symbol           | Parameters                | Ratings    | Units | Notes |
|------------------|---------------------------|------------|-------|-------|
| V <sub>CEO</sub> | Collector-Emitter Voltage | 30         | V     |       |
| V <sub>ECO</sub> | Emitter-Collector Voltage | 5          | V     |       |
| Ι <sub>C</sub>   | Collector Current         | 20         | mA    |       |
| T <sub>opr</sub> | Operating Temperature     | -40 ~ +85  | °C    |       |
| T <sub>stg</sub> | Storage Temperature       | -40 ~ +100 | °C    |       |
| T <sub>sol</sub> | Soldering Temperature     | 260        | °C    | 1     |

#### Notes:

1. Soldering time  $\leq$  5 seconds.

### **Electrical Optical Characteristics**

| Symbol               | Parameters                              | Test conditions   | Min | Тур | Max  | Units | Notes |
|----------------------|---|---|-----|-----|------|-------|-------|
| λ <sub>0.5</sub>     | Range Of Spectral Bandwidth             |   | 400 | -   | 1100 | nm    |       |
| λ <sub>P</sub>       | Wavelength Of Peak Sensitivity          |   | -   | 940 | -    | nm    |       |
| BV <sub>CEO</sub>    | Collector-Emitter Breakdown<br>Voltage  | I <sub>C</sub> =100µA<br>E <sub>e</sub> =0mW/cm²                      | 30  | -   | -    | V     |       |
| BV <sub>ECO</sub>    | Emitter-Collector Breakdown<br>Voltage  | I <sub>E</sub> =100μA<br>E <sub>e</sub> =0mW/cm²                      | 5   | -   | -    | V     |       |
| V <sub>CE(sat)</sub> | Collector-Emitter Saturation<br>Voltage | I <sub>C</sub> =2mA<br>E <sub>e</sub> =1mW/cm²                        | -   | -   | 0.4  | V     |       |
| I <sub>CEO</sub>     | Collector Dark Current                  | V <sub>CE</sub> =20V<br>E <sub>e</sub> =0mW/cm²                       | -   | -   | 100  | nA    |       |
| I <sub>C(ON)</sub>   | On State Collector Current              | $E_e$ =1mW/cm <sup>2</sup><br>$\lambda_P$ =940nm, V <sub>CE</sub> =5V | 0.1 | 0.5 | -    | mA    | 2     |
| t <sub>r</sub>       | Rise Time                               | V <sub>CE</sub> =5V, I <sub>C</sub> =1mA                              | -   | 15  | -    | μS    | 2     |
| t <sub>f</sub>       | Fall Time                               | $R_L=1000\Omega$  | -   | 15  | -    | μS    | 3     |

#### Notes:


2. Ic Bin Rank : :

| Bin Code | B1  |
|----------|-----|
| Min      | 0.1 |
| Max      | 0.8 |


| Official Product  | HT Part No. B1501PTH9C000213U1930 | Customer Part No. | Data She    | et No.    |
|---|-----------------------------------|-------------------|-------------|-----------|
| Tentative Product   | *****                             | ****              | -           |           |
| Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved. |                                   | 01/03/2019        | Version 1.4 | Page 6/14 |

#### Notes:

3. Test circuit : :




### Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering



(Unit: mm Tolerance: +/-0.1)

| Official Product  | HT Part No. B1501PTH9C000213U1930   | Customer Part No. | Data Sheet No. |           |
|-------------------|---|-------------------|----------------|-----------|
| Tentative Product | *****   | ****              |                | -         |
| , ,               | ct to changes for improvement without ry data, drawings, company confidential all | 01/03/2019        | Version 1.4    | Page 7/14 |

### **Characteristics of B1501PT**




| Official Product HT Par  | art No. B1501PTH9C000213U1930   | Customer Part No. | Data Sheet No. |           |
|--------------------------|---|-------------------|----------------|-----------|
| Tentative Product ****** | *******   | ****              |                | -         |
|                          | changes for improvement without<br>, drawings, company confidential all | 01/03/2019        | Version 1.4    | Page 8/14 |

#### Precaution for Use


- 1. The chips should not be used directly in any type of fluid such as water, oil, organic solvent, etc.
- 2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
- 3. LEDs must be stored in a clean environment. A sealed container with a nitrogen atmosphere is necessary if the storage period is over 3 months after shipping.
- 4. The LEDs must be used within 4 weeks after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
- 5. The appearance and specifications of the products may be modified for improvement without further notice.
- 6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs.If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs.Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.

| Official Product  | HT Part No. B1501PTH9C000213U1930   | Customer Part No. | Data Sheet No. |           |
|-------------------|---|-------------------|----------------|-----------|
| Tentative Product | *****   | ****              |                | -         |
|                   | ct to changes for improvement without ry data, drawings, company confidential all | 01/03/2019        | Version 1.4    | Page 9/14 |

## Packaging Tape Dimension




| Dim. A    | Dim. B    | Dim. C    | Q'ty/Reel |
|-----------|-----------|-----------|-----------|
| 3.50±0.05 | 1.88±0.05 | 1.27±0.05 | ЗK        |
|           |           |           | Unit: mm  |



| Official Product  | HT Part No. B1501PTH9C000213U1930 | Customer Part No. | Data Sheet No. |            |
|---|-----------------------------------|-------------------|----------------|------------|
| Tentative Product   | *****                             | ****              |                | -          |
| Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved. |                                   | 01/03/2019        | Version 1.4    | Page 10/14 |

### **Reel Dimension**



### 5 or 10 boxes per carton is available depending on shipment quantity.


| Official Product H  | IT Part No. B1501PTH9C000213U1930   | Customer Part No. | Data Sheet No. |            |
|---------------------|---|-------------------|----------------|------------|
| Tentative Product * | *****   | ****              |                | -          |
|                     | to changes for improvement without data, drawings, company confidential all | 01/03/2019        | Version 1.4    | Page 11/14 |

### **Dry Pack**

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

A humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



## Baking

Baking before soldering is recommended when the package has been unsealed for 4 weeks. The conditions are as followings:

- 1.  $60\pm3^{\circ}C\times(12\sim24hrs)$  and <5% RH, taped reel type.
- 2. 100±3°C×(45min~1hr), bulk type.
- 3. 130±3°C ×(15min~30min), bulk type.

### Precautions

- 1. Avoid exposure to moisture at all times during transportation or storage.
- 2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlInGaP products.
- 3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
- 4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
- 5. Avoid direct contact with the surface through which the LED emits light.
- 6. If possible, assemble the unit in a clean room or dust-free environment.


| Official Product  | HT Part No. B1501PTH9C000213U1930   | Customer Part No. | Data Sheet No. |            |
|-------------------|---|-------------------|----------------|------------|
| Tentative Product | ******  | ****              |                | -          |
|                   | ct to changes for improvement without ry data, drawings, company confidential all | 01/03/2019        | Version 1.4    | Page 12/14 |

### **Reflow Soldering**

Recommend soldering paste specifications:

- 1. Operating temp.: Above 220°C ,60sec
- 2. Peak temp.:260°C Max.,10sec Max.
- 3. Reflow soldering should not be done more than two times.
- 4. Never take next process until the component is cooled down to room temperature after reflow.
- 5. The recommended reflow soldering profile (measuring on the surface of the LED terminal) is following:

Lead-free Solder Profile



### Reworking

- Rework should be completed within 5 seconds under  $260^{\circ}$ C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

## Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50  $^\circ\!\mathrm{C}\,$  x 30sec. or <30  $^\circ\!\mathrm{C}\,$  x 3min
- Ultra sonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100°C max, <3min

| Official Product  | HT Part No. B1501PTH9C000213U1930   | Customer Part No. | Data Sheet No. |            |
|-------------------|---|-------------------|----------------|------------|
| Tentative Product | ******  | *****             |                | -          |
|                   | ct to changes for improvement without ry data, drawings, company confidential all | 01/03/2019        | Version 1.4    | Page 13/14 |

### **Cautions of Pick and Place**

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

#### **Revise History**

| Rev. | Descriptions   | Date       | Page |
|------|--|------------|------|
| 1.0  | -  | 05/19/2017 | -    |
| 1.1  | Packing Update   | 07/26/2017 | 11   |
| 1.2  | V <sub>CE(sat)</sub> Test conditions & Characteristics | 10/05/2017 | 6&8  |
| 1.3  | CHIP LEDs >> Phototransistor / Revise item name        | 12/29/2017 | 1&5  |
| 1.4  | Revise the resin color                                 | 01/03/2019 |      |
|      |  |            |      |
|      |  |            |      |
|      |  |            |      |
|      |  |            |      |
|      |  |            |      |
|      |  |            |      |
|      |  |            |      |
|      |  |            |      |
|      |  |            |      |
|      |  |            |      |
|      |  |            |      |
|      |  |            |      |

| Official Product  | HT Part No. B1501PTH9C000213U1930   | Customer Part No. | Data Sheet No. |            |
|-------------------|---|-------------------|----------------|------------|
| Tentative Product | *****   | ****              |                | -          |
|                   | ct to changes for improvement without ry data, drawings, company confidential all | 01/03/2019        | Version 1.4    | Page 14/14 |