BLAZAR BE3-RMW Accelerator Engine IC Intelligent In-Memory Computing

1Gb Memory

PRODUCT BRIEF: MSR830

Acceleration Engines Give Software and Hardware System Architects Acceleration Options not Previously Available

Bandwidth Engine (BE) Overview

The **BLAZAR Family of Accelerator Engines** are high capacity, high-speed memories that support high bandwidth, fast random memory access rates and includes optional *embedded In-Memory Eunctions (IMF)* that solve critical memory access challenges for memory bottlenecked applications like network search, statistics, buffering, security, firewall, 8k video, anomaly detect, genomics, ML random forest of trees, graph walking, traffic monitoring, AI and IoT.

All Accelerator Engines have two ways to be uses in a system:

- 1. As a standard parallel like QDR, SyncSRAM or RLDram
- 2. As a high density, high bandwidth memory with Optional In-Memory Acceleration Functions

Both modes are independent. You do not have to use the In-Memory functions if they are not useful in your application. In that case, you would use the Accelerator Engine like any other memory.

Base Features: The Bandwidth Engine 3	
RMW (BE3-RMW)	

- 1Gb of tRC of 2.7ns memory
 Replaces 8 QDR type memories
- Replaces 8 QDR type memo
 In-Memory BURST functions
- In-Memory RMW functions
- RTL Memory Controller

loSys

Key Features - Memory

- 1 Gb SRAM (16M x 72b)
 - User defined WORD width
 - Typical 8x, 16x, 32x, 36x, ... 72x
- High Bandwidth, low pin count serial interface
 - Highly efficient reliable transport command and data protocol optimized for 90% efficiency
 - Eases board layout and signal integrity, minimal trace length matching required, operates over connectors
 - Reduction of I/O pins from 5x to 45x depending on equivalent memory density and type
- High access rate SRAM class memory
 - Up to 6.5 Billion transactions/sec
 - o 2.7 ns tRC
- Highest Single Chip Bandwidth up to 640 Gb/s throughput (320 full duplex)

Applications Focus

- Slower speed applications needing high capacity
- SRAM with high capacity and high speed
- High bandwidth data access application where low latency and movement of data is a critical
- Applications that use base level compute or decisions functions
- FPGA Acceleration for Xilinx and Intel

Key Features – In-Memory Functions

• The Acceleration function are optional and do not impact the device used as a memory only

BURST In-Memory Function

- For sequential Read or Write functions for_data movement
- Burst length: 1, 2, 4 or 8 words
- Can double or triple QDR bandwidth

RMW In-Memory Function

- RMW are Read/Modify/Write functions
- Includes may functions for compute and decision
- Examples: ADD, SUB, Compare, INC plus 15 other functions
- Increases execution speed and bandwidth

MoSys Accelerator Engine Elements of BE3-RMW

MoSys Engines have a Unique Memory Architecture that can replace SyncRAM/RLDRAM memories and <u>Embeds In</u> <u>Memory Functions (IMF)</u> that execute many times faster. A single function replaces many traditional memory accesses.





Bandwidth Engine Device Key Features

High Speed Serial I/O

- GCI serial I/O versions of 10 and 12.5 Gbps for high bandwidth (up to 320 Gbps)
- Has two, full duplex 8 lane ports that operate independently
- Typical system only used 8 lanes
- Device can operate with a minimum of 4 lanes
- Reduces number of signal pins over traditional memories, increases signal integrity allowing longer board traces to ease board signal routing
- Operates across connectors
- 1Gb
 - 4 partitions/128 banks
 - o 16 READ and 16
 - WRITE ports
- 2.7 ns tRC at 25Gbps
- Allows parallel partition
 and bank execution
- Bandwidth 640 Gbps (320 Gbps full duplex)
- Up to 6.5 B access/sec



Memory/Function Controller

- Directs read/write function to selected bank of memory
- Manages the sequence of In-Memory functions
- BURST–Sequential read or writes
- Up to 8 read or writes
 RMW–
 - 4-8x reduction in RMW accesses
- o Insures no stale data
- ALU (mutec)
- Embedded RMW Functions utilize ALUs for in memory computational functions
 - There are 16 ALUsSimultaneous
 - operations

Result Reordering

 Reorder buffers handle simultaneous memory access ensure that results are returned to the output of the submitted input port

Common Key Features for Bandwidth Engines (BE2 & BE3)

- High capacity High-Speed Memory on a single device
 - o BE2 576Mb
 - o BE3 1Gb

High speed tRC access

- o BE2 with 3.2ns
- o BE3 with 2.7ns

Achieve the highest bandwidth possible

- Use of serial interface with high efficiency GCI protocol
- o BE2 with 3.3B access per sec
- $\circ~$ BE3 with 6.5B accesses per sec
- Reduce number of interface pins compared to other memories
 - Typical system uses 8 lanes or 32 pins
 - Highest bandwidth uses 16 lanes or 64 pins
 - Minimum use of 4 lanes on one port or 16 pins

- Eliminate external components required for signal integrity
 - On device Auto-Adaption to eliminate external signal conditioning board components
 - Signals will work over a backplane
- Make the interface like a parallel QDR
 - MoSys supplies an RTL memory controller that handles the memory and serial interface
 - Serial device interface is transparent to user
 - Provides a parallel QDR like Read/Write RTL interface
- Make interface easily adapted to an AXI or Avalon bus
 - o Minimal RTL logic required

SUMMARY OF BENEFITS

- Capacity ... 1Gb memory ... Replaces 8
 QDR/SyncSRAM devices
- Costs ... One BE-3 is approximately the price of 3 QDR memories with 8x the memory
- Pins ... Typical application uses only 16 signals (32 pins) with signal Auto-Adaptation

More High-Speed memory generally allows acceleration options for software and hardware architects/designers



Overview Comparison BE vs. QDR

- Memory size
 - BE3 with 1Gb equivalent to 8QDRs with 144Mb per device
- Device PCB board Space Saving
 - 1 BE3 device vs 8 QDR devices
- Signal Pin Reductions
 - o 8 QDR...1Gb requires 1072-1440 pins
 - 1 BE3 ...1Gb...BE3 typical system uses 8 lanes or 32 pins
 - All BE devices have Auto-Adaptation which handles on-board signal tuning, eliminating the need for any external components to insure clean, reliable signals
- Costs
 - One BE-3 with 8x the memory capacity is approx. the price of 3 QDR memories
- Application Benefits
 - o Larger Buffers, High Bandwidth
 - Allows Realtime operations and analysis at Line rate
 - Eliminates need for complex parallel operations using RLDRAM, HBM, or slow DRAM



Example of RMW Function (BE2/BE3/PHE)



Compatibility Quazar - Blazar Family of Accelerator Engines

- MSP220 (QPR4) pin compatible MSR622/MSR820 (BE2)
- MSP230 (QPR8) pin compatible MSR630/MSR830 (BE3)

When there is a need to move data at a high bandwidth, the In-Memory commands can save a tremendous amount of time in one tRC cycle In the BE2.

- 8 Read
- 8 Writes
- 8 Reads + 8 Writes

In the BE3

- 16 Reads
- 16 Writes
- 16 Reads + 16 Writes

Example In-Memory BURST time saving

- tRC 3ns
- QDR 144b read
- QPR 576b read
- QPR 4x of a QDR
- There are more than 12 different commands

Focused on DATA COMPUTING AND DECISION where there is need for memory location modification involving RMW in applications such as metering, as well a single or dual counter update for statistics.

There are over 27 operations available such as add, subtract, compare, increment, etc.

Example In-Memory RMW time saving

Add a Number to a Location (RMW)

QDR Traditional Memory System

- 3 operations Time Analysis
- Total Time = 6ns + FPGA ADD TIME

MoSys In Memory Function

- 1 operations Time Analysis
 - Total Time = 3ns

Simplifying the User Interface to BE2/3 with MoSys RTL Controller



MOSYS FPGA Parallel RTL Interface

MoSys-Supplied RTL Controller Simplifies The User Interface with the BE

MoSys-supplied FPGA RTL Memory Controller interfaces with the MoSys Bandwidth Engine. This controller is between the User Application RTL logic and the BE device.



Memory BE2 576Mb

BE3 1Gb Mb

MoSys-Supplied RTL Controller Simplifies the User Interface with the BE

- It handles all the logic for the Serial GigaChip Interface (GCI) in the FPGA
- Eliminates the user having to design a serial interface by making it transparent and providing a QDR parallel-like interface
- Memory WORD width is user definable in RTL
 - Typical word widths are 8, 16, 32, 36, 64 ... 0
- While the memory on the BE2 is organized as 8Mx72b and the BE3 is 16Mx72b, the address conversion mapping from the selected WORD width to the BE memory is handled by the RTL
 - Address translation to BE memory organization is transparent to the application
- All memory addressing and commands are presented to the QDR like parallel interface
- If the optional In-Memory functions are used, the RTL controller will manage their execution

The signal interface at the User Application is a simple SRAM memory Address, Data, Control structure. This simple interface shields the users from the BE commands, serial interface and the scheduling logic and memory partition timing.

High Speed GCI Serial Interface



Accelerator Engine Family Overview

Software Defined - Hardware Accelerated

	Part Number	r Description -	Package	Interface						Memory		Access Rate	In-Memory Functions			
In-Memory			Pkg Size	Lanes Rate per Lane Gb/s BW MAX.					BW MAX.	tRC	Size	Dillion		BUDST for		Custom & User
			mm	Tx/Rx	10.3	12.5	15.6	25	Gb	ns	Gb	Transactions F per second	R/W	Data Movement	for Compute and Decision	Functions with 32 RISC Cores
QPR4	MSQ220	QPR4 (Quad Partition Rate) 0.5 Gb	FCBGA 19X19	16	~	~			320	3.2	O.5	2.5	~			
QPR8	MSQ230	QPR8 (Quad Partition Rate) 1Gb	FCBGA 27X27	16			*	*	640		1	5	~			
BURST	MSR622	Bandwidth Engine 2 Burst Serial 0.5Gb High Access Memory	FCBGA 19x19	16	~	*			320	3.2	0.5	3.3	~	4		
	MSR630	Bandwidth Engine 3 Burst Serial 1Gb High Access Memory	FCBGA 27x27	16		~	~	~	640	2.7	1	6.5	~	~		
RMW	MSR820	Bandwidth Engine 2 RMW Serial 0.5Gb High Access Memory with ALU for RMW functions	FCBGA 19x19	16	1	~			320	3.2	0.5	3.3	~	√	√	
	MSR830	Bandwidth Engine 3 RMW Serial 1Gb High Access Memory with ALU for RMW functions	FCBGA 27x27	16		~	~	~	640	2.7	1	6.5	~	~	~	
Program	MSPS30	Programmable HyperSpeed Engine Serial Interface, 1Gb Memory, 32 RISC Processor cores for custom algorithms, compute, functions	FCBGA 27x27	16		~	~	~	717	2.7	1	24 Internal	~	~	~	~
RTL	RTL-AE	RTL Memory Controller for Bandwidth Engine and Programmable HyperSpeed Engine. Manages memory and the serial interface signals. Presents a QDR like parallel RTL interface to the user.	FPGA RTL Code		~	1	*	~			576Mb & 1Gb	6.5	~	¥	~	

In-Memory Acceleration Functions



Optional Function Will Not Impact the Device When Used as Memory Only

BURST In-Memory Function

- For sequential Read or Write functions for data movement
- Burst length: 1, 2, 4, or 8 words
- Can double or triple QDR bandwidth
- Simultaneous execution of read and writes

RMW In-Memory Function

- RMW are Read/Modify/Write functions
- Includes many functions for compute and decision
- Examples: ADD, SUB, Compare, INC plus 15 other functions
- Increases execution, speed and bandwidth



LineSpeed and the MoSys logo are trademarks of MoSys, Inc. All other marks mentioned herein are the property of their respective owners.

Flexible Configuration Uses



PB_AE_BE3-RMW w-RTL_R1_201006