ADD: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China. 518110

# **Ni-MH Battery Technology Specification**

Customer	
Part name	Ni-MH Battery
Model No	Ni-MH AAA600mAh 1.2V
Serial No	
Produce No	

Approved by	Drafted by	Xiaojun Nie
Checked by	Signed by	Wenfei Liang
Prepared by	Valid Date	2018-09-26

Company address: 4th Building, Meitai Technology Park, Guanguang

Road, Longhua, Shenzhen, China.

(Tel): +86-755-86670672 (Fax): +86-755-86670609

-1-

E-mail: <a href="mailto:pkcell@pkcell.net">pkcell@pkcell.com</a>
Website: <a href="mailto:http://www.pkcell.com">http://www.pkcell.com</a>

ADD: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China. 518110

### 1. SCOPE

This specification governs the performance of the following pkcell Nickel-Metal Hydride Cylindrical Cell and its stack-up batteries.

pkcell Model: Ni-MH AAA600mAh 1.2V

The data involving nominal voltage and the approximate weight of stake-up batteries shall be equal to the value of the unit cell multiplied by the number of unit cells in the battery.

Nominal voltage of unit cell =1.2V

### 2. RATINGS

Description	Unit	Specification	Conditions
Nominal Voltage	V	1.2	
Nominal Capacity	mAh	600	Standard Charge/discharge
Minimum Capacity	mAh	540	Standard Charge/discharge
Standard Change	mA	60(0.1C)	Ta=0∼45°C
Standard Charge	hour	14-16	1a=0~45 €
	mA	300(0.5C)	-ΔV=5~10mV/pcs Timercutoff=110%input
Fast Charge	hour	2.2approx	capacity Temp.cutoff=55°C Ta=10~45°C
Trickle Charge	mA	30(0.05C) ~ 60(0.1C)	Ta=0~45 °C
Discharge Cut-off Voltage	V	1.0	Ta=-20∼55°C
Maximum Discharging Current	mA	1200	Ta=10∼45°C
Storage Temperature	$^{\circ}$ C	-20∼35℃	Discharge state

#### 3. PERFORMANCE

Unless otherwise stated, tests should be done within one month of delivery under the following

conditions:

Ambient Temperature: Ta=20±5°C Relative Humidity: 65±20% Standard Charge/ Discharge Condition:



# SHENZHEN PKCELL BATTERY CO.,LTD

ADD: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China. 518110

Charge:  $60\text{mA}(0.1\text{C}) \times 16\text{hrs}$ 

Discharge: 120mA(0.2C) to 1.0V/cell

### Table 1

Test	Unit	Specification	Conditions	Remarks
Capacity(0.2C)	min	≥290	≥290 Standard Charge/Discharge	
Open Circuit Voltage (OCV)	V	≥1.25	≥1.25 Within 1hr after standard charge	
Internal Impedance (Ri)	mΩ	≤40 Upon fully charge(1kHz) (1kHz)		
High Rate Discharge (0.5C)	min	≥108	Standard Charge,1hr rest before discharge	
High Rate Discharge (1C)	min	≥54	Standard Charge,1hr rest before discharge	
Overcharge	N/A	No leakage nor explosion	60mA(0.1C) charge 48 hours	
Charge Retention	mAh	≥480(80%)	Standard Charge, Storage: 7 days at 45°C,0.2C Standard Discharge	- 3 -
Charge reserve	mAh	≥85% ≥75% First capacity	Standard charge Storage at 20 degree: 180 days Standard charge Storage at 20 degree: 360 days Standard discharge (0.2C)	1.0V/cell Cut- off
IEC Cycles Test	Cycle	≥500	IEC61951-2 (2003)	

## Table 2

Test	Unit	Specification	Conditions
Leakage N/	N/A	No leakage nor	Full charged at (0.1C) stand for 14
	1 <b>N</b> /A	deformation.	days
Short Circuit		Leakage & deformation	After standard charge, short circuit
	N/A	may occur, but no	for 1 hour(leading
		explosion is allowed.	wire=0.75mm <sup>2</sup> ×20mm)



## SHENZHEN PKCELL BATTERY CO.,LTD

-4-

ADD: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China. 518110

Vibration Resistance	N/A	Change of voltage $\Delta V < 0.02V$ , Change of internal Impedance $\Delta Ri < 5 \text{ m}\Omega$ .	Charge the battery 0.1C 16hrs,the n leave for 24hrs. check battery b efore / after vibration. Amplitude:1.5mm Vibration:3000CPM Any direction for 60mins.
Impact Resistance	N/A	Change of voltage $\Delta V < 0.02V$ , Change of internal Impedance $\Delta Ri < 5 \text{ m}\Omega$ .	Charge the battery 0.1C 16hrs,then leave for 24hrs. (check battery before / after ) dropped, Height:50cm,Wooden board(thickness 30mm)Direction not specified 3 times.

### 4. CONFIGURATION, DIMENSIONS AND MARKINGS

Please refer to the attached drawing.

### 5. EXTERNAL APPEARANCE

The cell/ battery shall be free from cracks, scars, breakage, rust, Discoloration, leakage nor deformation.


#### 6, CAUTION

- ◆.Reverse charging is not acceptable
- ◆.Do not burthen current when charging.
- ◆.Do not charge/discharge with more than the specified current.
- ◆.Do not short circuit the cell/ battery. Permanent damage to the cell/ battery may result.
- ◆. Do not incinerate or mutilate the cell/ battery.
- ◆.Do not subject batteries to adverse conditions like: extreme temperature, deep cycling and excessive Overcharge/overdischarge. The life expectancy may be reduced.
- ◆.Store the cell/battery in a cool dry place. Always discharge the cell/battery before bulk storage or shipment.
- ◆. Cycle(charge and discharge) the battery every 6-9months to maintain cell/battery performance when being stored for an extended period of time.
- ◆.Keep away from children. If swallowed, contact a physician at once.
- ◆. Avoid airtight battery compartments. Ventilation should be provided in the plastic case of batteries, otherwise oxygen and hydrogen gas generated inside can cause explosion when exposed to fire sources such as motors or switches.



ADD: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China. 518110

### 7. Dimensions of the battery:



- 5 -

.....END......

- 5 - If manufacturer want to modify the product technology specification, we won't inform you additionally)