

PC901V0NSZX Series

Digital Output, Normal ON Operation DIP 6 pin *OPIC Photocoupler



■ Description

PC901V0NSZX Series contains an IRED optically coupled to an OPIC chip.

It is packaged in a 6 pin DIP. Input-output isolation voltage(rms) is 5.0kV.

■ Features

- 1. 6 pin DIP package
- 2. Double transfer mold package (Ideal for Flow Soldering)
- 3. Normal ON operation, open collector output
- 4. TTL and LSTTL compatible output
- 5. Operating supply voltage ($V_{CC}=3$ to 15 V)
- 6. Isolation voltage (V_{iso(rms)}: 5.0 kV)

■ Agency approvals/Compliance

- Recognized by UL1577 (Double protection isolation), file No. E64380 (as model No. PC901V)
- Approved by TÜV (VDE0884) (as an option) file No. R2050948 (as model No. PC901V)
- 3. Package resin: UL flammability grade (94V-0)


Applications

- 1. Programmable controllers
- 2. PC peripherals
- 3. Electronic musical instruments

^{* &}quot;OPIC"(Optical IC) is a trademark of the SHARP Corporation. An OPIC consists of a light-detecting element and a signal-processing circuit integrated onto a single chip.




■ Internal Connection Diagram



■ Outline Dimensions

(Unit:mm)



Product mass: approx. 0.36g



Date code (2 digit)

1st digit				2nd digit		
	Year of production		Month of production			
A.D.	Mark	A.D	Mark	Month	Mark	
1990	A	2002	P	January	1	
1991	В	2003	R	February	2	
1992	С	2004	S	March	3	
1993	D	2005	T	April	4	
1994	Е	2006	U	May	5	
1995	F	2007	V	June	6	
1996	Н	2008	W	July	7	
1997	J	2009	X	August	8	
1998	K	2010	A	September	9	
1999	L	2011	В	October	0	
2000	M	2012	С	November	N	
2001	N	:	:	December	D	

repeats in a 20 year cycle

Country of origin Japan



■ Absolute Maximum Ratings (T _a =25°					
	Parameter	Symbol	Rating	Unit	
	Forward current	I_{F}	50	mA	
Input	*1 Peak forward current	I_{FM}	1	A	
	Reverse voltage	V_R	6	V	
	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	70	mW		
Output	Supply voltage	V _{CC}	16	V	
	High level output voltage	V_{OH}	16	V	
Output	Low level output current	I_{OL}	50	mA	
	Power dissipation	Po	150	mW	
Total power dissipation		P _{tot}	170	mW	
Operating temperature		T_{opr}	-25 to +85	°C	
Storage temperature		T _{stg}	-40 to +125	°C	
*2 Isolation voltage			5.0	kV	
*3 Soldering temperature		T _{sol}	260	°C	

^{*1} Pulse width≤100µs, Duty ratio:0.001

■ Electro-optical Characteristics

(unless otherwise specified $T_a=0$ to $+70^{\circ}C$)

Parameter		Symbol	Conditions	MIN.	TYP.	MAX.	Unit		
Input -	Б	Forward voltage		I _F =4mA	_	1.1	1.4	V	
	Forwa			$I_F=0.3mA$	0.7	1.0	_		
	Reverse current		IR	$T_a=25^{\circ}C, V_R=4V$	_	-	10	μΑ	
	Terminal capacitance		Ct	$T_a=25$ °C, V=0, f=1kHz	-	30	250	pF	
Operating supply voltage		Vcc	-	3	_	15	V		
	Low level output voltage		Vol	I_{OL} =16mA, V_{CC} =5V, I_F =0	_	0.2	0.4	V	
	High level output current		Іон	$V_O=V_{CC}=15V$, $I_F=4mA$	_	_	100	μΑ	
	Low level supply current		Iccl	$V_{CC}=5V, I_F=0$	_	2.5	5.0	mA	
	High level supply current		Іссн	$V_{CC}=5V$, $I_F=4mA$	_	2.7	5.5	mA	
Output	*4 "Low	*4 "Low→High" input threshold		T_a =25°C, V_{CC} =5V, R_L =280 Ω	_	1.1	2.0	mA	
	current		IFLH	V_{CC} =5 V , R_L =280 Ω	-	_	4.0		
	*5 "High→Low" input threshold current		IFHL	$T_a=25^{\circ}C, V_{CC}=5V, R_L=280\Omega$	0.4	0.8	-	mA	
				V_{CC} =5 V , R_L =280 Ω	0.3	-	ı		
	*6 Hysteresis		IFHL/IFLH	V_{CC} =5 V , R_L =280 Ω	0.5	0.7	0.9	_	
	Isolation voltage		Riso	T _a =25°C, DC500V, 40 to 60%RH	5×10 ¹⁰	1×10 ¹¹	ı	Ω	
	Response time	"Low→High" propagation delay time	t PLH	T 05°C	_	1	3	μs	
		"High→Low" propagation delay time	t PHL	$T_a=25^{\circ}C$ $V_{CC}=5V, I_F=4mA$	-	2	6		
		Rise time	tr	$R_{L}=280\Omega$	_	0.1	0.5		
Transfer characteristics		Fall time	tf	145 2001	_	0.05	0.5		
	Instantaneous common mode rejection voltage "Output: High level"		СМн	V_{CM} =600V(peak), V_{O} (MIN.)=2V I_{F} =4mA, R_{L} =280 Ω , T_{a} =25°C	_	-2 000	_	V/µs	
	Instantaneous common mode rejection voltage "Output: Low level"		CML	V_{CM} =600V(peak), V_{O} (MAX.)=0.8V I_{F} =0, R_{L} =280 Ω , T_{a} =25 $^{\circ}$ C	-	2 000	ı	V/µs	

^{*4} I_{FLH} represents forward current when output goes from low to high.

^{*2 40} to 60%RH, AC for 1minute, f=60Hz

^{*3} For 10s

^{*5} I_{FHL} represents forward current when output goes from high to low. *6 Hysteresis stands for I_{FHL}/I_{FLH}.



■ Model Line-up


Lead Form	Through-Hole			
Doolsooo	Sleeve			
Package	50 pcs/sleeve			
VDE0884		Approved		
Model No.	PC901V0NSZX	PC901V0YSZX		

Please contact a local SHARP sales representative to inquire about production status and Lead-Free options.

Sheet No.: D2-A05401EN



Fig.1 Test Circuit for Response Time







Fig.2 Test Circuit for Instantaneous Common Mode Rejection Voltage






Fig.3 Forward Current vs. Ambient Temperature




Fig.4 Power Dissipation vs. Ambient Temperature






Fig.5 Forward Current vs. Forward Voltage




Fig.7 Relative Input Threshold Current vs. Ambient Temperature




Fig.9 Low Level Output Voltage vs. Ambient Temperature




Fig.6 Relative Input Threshold Current vs. Supply Voltage




Fig.8 Low Level Output Voltage vs. Low Level Output Current




Fig.10 High Level Output Current vs. Forward Current






Fig.11 High Level Output Current vs.
Ambient Temperature




Fig.13 Propagation Delay Time vs. Forward Current




Fig.12 Supply Current vs. Supply Voltage





Fig.14 Rise Time, Fall Time vs. Load Resistance



Remarks: Please be aware that all data in the graph are just for reference and not for guarantee.



■ Design Considerations

Notes about static electricity

Transistor of detector side in bipolar configuration may be damaged by static electricity due to its minute design.

When handling these devices, general countermeasure against static electricity should be taken to avoid breakdown of devices or degradation of characteristics.

Design guide

In order to stabilize power supply line, we should certainly recommend to connect a by-pass capacitor of $0.01\mu F$ or more between V_{CC} and GND near the device.

In case that some sudden big noise caused by voltage variation is provided between primary and secondary terminals of photocoupler some current caused by it is floating capacitance may be generated and result in false operation since current may go through IRED or current may change.

If the photocoupler may be used under the circumstances where noise will be generated we recommend to use the bypass capacitors at the both ends of IRED.

The detector which is used in this device, has parasitic diode between each pins and GND.

There are cases that miss operation or destruction possibly may be occurred if electric potential of any pin becomes below GND level even for instant.

Therefore it shall be recommended to design the circuit that electric potential of any pin does not become below GND level.

This product is not designed against irradiation and incorporates non-coherent IRED.

Degradation

In general, the emission of the IRED used in photocouplers will degrade over time.

In the case of long term operation, please take the general IRED degradation (50% degradation over 5years) into the design consideration.

Please decide the input current which become 2times of MAX. I_{FLH}.

☆ For additional design assistance, please review our corresponding Optoelectronic Application Notes.



■ Manufacturing Guidelines

Soldering Method

Flow Soldering:

Due to SHARP's double transfer mold construction submersion in flow solder bath is allowed under the below listed guidelines.

Flow soldering should be completed below 270°C and within 10s.

Preheating is within the bounds of 100 to 150°C and 30 to 80s.

Please don't solder more than twice.

Hand soldering

Hand soldering should be completed within 3s when the point of solder iron is below 400°C.

Please don't solder more than twice.

Other notices

Please test the soldering method in actual condition and make sure the soldering works fine, since the impact on the junction between the device and PCB varies depending on the tooling and soldering conditions.

Sheet No.: D2-A05401EN



Cleaning instructions

Solvent cleaning:

Solvent temperature should be 45°C or below Immersion time should be 3minutes or less

Ultrasonic cleaning:

The impact on the device varies depending on the size of the cleaning bath, ultrasonic output, cleaning time, size of PCB and mounting method of the device.

Therefore, please make sure the device withstands the ultrasonic cleaning in actual conditions in advance of mass production.

Recommended solvent materials:

Ethyl alcohol, Methyl alcohol and Isopropyl alcohol

In case the other type of solvent materials are intended to be used, please make sure they work fine in actual using conditions since some materials may erode the packaging resin.

Presence of ODC

This product shall not contain the following materials.

And they are not used in the production process for this device.

Regulation substances: CFCs, Halon, Carbon tetrachloride, 1.1.1-Trichloroethane (Methylchloroform)

Specific brominated flame retardants such as the PBBOs and PBBs are not used in this product at all.



■ Package specification

Sleeve package

Package materials

Sleeve: HIPS (with anti-static material)

Stopper: Styrene-Elastomer

Package method


MAX. 50 pcs. of products shall be packaged in a sleeve.


Both ends shall be closed by tabbed and tabless stoppers.

The product shall be arranged in the sleeve with its anode mark on the tabless stopper side.

MAX. 20 sleeves in one case.

Sleeve outline dimensions







■ Important Notices

- · The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- · Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- · Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:
- (i) The devices in this publication are designed for use in general electronic equipment designs such as:
 - --- Personal computers
 - --- Office automation equipment
 - --- Telecommunication equipment [terminal]
 - --- Test and measurement equipment
 - --- Industrial control
 - --- Audio visual equipment
 - --- Consumer electronics
- (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection

with equipment that requires higher reliability such as:

- --- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
- --- Traffic signals
- --- Gas leakage sensor breakers
- --- Alarm equipment
- --- Various safety devices, etc.
- (iii) SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:
 - --- Space applications
 - --- Telecommunication equipment [trunk lines]
 - --- Nuclear power control equipment
 - --- Medical and other life support equipment (e.g., scuba).
- · If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- · This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- Contact and consult with a SHARP representative if there are any questions about the contents of this publication.