

# MPLAD36KP14A – MPLAD36KP400CA



## Surface Mount 36,000 Watt Transient Voltage Suppressor

High-Reliability  
screening available in  
reference to  
MIL-PRF-19500


### DESCRIPTION

These high power 36 kW rated transient voltage suppressors in a surface mount package are provided with design features to minimize thermal resistance and cumulative heating. Typical applications include lightning and automotive load dump protection. They are particularly effective at meeting the multi-stroke lightning standard RTCA DO-160, section 22 for aircraft design. This efficient low profile package design is offered in standoff voltage selections ( $V_{VM}$ ) of 14 volts to 400 volts in either unidirectional or bidirectional construction.

**Important:** For the latest information, visit our website <http://www.microsemi.com>.

### FEATURES

- Available in both unidirectional and bidirectional construction (bidirectional with CA suffix)
- High reliability with wafer fabrication and assembly lot traceability
- All parts surge tested
- Low profile surface mount package
- Optional upscrewing is available with various screening and conformance inspection options based on MIL-PRF-19500. Refer to [Hirel Non-Hermetic Product Portfolio](#) brochure on our web site for more details on the screening options.
- Suppresses transients up to 36,000 W @ 10/1000  $\mu$ s (see [Figure 1](#))
- Moisture classification is Level 1 with no dry pack required per IPC/JEDEC J-STD-020B
- RoHS compliant versions are available
- $3\sigma$  lot norm screening performed on standby current ( $I_D$ )



### PLAD

(The cathode is the metal base under the body of this device.)

### APPLICATIONS / BENEFITS

- Protection from switching transients and induced RFI
- Protection from ESD, and EFT per IEC 61000-4-2 and IEC 61000-4-4
- Secondary lightning protection per IEC 61000-4-5 with 42 ohms source impedance:
  - Class 1,2,3,4,5: MPLAD36KP14A to 400CA
  - Class 5: MPLAD36KP14A to 400CA (short distance)
  - Class 5: MPLAD36KP14A to 260CA (long distance)
- Secondary lightning protection per IEC 61000-4-5 with 12 ohms source impedance:
  - Class 1,2,3: MPLAD36KP14A to 400CA
  - Class 4: MPLAD36KP14A to 280CA
- Secondary lightning protection per IEC 61000-4-5 with 2 ohms source impedance:
  - Class 2: MPLAD36KP10A to 400CA
  - Class 3: MPLAD36KP14A to 260CA
  - Class 4: MPLAD36KP14A to 130CA
- Pin injection protection per RTCA/DO-160F for Waveform 4 (6.4/69  $\mu$ s @ 25°C)\*:
  - Level 4: MPLAD36KP14A to 400CA
  - Level 5: MPLAD36KP14A to 300CA
- Pin injection protection per RTCA/DO-160F for Waveform 5A (40/120  $\mu$ s @25°C)\*:
  - Level 4: MPLAD36KP14A to 78CA
  - Level 5: MPLAD36KP14A to 38CA

\*See [MicroNote 132](#) for further temperature derating selection.

# MPLAD36KP14A – MPLAD36KP400CA

## MAXIMUM RATINGS @ 25°C unless otherwise specified


Symbol	Parameters / Test Conditions	Value	Unit	
T <sub>J</sub> and T <sub>STG</sub>	Junction and Storage Temperature	-55 to +150	°C/W	
R <sub>θJA</sub>	Thermal Resistance Junction-to-Ambient <sup>(1)</sup>	50		
R <sub>θJC</sub>	Thermal Resistance Junction-to-Case	1.0		
P <sub>PP</sub>	Peak Pulse Power @ 10/1000 μs <sup>(2)</sup>	36,000	W	
	t <sub>clamping</sub> (0 volts to V <sub>(BR min)</sub> )	Unidirectional Bidirectional	<100 <5	ps ns
V <sub>FS</sub>	Forward Clamping Voltage @ 500 Amps <sup>(3)</sup>	4.0	V	
I <sub>FSM</sub>	Forward Surge Current <sup>(3)</sup>	1500	A	
T <sub>SP</sub>	Solder Temperature @ 10s	260	°C	
P <sub>D</sub>	Steady-State Power dissipation <sup>(5)</sup>	T <sub>A</sub> = 25°C	2.5 <sup>(1)</sup>	W
		T <sub>C</sub> = 100°C	71 <sup>(1)</sup>	

- Notes:**
- When mounted on FR4 PC board with recommended mounting pad (see [pad layout](#)).
  - Also see [figures 1 and 2](#). With impulse repetition rate (duty factor) of 0.05% or less.
  - At 8.3 ms half-sine wave (unidirectional devices only).
  - Case temperature controlled on heat sink as specified.
  - See [MicroNote 134](#) for derating P<sub>PP</sub> when also applying steady-state power.

## MECHANICAL and PACKAGING

- CASE: Void-free transfer molded thermosetting epoxy body meeting UL94V-0
- TERMINALS: Tin-lead or RoHS compliant annealed matte-tin plating readily solderable per MIL-STD-750, method 2026
- MARKING: Body marked with part number
- POLARITY: For unidirectional devices, the cathode is on the metal backside (package bottom)
- Available in bulk or custom tape-and-reel packaging
- TAPE-AND-REEL: Standard per EIA-481-B (add "TR" suffix to part number). Consult factory for quantities.
- WEIGHT: Approximately 1.7 – 2.0 grams
- See [Package Dimensions](#) on last page.

## PART NOMENCLATURE



# MPLAD36KP14A – MPLAD36KP400CA

## SYMBOLS & DEFINITIONS

Symbol	Definition
$I_{(BR)}$	Breakdown Current: The current used for measuring breakdown voltage $V_{(BR)}$ .
$I_D$	Standby Current: The current at the rated standoff voltage $V_{WM}$ .
$I_{PP}$	Peak Impulse Current: The peak current during the impulse.
$V_{(BR)}$	Breakdown Voltage: The minimum voltage the device will exhibit at a specified current.
$V_C$	Clamping Voltage: Clamping voltage at $I_{PP}$ (peak pulse current) at the specified pulse conditions (typically shown as maximum value).
$V_{WM}$	Related Working Standoff Voltage: The maximum peak voltage that can be applied over the operating temperature range.
$\alpha_{V(BR)}$	Temperature Coefficient of Breakdown Voltage: The change in breakdown voltage divided by change temperature.

## ELECTRICAL CHARACTERISTICS @ 25°C unless otherwise specified


MICROSEMI PART NUMBER		REVERSE STANDOFF VOLTAGE $V_{WM}$ (Note 1)	BREAKDOWN VOLTAGE $V_{(BR)}$ @ $I_{(BR)}$		MAXIMUM CLAMPING VOLTAGE $V_C$ @ $I_{PP}$	MAXIMUM STANDBY CURRENT $I_D$ @ $V_{WM}$	MAXIMUM PEAK PULSE CURRENT $I_{PP}$ (FIG. 3)	MAXIMUM TEMPERATURE COEFFICIENT $\alpha_{V(BR)}$
Unidirectional	Bidirectional	Volts	Volts	mA	Volts	$\mu A$	A	mV/ °C
MPLAD36KP14A	MPLAD36KP14CA	14	15.6 – 17.2	150	24.0	3000	1500*	10
MPLAD36KP15A	MPLAD36KP15CA	15	16.7 – 18.5	5	25.8	750	1396*	12
MPLAD36KP16A	MPLAD36KP16CA	16	17.8 – 19.7	5	27.2	450	1324*	12
MPLAD36KP17A	MPLAD36KP17CA	17	18.9 – 20.9	5	28.8	150	1250*	14
MPLAD36KP18A	MPLAD36KP18CA	18	20.0 – 22.1	5	30.8	60	1169*	16
MPLAD36KP20A	MPLAD36KP20CA	20	22.2 – 24.5	5	34.0	45	1059*	18
MPLAD36KP22A	MPLAD36KP22CA	22	24.4 – 26.9	5	36.4	10	990	20
MPLAD36KP24A	MPLAD36KP24CA	24	26.7 – 29.5	5	39.8	10	905	22
MPLAD36KP26A	MPLAD36KP26CA	26	28.9 – 31.9	5	43.0	10	838	24
MPLAD36KP28A	MPLAD36KP28CA	28	31.1 – 34.4	5	46.4	10	776	26
MPLAD36KP30A	MPLAD36KP30CA	30	33.3 – 36.8	5	48.8	10	738	30
MPLAD36KP33A	MPLAD36KP33CA	33	36.7 – 40.6	5	53.3	10	676	35
MPLAD36KP36A	MPLAD36KP36CA	36	40.0 – 44.2	5	58.1	10	620	38
MPLAD36KP40A	MPLAD36KP40CA	40	44.4 – 49.1	5	64.5	10	559	44
MPLAD36KP43A	MPLAD36KP43CA	43	47.8 – 52.8	5	69.4	10	519	50
MPLAD36KP45A	MPLAD36KP45CA	45	50.0 – 55.3	5	72.7	10	496	51
MPLAD36KP48A	MPLAD36KP48CA	48	53.3 – 58.9	5	77.4	10	466	54
MPLAD36KP51A	MPLAD36KP51CA	51	56.7 – 62.7	5	82.4	10	437	58
MPLAD36KP54A	MPLAD36KP54CA	54	60.0 – 66.3	5	87.1	10	414	64
MPLAD36KP58A	MPLAD36KP58CA	58	64.4 – 71.2	5	93.6	10	385	70
MPLAD36KP60A	MPLAD36KP60CA	60	66.7 – 73.7	5	96.8	10	372	72
MPLAD36KP64A	MPLAD36KP64CA	64	71.1 – 78.6	5	103.0	10	350	75
MPLAD36KP70A	MPLAD36KP70CA	70	77.8 – 86.0	5	113	10	319	84
MPLAD36KP75A	MPLAD36KP75CA	75	83.3 – 92.1	5	121	10	298	90
MPLAD36KP78A	MPLAD36KP78CA	78	86.7 – 95.8	5	126	10	286	95
MPLAD36KP85A	MPLAD36KP85CA	85	94.4 – 104.0	5	137	10	263	104
MPLAD36KP90A	MPLAD36KP90CA	90	100 – 111	5	146	10	247	109
MPLAD36KP100A	MPLAD36KP100CA	100	111 – 123	5	162	10	223	122
MPLAD36KP110A	MPLAD36KP110CA	110	122 – 135	5	177	10	204	132
MPLAD36KP120A	MPLAD36KP120CA	120	133 – 147	5	193	10	187	145
MPLAD36KP130A	MPLAD36KP130CA	130	144 – 159	5	209	10	173	157
MPLAD36KP150A	MPLAD36KP150CA	150	167 – 185	5	243	10	149	183
MPLAD36KP160A	MPLAD36KP160CA	160	178 – 197	5	259	10	139	195
MPLAD36KP170A	MPLAD36KP170CA	170	189 – 209	5	275	10	131	207
MPLAD36KP180A	MPLAD36KP180CA	180	200 – 221	5	291	10	124	219
MPLAD36KP200A	MPLAD36KP200CA	200	222 – 245	5	322	10	112	243
MPLAD36KP220A	MPLAD36KP220CA	220	245 – 271	5	356	10	102	269
MPLAD36KP260A	MPLAD36KP260CA	260	289 – 320	5	419	10	86	318
MPLAD36KP280A	MPLAD36KP280CA	280	311 – 345	5	451	10	80	344
MPLAD36KP300A	MPLAD36KP300CA	300	333 – 369	5	483	10	75	368
MPLAD36KP350A	MPLAD36KP350CA	350	389 – 431	5	564	10	64	430
MPLAD36KP400A	MPLAD36KP400CA	400	444 – 492	5	644	10	56	490

**NOTE 1:** Transient Voltage Suppressors are normally selected with reverse standoff voltage  $V_{WM}$ , which should be equal to or greater than peak operating voltage.


\* Surge Testing is performed to 1000Amps due to equipment limitations

# MPLAD36KP14A – MPLAD36KP400CA

## GRAPHS




**Figure 1**  
Peak Pulse Power vs. Pulse Time



**Figure 2**  
Pulse Waveform  
Test waveform parameters: tr = 10 μs, tp = 1000 μs

# MPLAD36KP14A – MPLAD36KP400CA


## GRAPHS (continued)




**Figure 3**  
Derating Curve

# MPLAD36KP14A – MPLAD36KP400CA

## PACKAGE DIMENSIONS



## PAD LAYOUT



Ref.	Dimensions	
	Inch	Millimeters
	Typical	Typical
A	0.470	11.94
B	0.230	5.85
C	0.100	2.44
D	0.045	1.15

# MPLAD36KP14A – MPLAD36KP400CA



**Microsemi Corporate Headquarters**  
One Enterprise, Aliso Viejo, CA 92656 USA  
Within the USA: +1 (800) 713-4113  
Outside the USA: +1 (949) 380-6100  
Sales: +1 (949) 380-6136  
Fax: +1 (949) 215-4996  
Email: [sales.support@microsemi.com](mailto:sales.support@microsemi.com)  
[www.microsemi.com](http://www.microsemi.com)

©2016 Microsemi Corporation. All rights reserved. Microsemi and the Microsemi logo are registered trademarks of Microsemi Corporation. All other trademarks and service marks are the property of their respective owners.

Microsemi Corporation (Nasdaq: MSCC) offers a comprehensive portfolio of semiconductor and system solutions for aerospace & defense, communications, data center and industrial markets. Products include high-performance and radiation-hardened analog mixed-signal integrated circuits, FPGAs, SoCs and ASICs; power management products; timing and synchronization devices and precise time solutions, setting the world's standard for time; voice processing devices; RF solutions; discrete components; enterprise storage and communication solutions; security technologies and scalable anti-tamper products; Ethernet solutions; Power-over-Ethernet ICs and midspans; as well as custom design capabilities and services. Microsemi is headquartered in Aliso Viejo, California and has approximately 4,800 employees globally. Learn more at [www.microsemi.com](http://www.microsemi.com)

Microsemi makes no warranty, representation, or guarantee regarding the information contained herein or the suitability of its products and services for any particular purpose, nor does Microsemi assume any liability whatsoever arising out of the application or use of any product or circuit. The products sold hereunder and any other products sold by Microsemi have been subject to limited testing and should not be used in conjunction with mission-critical equipment or applications. Any performance specifications are believed to be reliable but are not verified, and Buyer must conduct and complete all performance and other testing of the products, alone and together with, or installed in, any end-products. Buyer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is the Buyer's responsibility to independently determine suitability of any products and to test and verify the same. The information provided by Microsemi hereunder is provided "as is, where is" and with all faults, and the entire risk associated with such information is entirely with the Buyer. Microsemi does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other IP rights, whether with regard to such information itself or anything described by such information. Information provided in this document is proprietary to Microsemi, and Microsemi reserves the right to make any changes to the information in this document or to any products and services at any time without notice.