

# **SUNON**

## SPECIFICATION FOR APPROVAL

CUSTOMER	:	Sunon Inc.
MOTOR TYPE	:	MAGLev® Fan & Blower by SUNON
DESCRIPTION	:	MagLev Motor Fan
DIMENSIONS	:	12X12X3 mm
MODEL	:	UF3C3-700
SUNON SPEC. NO.	:	D01001061F-01
CUSTOMER APPROVAL NO.	:	UF3C3-700 TC
APPROVED BY CUSTOMER (AUTHORIZED)	:	

						SPEC.NO	D01001061F-01
Alice- DRAWN chang CHECKED Chin-jung APPROVED					ISSUE DATE	10.19.2018	
	Chin-jung	EDITION	0				
	10/19			<b>REVISION DATE</b>			
				E.SPEC	E30900399		
建準電	機工業股份	}有限公司	J				
SUNO	NWEALTH	I ELECT	RIC MACHI	NE INDU	STRY CO.,	LTD.	
NO. 30, LN. 296, XINYA RD., QIANZHEN DIST., TEL:886-7-8135888							
KAOHSIUNG CITY 80673, TAIWAN (R.O.C) FAX:886-7-8230505/8230606/8231010							
URL:http://www.sunon.com E-mail: sunon@email.sunon.com.tw							

### DC BRUSHLESS FAN MODEL : UF3C3-700

₩<sup>工業</sup>後 D.C.C. <sup>¬</sup>

章

SUNON1

發行

### **CHARACTERISTICS**

1. Motor Design	: Single phase, 6-poles Brushless DC motor.
2. Insulation Resistance	: More than 20M ohm between internal stator and
	lead wire(+) measured at DC 100V.
3. Dielectric Strength	: Applied AC 500V for one minute or AC 600V for
	2 seconds between housing and lead wire(+)
4. Noise Level	: Measured in a semi-anechoic chamber
	with background noise level below 15
	dB(A). The fan is running in free air with the
	microphone at a distance of 20 centimeter
	from the fan intake.
5. Input Power, Current & Speed	: Measured after continuous 10 minute
	operation at rated voltage in clean air, and
	at ambient temperature of 25 degrees C.
6. Tolerance	: +15% / -30% on rated power and current.
7. Air Performance	: Measured by a double chamber. The values
	are recorded when the fan speed has stabilized
	at rated voltage.
建準電機工業股份有限公司	SPEC.NO D01001061F-01 REVISION DATE

建準電機工業股份有限公司	SPEC.NO	D01001061F-01	<b>REVISION DATE</b>	
SUNONWEALTH ELECTRIC	<b>ISSUE DATE</b>	10.19.2018	ΕΟΙΤΙΟΝ	0
MACHINE INDUSTRY CO., LTD.	PAGE	2 OF 10		

## SPECIFICATIONS

#### **MODEL : UF3C3-700**


1-2. Operating Voltage Range	: 2.0~3.5 VDC					
1-3. Starting Voltage	: 2.0 VDC (25 deg. C POWER ON/OFF)					
1-4. Rated Speed	: 16500 RPM ± 30%					
1-5. Air Delivery	: 5.95 l/min					
1-6. Static Pressure	: 18.91 Pa					
1-7. Rated Current	: 97 mA					
1-8. Rated Power	: 0.3 WATTS					
1-9. Noise Level	: 14.0 dB(A) @ 1M 28.3 dB(A) @ 0.2M					
1-10. Direction of Rotation	: Counter-clockwise viewed from front of fan blade					
1-11. Operating Temperature	: -10 to +70 deg. C					
1-12. Storage Temperature	: -40 to +70 deg. C					
1-13. Bearing System	: Vapo bearing system					
1-14. Weight	: 0.7 g					
1-15. Safety	: CE Approvals					
1-16. Protection	: ☑Automatic Restart Capability Note: In a situation where the fan is locked by an external force while the electricity is on, an increase in coil temperature will be prevented by temporarily turning off the electrical power to the motor. The fan will automatically restart when the locked rotor condition is released. ☑Polarity Protection					
1-17. IP Class : IP55	<ul> <li>According to IEC 60529 (or IEC 34-5) IP standard, the average temperature is 23~24°C and humidity is 67% RH for Dust Water Test. The fan needs to be test and Spray Put in dust box for 8 hours for Dust Test and be sprayed low pressure jets of water from all directions for Spray Water Test. After these 2 tests, which executing by regular standard, the fan will be measured the performance is normal or not.</li> <li>PS. There are different applicative environments and systems by different customers, so please put the product in the most suitable environment to measure the performances.</li> </ul>					
	PEC.NO     D01001061F-01     REVISION DATE       SSUE DATE     10.10.2018     E. D. L.T. L.O. N. 0					
UNONWEALTH ELECTRIC	SSUE DATE         10.19.2018         E D I T I O N         0           P A G E         3 OF 10					


D.C.C

行

SU2NE) NO1

發





# ● **SUNON**1 發行章

# Notes

#### I .SAFETY

- 1. DO NOT use or operate this fan in excess of the limitations set forth in this specification. SUNON is not responsible for the non-performance of this fan and/or any damages resulting from its use, if it is not used or operated in accordance with the specifications.
- 2. SUNON recommends adding a protection circuit to the product or application in which this fan is installed, such as a thermo-fuse, or current-fuse or thermo-protector. The failure to use such a device may result in smoke, fire, electric shock by insulation degradation in cases of motor lead short circuit, overload, or over voltage, and/or other failure.
- 3. SUNON recommends installing a protection device to the product or application in which this fan is installed if there is a possibility of reverse-connection between VDC (+) and GND (-). The failure to install such a device may result in smoke, fire, and/or destruction, although these conditions may not manifest immediately.
- 4. This fan must be installed and used in compliance with all applicable safety standards and regulations.
- 5. Use proper care when handling and/or installing this fan. Improper handling or installation of this fan may cause damage that could result in unsafe conditions.
- 6. Use proper care during installation and/or wiring. Failure to use proper care may cause damage to certain components of the fan including, but not limited to, the coil and lead wires, which could result in smoke and/or fire.
- 7. DO NOT use power or ground PWM to control the fan speed. If the fan speed needs to be adjusted, please contact SUNON to customize the product design for your application.
- 8. For critical or extreme environments, including non stop operation, please contact SUNON and we will gladly provide assistance with your product selection to ensure an appropriate cooling product for your application.

建準電機工業股份有限公司	SPEC.NO	D01001061F-01	<b>REVISION DATE</b>	
SUNONWEALTH ELECTRIC	<b>ISSUE DATE</b>	10.19.2018	ΕΟΙΤΙΟΝ	0
MACHINE INDUSTRY CO., LTD.	PAGE	6 OF 10		

# Notes



- 1. SUNON offers engineering assistance on fan installation and cooling system design.
- 2. All changes, modifications and/or revisions to the specifications, if any, are incorporated in the attached specifications.
- 3. No changes, modifications and/or revisions to these specifications are effective absent agreement, by both SUNON and the customer, in writing.
- 4. This fan will be shipped in accordance with the attached specification unless SUNON and the customer have agreed otherwise, in writing, as specified in Paragraph 3, above.

#### III. OTHER

- 1. When building your device, please examine thoroughly any variation of EMC, temperature rise, life data, quality, etc. of this product by shock/drop/vibration testing, etc. If there are any problems or accidents in connection with this product, it should be mutually discussed and examined.
- 2. Use proper care when handling this fan. Components such as fan holders or bearings may be damaged, if touched with fingers or other objects. Additionally, static electricity (ESD) may damage the internal circuits of the fan.
- **3.** DO NOT operate this fan in proximity to hazardous materials such as organic silicon, cyanogens, formalin, phenol, or corrosive gas environments including, but not limited to, H<sub>2</sub>S, SO<sub>2</sub>, NO<sub>2</sub>, or Cl<sub>2</sub>.
- 4. SUNON recommends that you protect this fan from exposure to outside elements such as dust, condensation, humidity or insects. Exposure of this fan to outside elements such as dust, condensation, humidity or insects may affect its performance and may cause safety hazards. SUNON does not warrant against damage to the product caused by outside elements.

Re: The term can be excluded, if the fan has been with IP design and meets customer's IP requirement.

建準電機工業股份有限公司	SPEC.NO	D01001061F-01	<b>REVISION DATE</b>	
SUNONWEALTH ELECTRIC	<b>ISSUE DATE</b>	10.19.2018	ΕΟΙΤΙΟΝ	0
MACHINE INDUSTRY CO., LTD.	PAGE	7 OF 10		

# Notes

- 5. This fan must be installed properly and securely. Improper mounting may cause harsh resonance, vibration, and noise.
- 6. Fan guards may prevent injury during handling or installation of the fan and are available for sale with this fan.
- 7. Unless otherwise noted, all testing of this fan is conducted at 25°C ambient temperature and sixty-five percent (65%) relative humidity.
- 8. DO NOT store this fan in an environment with high humidity. This fan must be stored in accordance with the attached specifications regarding storage temperature. If this fan is stored for more than 6 months, SUNON recommends functional testing before using.
- 9. SUNON reserves the right to use components from multiple sources at its discretion. The use of components from other sources will not affect the specifications as described herein.
- 10.The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy Test Reports (L10 and MTTF Report) that relate to this fan are only for reference.

#### VI. WARRANTY

This fan is warranted against all defects which are proved to be fault in our workmanship and material for one year from the date of our delivery. The sole responsibility under the warranty shall be limited to the repair of the fan or the replacement thereof, at SUNON's sole discretion. SUNON will not be responsible for the failures of its fans due to improper handing, misuse or the failure to follow specifications or instructions for use. In the event of warranty claim, the customer shall immediately notify SUNON for verification. SUNON will not be responsible for any consequential damage to the customer's equipment as a result of any fans proven to be defective.

建準電機工業股份有限公司	SPEC.NO	D01001061F-01	<b>REVISION DATE</b>	
SUNONWEALTH ELECTRIC	<b>ISSUE DATE</b>	10.19.2018	ΕΟΙΤΙΟΝ	0
MACHINE INDUSTRY CO., LTD.	PAGE	8 OF 10		

### **Declaration of Restricted Materials**

Control declaration of environment- related substances/ materials

1. In accordance with the Restriction of Hazardous Substances (RoHS) Directive 2011/65/EU and specific market requirements, Sunon Halogen-Free Product have complied with law and discipline not to employ the forbidden substances, and restrict the allowable concentration of some limited substances deliberately in our components.

D.C.C.

行

SUN0.N.01

發

No			Substance			С	riteria	
1	CFCs & HCFCs (ozone depleting substances)					Forbid	den	
2	<b>Chlorinated Organic Solv</b>	<u> </u>	,			Forbid	den	
	8	Plastic (Frame, Impeller, wire harness, et		c.)	<100pp			
			Solder			<1000p		
3	Lead and its compounds	Steel al	lov			<b>&lt;3500</b>		
	I		nium alloy			<4000ppm		
		Copper	U			<4wt%	±	
		Solder	J			<20pp	m	
4	Cadmium and its compounds		omposed of met ass, zinc for die	als containing zinc casting)		<100pp		
		Plastic				<5ppm	l	
5	<b>PBBs and PBDEs</b>					Forbid	den	
6	PCB and PCT					Forbid	den	
7	CP, Short-chain Chlorina	ted para	ffins C10-13, Cl	≥48 wt%		Forbid	den	
8	Mirex	•	,			Forbid	den	
9	PCN					Forbidden		
10	Hexavalent Chromium compounds					<100pp	om	
11	Mercury and its compounds						Forbidden	
12							den	
13	Organic Tin compounds					Forbid	den	
14	Azo compounds					Forbid	den	
15	TBBP-A in external case	plastic p	arts of products	(PCB is exempted)		<1000p	opm	
16	Nickel in external case par	ts, which	are likely to resu	ılt in prolonged skir	n exposure	<1000p	opm	
17	Hexabromocyclododecane	(HBCDD	))			<1000p	opm	
18	Di-butyl Phthalate (DBP)					<1000p	opm	
19	Benzyl butyl Phthalate (BB	BP)				<1000p	opm	
20	Di-ethylhexyl Phthalate (D					<1000p	opm	
21	Di-isobutyl Phthalate (DIB	P)				<1000p	opm	
22	Brominated/chlorinated f applicatable item: frame,		· · · · · · · · · · · · · · · · · · ·			Br<900 Cl<900	* *	
	insulator.						<1500ppm	
23						BaP <		
24	<b>4</b> PCB and electroplating material, PFOS content complianced with					PFOS coating	≤1000ppm ≤1000ppm g material ≤ 1µg/m²	
A			SPEC.NO	D01001061F-01	REVISION	JDATE		
準電机	幾工業股份有限公司		SI ECINO	D01001001L-01	KE VISIOF	DAIL		

建準電機工業股份有限公司	SPEC.NO	D01001061F-01	<b>REVISION DATE</b>	
SUNONWEALTH ELECTRIC	<b>ISSUE DATE</b>	10.19.2018	ΕΟΙΤΙΟΝ	0
MACHINE INDUSTRY CO., LTD.	PAGE	9 OF 10		

