




**L.T.F.**

## DOB AC Line Voltage LED Boards



### Dimmable 30W Round 228mm (OD) QLUXDOBAR22830W110LED DOB Series

## QLUX DOB



<b>Wattage</b>	30W
<b>Input</b>	120V AC 50/60 Hz
<b>CRI</b>	90+
<b>CCT Options</b>	2500K - 4000K
<b>Custom CCT</b>	Available
<b>Size</b>	228mm (OD)
<b>Dimming</b>	ELV, Triac
<b>Optional Dimming</b>	0-10V
<b>Beam Angle</b>	160°



**RoHS**



### FEATURES

- Exceeds California Title 24 requirements
- AC line voltage driver on board module; No external drivers or transformers required
- High efficacy lumen output: > 80 lm/W
- Smooth dimming with ELV & Triac dimmers
- Optional 0-10V dimming
- 220-240V, 277V AC input with optional voltage converter
- LM-80 compliant LEDs
- High Color Renedering Index (CRI) 90+

- Tight binning 3 Step Mac Adam Ellipses
- Low heat generation, easy thermal management
- L70 > 60,000 Hours



### APPLICATIONS

- New or retrofit OEM fixtures
- Indoor or outdoor applications
- Architectural and commercial
- Flush mount and recessed fixtures



### AVAILABLE CONFIGURATIONS

Model Number	Suffix	CRI	CCT	Lumens
QLUXDOBAR22830W110LED	- 925	90+	2500K	2400lm
QLUXDOBAR22830W110LED	- 927		2700K	2500lm
QLUXDOBAR22830W110LED	- 930		3000K	2600lm
QLUXDOBAR22830W110LED	- 935		3500K	2700lm
QLUXDOBAR22830W110LED	- 940		4000K	2700lm

Custom CCT available

[1] Luminous flux and efficacy are typical value, measured by an integrated sphere at 25°C, tolerance: ± 10%;

[2] Ra/CRI is measured with tolerance: ± 2;

[3] Tolerance of power: ± 1W.




**L.T.F.**

## DOB AC Line Voltage LED Boards


**Dimmable 30W Round 228mm (OD)  
QLUXDOBAR22830W110LED DOB Series**

### SPECTRORADIOMETRIC CHARACTERISTICS



\* Test result shown based on 3000K CCT

### CRI TEST RESULTS



R1=97	R2=100	R3=99	R4=95	R5=97	R6=97	R7=93	R8=89
R9=76	R10=98	R11=97	R12=82	R13=98	R14=100	R15=94	

\* Test result shown based on 3000K CCT



**L.T.F.**

## DOB AC Line Voltage LED Boards

Dimmable 30W Round 228mm (OD)  
QLUXDOBAR22830W110LED DOB Series

### ABSOLUTE MAXIMUM RATINGS (Ta=25°C)

Parameter	Symbol	Value	Unit
Voltage	V in	132	Vac
Operating Temperature	---	-35~+50	°C
LED Solder Temperature	Ts	110	°C
Storage Temperature	Tstg	-40~+100	°C
ESD Sensitivity (HBM)	---	±4000	V
Surge	---	2500	Vac

### MECHANICAL SPECIFICATIONS

