


### PRODUCT NUMBER: 867-22-005-70-501011

www.mill-max.com DATA SHEET





# 867-22-005-70-501011- SPECIFICATIONS

General Info	
Description <sup>1</sup> :	Wire Termination Spring-Loaded Header Pre-Wired with 8" 24 AWG Black Stranded Wires
Туре:	Spring-Loaded
Category:	Crimped Wire Cable Assembly
Mounting Style:	Wire Termination - Crimp Type
# Pins:	5
Pitch:	.100" (2,540mm)
Rows:	Single Row
Product Lifecycle:	Active

Waterials	
Loose Pin/Receptacle #(Material):	0992 (Brass Alloy)
Shell Plating:	20µ" Gold over Nickel
Inner Plating:	(Spring) 10µ" Gold
Insulator Material:	Nylon 4/6
Technical Specs	

.055" (1,397mm)

100 VRMS/150 VDC

10,000 MΩ min.

1,000 VRMS min.

Matorials

Stroke:

**Electrical Specs** 

**Rated Voltage:** 

**Insulation Resistance:** 

**Dielectric Withstanding Voltage:** 

# Environmental Specs

Temperature Range <sup>2</sup> :	-55/+125° C
Shock <sup>3</sup> :	No Elect. Discontinuity > 1 $\mu$ s @ 50g
Vibration <sup>3</sup> :	No Elect. Discontinuity > 1µs @ 10-2000HZ, 15 G
RoHS⁴:	Yes

#### **Mechanical Specs**

Durability: 100,000 to 1,000,000 Cycles @ Mid-Stroke

## **NOTES:**

#### 1. Standard Tolerances

Assembly tolerance: +/-.010" (.25mm)

Connector Length "L"

Tolerance
+/005" (+/127 mm)
+ .007/006" (+ .178/152 mm)
+ .009 /007" (+ .229 /178 mm)
+ .011 /008" (+ .279 /203 mm)
+ .013 /009" (+ .330 /229 mm)

Insulator width: +/-.005 (.13mm)

Insulator height: +/-.005 (.13mm) Co-planarity of SMT connectors: .005" (.13mm) up to 1" (25.4mm) in connector length Insulator Flatness: .005" (.13mm) up to 1" (25.4mm) in connector length Pin Length: +/-.006 (.15mm) Pin Diameter: +/-.002 (.051mm)

Pin Angle: +/-2°

- 2. Per IEC 60512-11-(4,-9,-10,-12)
- 3. For discrete pin only. Per IEC 60512-6-3: Test 6c: Shock
- Mill-Max products labeled with the RoHS symbol are compliant with all three ROHS Directives. All of our products previously described as RoHS (2002/95/EC) and RoHS-2 (2011/65/EC) are also compliant with RoHS-3 (2015/863/EU).

# ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance, Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

# **RELATED LINKS AND DOCUMENTS**

Engineering Notebook: (<u>https://www.mill-max.com/engineering-notebooks/introduction-to-spring-loaded-pogo-pins-connectors</u>) Environmental Compliance: (<u>https://www.mill-max.com/rohs</u>)