

Features

- Universal Input 100~240VAC 50/60Hz
- IEC/EN/ANSI/AAMI ES 60601-1 (ED 3.1)
- EMC: IEC60601-1-2:2014(ED 4.0)
- Safety Approvals: cULus / UKCA / CB / PSE / FCC / CE / TUV / RoHS / REACH
- Means of Protection: 2 X MOPP
- Touch Current: < 100μA
- Single Output to 120W
- Regulated Output with Low Ripple Noise
- Safety Agency Requirements and EMI/EMS Certified
- Meets DoE Level VI, Energy Star, ErP Stage 2
- No Load Power Consumption Less Than 0.21W
- IEC C14 Connector
- Dimensions: L 168 x W 66 x H 39 (mm)
- Weight: 590g



The purpose of the document is to specify a Single-phase AC input, single output switching power supply. This specification is for: Desktop Power Supplies 120W Series. This product is suitable for use in medical applications. This Specification defines the input, output, performance characteristics, environment, noise and safety requirements.

Models			
Model Number	Output Voltage	Output Current	Output Power
44ATM120T-P120	12V DC	9A	108W
44ATM120T-P150	15V DC	8A	120W
44ATM120T-P180	18V DC	6.67A	120W
44ATM120T-P200	20V DC	6A	120W
44ATM120T-P240	24V DC	5A	120W
44ATM120T-P480	48V DC	2.5A	120W

General Specification

Туре	Switched Mode Power Supply
Input Connector	IEC 320-C14
Output Connection	4 Pin Kycon
Number of Outputs	1
Energy Efficiency Level	VI
Mounting Style	Desktop
MTBF	300,000 hours calculated at 25°C, by Telcoria SR-332
Power Indicator	LED Indicator for power on
Cable Length	1200mm(±30mm) – 1500mm(±30mm) Depending on Model
Cable Type	16AWG/18AWG/20AWG (Depending on model)
Medical Approved	Yes



44ATM120T-P 120W Desktop Series

Mechanical Specifications

Housing Material	Fully Enclosed Plastic Case
Overall Dimensions	168mm x 66mm x 39mm
Overall Length	168mm
Overall Height	39mm
Overall Width	66mm
Weight	590g

Input Specifications

Rated Input Voltage	100~240Vac (±10%)
Rated Frequency	50/60Hz
Efficiency Level VI	Level VI / Efficiency (EU) 2019/1782
Input Current	1.5A-0.7A
Inrush Current	100A Max. / 230Vac (Cold Start At 25°C, Full Load)
Touch Current	Less than 100μA
Input Protection	Internal Primary Current Fuse

Output Specifications

Output Regulation	±5%	_
Ripple & Noise (max.)	1% Vp-p Max. for Output Voltage @ Full Load (1.25% for 12V Model)	
Voltage Tolerance	±5%	_
Load Regulation	±5%	_
No Load Power Consumption	<0.21W	
Number of Outputs	1	
Insulation Class		_
Dielectric Strength	Primary to Secondary 4,000Vac for 1 Minutes	
Isolation Resistance	10M Ω for 500Vdc	
Short Circuit Protection	Auto-recovery	
Over Voltage Protection	V out * 150% MAX., latch off	
Over Current Protection	I out * 170% MAX., auto-recovery	_

Protection Category

Means of Protection	2 X MOPP	



44ATM120T-P 120W Desktop Series

Approvals

Compliance/Certifications	ations CB / cULus/ FCC / CE / UKCA / T-mark / TUV / PSE	
Safety Standard	IEC/EN/ANSI/AAMI ES 60601-1	
EMC Emission:	Directive 93/42/EEC (EN 60601-1-2)	

