

Harvatek Surface Mount CHIP LED Data Sheet B1191NG--20C000133U1930

Official Product	HT Part No. B1191NG20C000133U1930				
Tentative Product	********				
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 1/14	



PRODUCT SPECIFICATIONS	DISCLAIMER	3
LABEL SPECIFICATIONS	PRODUCT SPECIFICATIONS	4
PRODUCT SPECIFICATIONS	ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION	4
PRODUCT FEATURES ELECTRO-OPTICAL CHARACTERISTICS. PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW SOLDERING. ABSOLUTE MAXIMUM RATINGS. PRECAUTION FOR USE. CHARACTERISTICS OF B119NG. TAPE DIMENSION. REEL DIMENSION. PACKING. DRY PACK. BAKING. PRECAUTIONS. REFLOW SOLDERING. REWORKING. CLEANING.	LABEL SPECIFICATIONS	5
ELECTRO-OPTICAL CHARACTERISTICS. PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW SOLDERING	PRODUCT SPECIFICATIONS	6
PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW SOLDERING	PRODUCT FEATURES	7
SOLDERING ABSOLUTE MAXIMUM RATINGS PRECAUTION FOR USE CHARACTERISTICS OF B119NG PACKAGING TAPE DIMENSION REEL DIMENSION PACKING DRY PACK BAKING PRECAUTIONS REFLOW SOLDERING REWORKING CLEANING		
ABSOLUTE MAXIMUM RATINGS PRECAUTION FOR USE CHARACTERISTICS OF B119NG PACKAGING TAPE DIMENSION REEL DIMENSION PACKING DRY PACK BAKING PRECAUTIONS REFLOW SOLDERING REWORKING CLEANING		
PRECAUTION FOR USE CHARACTERISTICS OF B119NG PACKAGING TAPE DIMENSION REEL DIMENSION PACKING DRY PACK BAKING PRECAUTIONS REFLOW SOLDERING REWORKING CLEANING		
CHARACTERISTICS OF B119NG PACKAGING TAPE DIMENSION REEL DIMENSION PACKING DRY PACK BAKING PRECAUTIONS REFLOW SOLDERING REWORKING CLEANING		
TAPE DIMENSION REEL DIMENSION PACKING DRY PACK BAKING PRECAUTIONS REFLOW SOLDERING REWORKING CLEANING		
REEL DIMENSION	PACKAGING	10
PACKING DRY PACK BAKING PRECAUTIONS REFLOW SOLDERING REWORKING CLEANING	TAPE DIMENSION	10
DRY PACK Baking Precautions REFLOW SOLDERING Reworking Cleaning	REEL DIMENSION	11
BAKING PRECAUTIONS REFLOW SOLDERING REWORKING CLEANING	Packing	11
PRECAUTIONS REFLOW SOLDERING REWORKING CLEANING	DRY PACK	12
REFLOW SOLDERING	BAKING	12
REWORKINGCLEANING	PRECAUTIONS	12
CLEANING	REFLOW SOLDERING	13
	REWORKING	13
REVISE HISTORY	CLEANING	13
	REVISE HISTORY	14

Official Product	HT Part No. B1191NG20C000133U1930				
Tentative Product	********				
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 2/14	



DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

LIFE SUPPORT POLICY

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	HT Part No. B1191NG20C000133U1930				
Tentative Product	********				
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 3/14	



Product Specifications

	Specification	Material	Quantity
Luminous	NG:180.0-450.0 mcd		
Intensity(Iv)	@20mA/ T _s = 25°C ;Tolerance:±10%		
Wavelength	NG:520-535 nm		
	@20mA/ T_S = 25 $^{\circ}$ C; Tolerance: ±0.5nm		
Vf	NG:2.7-3.9 V(0.2V/BIN)		
	@20mA/ T _S = 25°C ;Tolerance:±0.05V		
Ir	< 10 µA @ V _R = 5 V		
Resin	Clear	Epoxy resin	
Carrier tape	EIA 481-1A specs	Conductive black tape	3000pcs per reel
Reel	EIA 481-1A specs	Conductive black	
Label	HT standard	Paper	
Packing bag	250x230mm	Aluminum laminated bag/ no-zipper	One reel per bag
Carton	HT standard	Paper	Non-specified

Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of Iv, λ_D and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

ATTENTION: Electrostatic Discharge (ESD) protection



The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlGaInP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must


be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.

Official Product	HT Part No. B1191NG20C000133U1930				
Tentative Product	********				
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 4/14	



Label Specifications



Harvatek P/N:

B 119 1 NG-- 20C- 0001 33

Product	Package	Dice Qty	Color	Current	Series Number	Taping
РСВ	3.2(L)x1.5(W)x1.0(H) mm	1:Single	NG:Green	20mA	X001~XZZZ	1.Taping style
						2. Qty

Lot No.:

1	2	3	4	5	6	7	8	9	10
E	1	Α	1	Α	2	2	L	1	2
Code	e 1 2	Code 3	Code 4	Code 5	Code 6	Code 7	Code 8	Code 9	Code 10
),	Mfg. Year	Mfg. Month	Mfg. Date	Consecuti	ve number		Special code	
Internal Tra	acing Code	2020-L 2021-M 2022-P 2023-Q 2026-T 2027-V 2030-Y 2031-Z	1:Jan. 2:Feb. A:Oct. B:Nov. C:Dec.	1:A 2:B 3:C 26:Z 27:7 28:8 29:9 30:3 31:4	01-	-ZZ		000~ZZZ	

Official Product	HT Part No. B1191NG20C000133U1930				
Tentative Product	*******				
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 5/14	



Product specifications

Luminous Intensity (Iv) Bin:

Color	Bin Code	Spec. Range
	s	180.0-285.0 mcd
NG	Т	285.0-360.0 mcd
	U	360.0-450.0 mcd

Note: It maintains a tolerance of ±10% on Luminous Intensity

Wavelength Bin:

Color	Bin Code	Spec. Range
	В	520.0-525.0 nm
NG	С	525.0-530.0 nm
	D	530.0-535.0nm

Note: It maintains a tolerance of ±0.5nm on Wavelength Bin

Forward Voltage (Vf) Bin:

Color	Bin Code	Spec. Range
	G8	2.7-2.9 V
	H7	2.9-3.1 V
NG	H8	3.1-3.3 V
NG	J7	3.3-3.5 V
	J8	3.5-3.7 V
	K7	3.7-3.9 V

Note: It maintains a tolerance of ±0.05V on forward voltage measurements

Official Product	HT Part No. B1191NG20C000133U1930			
Tentative Product	*********	******		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 6/14



Product Features


Electro-Optical Characteristics

(T_{Soldering}, 25 °C)

Corios	Emitting Color	Matarial	V _F (V) Wavelen		Waveleng	Wavelength λ(nm)		I _V (mcd)	Viewing
Series	Emitting Color	Material ty	typ	max	λ_{D}	λ_{P}	Δ λ	Typical	Angle $2\theta \frac{1}{2}$
B1191NG20	NG InGaN	In CoN	2.2	2.0	507	F20	40	205.0	X=140
		3.3	3.9	9 527	527 520	40	285.0	Y=115	

Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering

Unit: mm Tolerance: +/-0.1



Absolute Maximum Ratings

(T_{Soldering} 25 °C)

Series	P _D (mW)	I _F (mA)	I _{FP} (mA)*	T _{OP} (°C)	T _{ST} (°C)
Color	Power Dissipation	Forward Current	Pulse Forward	Operating	Storage
			Current	Temperature	Temperature
NB	78	20	80	-40~+85	-40~+100

^{*}Condition for I_{FP} is pulse of 1/10 duty and 0.1msec width

Official Product	HT Part No. B1191NG20C000133U1930			
Tentative Product	*********	********		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 7/14




Precaution for Use


- 1. The chips should not be used directly in any type of fluid such as water, oil, organicsolvent, etc.
- 2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
- 3. LEDs must be stored in a clean environment. A sealed container with a nitrogen atmosphere is necessary if the storage period is over 3 months after shipping.
- 4. The LEDs must be used within 4 weeks after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
- 5. The appearance and specifications of the products may be modified for improvement without further notice.
- 6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs. If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs. Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.


Official Product	HT Part No. B1191NG20C000133U1930			
Tentative Product	*********	********		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 8/14





Characteristics of B119NG
















Official Product	HT Part No. B1191NG20C000133U1930				
Tentative Product	*********	********			
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 9/14	



Packaging Tape Dimension




Dim. A	Dim. B	Dim. C	Qty/Reel
3.40±0.10	1.70±0.10	1.20±0.10	3К




Official Product	HT Part No. B1191NG20C000133U1930				
Tentative Product	*********	*********			
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 10/14	



Reel Dimension



Packing



5 or 10 boxes per carton is available depending on shipment quantity.

Official Product	HT Part No. B1191NG20C000133U1930			
Tentative Product	*********	********		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 11/14




Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

A humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



Baking

Baking before soldering is recommended when the package has been unsealed for 4 weeks. The conditions are as followings:

- 1. 60±3°C×(12~24hrs)and<5%RH, taped reel type.
- 2. $100\pm3^{\circ}$ C×(45min~1hr), bulk type.
- 3. 130±3°C×(15min~30min), bulk type.

Precautions

- 1. Avoid exposure to moisture at all times during transportation or storage.
- 2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlGaInP products.
- 3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
- 4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
- 5. Avoid direct contact with the surface through which the LED emits light.
- 6. If possible, assemble the unit in a clean room or dust-free environment.

Official Product	HT Part No. B1191NG20C000133U1930			
Tentative Product	*********	********		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 12/14




Reflow Soldering

Recommend soldering paste specifications:

- 1. Operating temp.: Above 217 °C ,60-150sec.
- 2. Peak temp.:260 °CMax.,10sec Max.
- 3. Reflow soldering should not be done more than two times.
- Never attempt next process until the component is cooled down to room temperature after reflow.
- 5. The recommended reflow soldering profile (measured on the surface of the LED terminal) is as following:

Lead-free Solder Profile



Reworking

- Rework should be completed within 5 seconds under 260 °C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50°C x 30sec. or <30°C x 3min
- Ultrasonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100 ^OC max, <3min

Official Product	HT Part No. B1191NG20C000133U1930			
Tentative Product	*********	*******		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 13/14



Cautions of Pick and Place

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

Revise History

Rev.	Descriptions	Date	Page
1.0	-	09/04/2017	-
1.1	Renew From	06/14/2022	-

Official Product	HT Part No. B1191NG20C000133U1930			
Tentative Product	********	********		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		06/14/2022	Version 1.1	Page 14/14