ONLY FOR REFERENCE

<u>Standard Spec Sheet</u>

Mitsumi Model Name	SOU-242HST
Mitsumi Model No.	R66 6939
Operating Force/ Boss	1.6N / With
Pcs/Reel	5,000


This specification is only for reference. If you have any questions for the details, please contact SW engineering division.

For your adopting the products, the formal supply specification will be provided.

MITSUMI ELECTRIC CO., LTD.

2-11-2, Tsurumaki, Tama-shi. Tokyo 206-8657 Japan.

SWITCH ENGINEERING SECTION 1049,Tateiwa,Iizuka-shi. Fukuoka 820-8533 Japan.



		(1/10)
APPROVED	CHECKED	WRITTEN
May.26.'08	May.26.'08	May.26.'08
SW	SW	SW

58EI

General Specification

1. GENERAL SCOPE

1-1 THE SCOPE OF APPLICATION

This specification covers the general requirements of mechanical and electrical characteristics of Side Click Type Tactile Switch mainly used as signal switch of electric devices.

1-2 TEST CONDITIONS

Tests and measurements shall be made in the following standard conditions unless otherwise specified. Normal temperature : 5 to 35°C

Normal humidity: Relative humidity 45 to 85%

In case any question arises from the judgment made, tests shall be conducted

the following conditions.

Temperature : 20+/-2°C, Humidity: 65 +/- 5%


2. APPEARANCE AND CONSTRUCTION

2-1 Outer dimensions: Refer to the attached drawing.

2-2 Materials: As shown in Table-1.

- 2-3 Appearance: There should be no critical crack, scratch, dirt, discoloration and contamination which affect the functional characteristics of the switch. If these problems don't affect the characteristics, the switch can be judged as a good one.
 - * There may be rare occasions when any substance such as a white stain attaches to the top of cover, but this substance is a constituent of quick-drying grease which doesn't affect the performance of switch.

2-4 Cross section



 \triangle 5%The switch with boss type is shown above as a typical drawing.



Part Name	Material	Remai	rks
(1) Cover	SUS		(SPUE)
(2) Slider	Nylon		21 Det
(3) Cover Tape	Polyimide		
(4) Switch base	Nylon		<u>3</u> 2016
(5) Spring	φ2.4 mm, SUS	Ni + Ag	The server
(6) Terminal	Phosphor bronze	Ag /q	- THE ET.
		Produ	ct weight:23mg $\sqrt{8}$
3. RATING	Maximum ratings 50mA, 12V D.C. (1	Resistive load)	<u></u>

NG Maximum ratings 50mA, 12V D.C. (Resistive load)

с	$\triangle 10 \times 2$	Oct.20th,'16	Change the bar code label to QR code label	Nakashima	Code	ID No.	File No.	
Revision	riangle 9 imes 4	Jan.15th,'15	Circuit symbol changed. The condition added to Operating Temperature range. PRECAUTIONS IN USE added.	Tsutsui	S	66	1385	
Ц	$\triangle 8 \times 1$	Mar.12th.'14	To 2-4 Addtion Product weight	Fujisaki	2	UU	1000	
			MITSUMI ELI	ECTRIC (CO., LTE).		S-0115

4. ELECTRICAL CHARACTERISTICS				
Items	Test conditions	Criteria		
4-1 Contact	Applying a below static load to the center of the stem, measurement			
Resistance	shall be made.			
	(1)Depression			
	:1.5 to 2 times the operating force of the standard center value			
	(2)Measuring method			
	: To be measured with A.C. 1kHz +/- 200Hz			
	(MAX. 20mV, 50mA)			
4-2 Insulation	Maggurger and shall be used a fallowing the test act farms halow	10 M ohm min.		
Resistance	Measurements shall be made following the test set force below: (1)Test voltage			
Resistance	:100 V DC for 1min.			
	(2)Applied position			
	:Between all terminals, between terminal and cover.			
4-3 Withstanding	Measurements shall be made following the test set force below	There shall be no damage and		
Voltage	(1)Test voltage	breakdown.		
	:100V AC (50/60Hz) for 1min.			
	(2)Leak current			
	:2mA			
	(3)Applied position			
	:Between all terminals, between terminal and cover.			
4-4 Bouncing	Lightly striking the center of the lengh of a rate	ON bounce :10ms. Max.		
4-4 Bouncing	Lightly striking the center of the knob at a rate encountered in normal use (3 to 4 operations per sec.),	OFF bounce: 10ms. Max.		
	bounce shall be tested at "ON" and "OFF".	OFF bounce. rollis. Max.		
	bounce shall be tested at ON and OFF .			
	^			
	I SW $\leq 5k\Omega$ Oscilloscope			
	DC5V			
	"ON""OFF"			
		SUA		
		13 50		
		(21.Oct)		
		2016		
		12 AVQUEELNO		
		File No.		
		1385		

(3/10)

	Test conditions	Criteria
5-1 Operating	Placing the switch such that the direction of switch operation	Refer to the attached drawing.
Force	is vertical and then gradually increasing the load applied to	
	the center of the stem, the maximum load required for the switch	
	to come to a stop shall be measured.	
	The measurement shall be made just after 10 times pushing.	
5-2 Return Force	The sample switch is installed such that the direction of switch operation	Refer to the attached drawing.
	is vertical and, upon depression of the stem in its center the whole travel	
	distance, the force of the stem to return to its free position shall be	
	measured.	
	The measurement shall be made just after 10 times pushing.	
5-3 Travel	Placing the switch such that the direction of switch operation is vertical	Refer to the attached drawing.
	and then applying a static load to the center of the stem, the travel	
	distance for the switch to come to a stop shall be measured.	
	The measurement shall be made just after 10 times pushing.	
5-4 Stopper	Placing the switch such that the direction of switch operation	There shall be no sign of damage
Strength	is vertical and then a below static load shall be applied in the direction	mechanically and electrically.
	of stem operation.	
	1) Depression: 30 N	
	2) Time: 15s	
	3) Push stick shape: As shown below. 0. 05mm	
	←	
5-5 Impact Proof	Measurements shall be made following the test set forth below.	There shall be no sign of damage
-	1) Acceleration: 735m/s2	mechanically and electrically.
	2) Acting time: 6 msec	
	3) Test direction: 6 directions	
	4) Cycles of test: 3 cycles per direction (18 cycles in total)	
5-6 Vibration	Measurements shall be made following the test set forth below.	There shall be no sign of damage
Resistance	1) Range of oscillation: 10 to 55 Hz	mechanically and electrically.
	2) Amplitude, pk-to-pk: 1.5 mm	
	3) Cycle of sweep: 10-55-10 Hz in approx. 1minute	
	4) Mode of sweep: Logarithmically sweep or uniform sweep	GSUR
	5) Direction of oscillation: Three mutually perpendicular directions,	
	including the direction of stem travel	(<u>*</u> (21.0ct),
	6) Duration of testing: 2 hours each, for a total of 6 hours	2016
		2 AVO/NEERING
		Eile No
		File No. 1385

Items	Test conditions	Criteria
-7 Solderability	Measurements shall be made following the test set force below:	More than 75% of the
	1) Soldering temperature: 230 +/- 5 degrees C	dipped part shall be covered
	2) Soldering time : 3 +/- 0.5 seconds	with solder.
	3) Solder : Sn-3.0Ag-0.5Cu	
	4) Soldering flux : Rosin 25%, Alcohol 75%	
5-8 Soldering heat	1) Hand soldering	There shall be no damage
Resistance	1-1) Temperature of soldering iron tip: 350 +/- 5 degrees C	on appearance.
	1-2) Soldering time: 3 +1/-0 seconds	Electrical performance in
	1-3) The soldering iron should be applied to the terminals.	Section 4 shall be assured.
	1-4) Excessive load should not be applied.	Operating force (Item 5-1)
	1-5) Power of the soldering iron should not exceed 15 W.	shall be assured.
	2) Reflow soldering	
	2-1) Heating method: Far-infrared heating	
	2-2) Temperature-time profile (Maximum value): As shown below.	
	2-3) Allowable soldering time: 2 times	
	Temp $[^{\circ}C]$ 250 230 180 150 90+/-30sec $30\pm10sec$	
	0 Profile of Reflow Soldering (Max) Time [sec]	
	The condition mentioned above is a temperature on the PWB surface on which parts are mounted. There are cases where board's temperature greatly differs from switch's surface temperature, depending on board's material, size, thickness, etc. Please care, therefore, should be used not to allow switch's surface temperature to exceed 250°C.	
	The above temperature profile is the conditions for heat resistance test. Therefore, conditions of soldering shall be confirmed under actual production conditions.	SSUE

- 1) Do not overheat when you solder with soldering iron.
- 2) Following the soldering process, do no try to clean the switch with a solvent or the like.
- 3) Safeguard the switch assembly against flux penetration from its top side.
- 4) As the conditions vary somehow on the kind of reflow soldering equipment, please make sure you have the right one before use.
- 5) As the click ratio may deteriorate when a high heat load is applied, reflow soldering should be performed in the shortest period and at the lowest temperature possible.
- 6) Please use the proper amount of solder in order to prevent the flux penetration into the switch.
- 7) Switch terminals and PWB upper face shall be free from flux prior to soldering.
- 8) Note that if the load is applied to the terminals during soldering it might cause deformation and defects in electrical performance.

File No.

VOINEER

1385

6. ENDURANCE		
Items	Test conditions	Criteria
6-1 Operating life	Measurements shall be made following the test set forth below :	Contact resistance: 10hm max.
1 0	(1) DC12V 50mA resistive load.	Insulation resistance:10M-ohm min.
	(2) Rate of operation: 2 operations per second.	Bounce: ON bounce 20 msec max.
	(3) Depression:	OFF bounce 20 msec max.
	: The maximum load of a specification of the operating force.	Withstanding voltage: Item 4-3
	(4) Cycles of operation: 100,000 cycles	Operating force: -30 to $+30\%$ of
	(5)Pusher	initial force
	: Material SUS, φ4.0 Tip: flat shape	Travel: Item 5-3
7. ENVIRONMEN	TAL	
Items	Test conditions	Criteria
7-1 Moisture	After testing at $+60+/-3$ °C and 90 to 96% in relative humidity for	Contact resistance: 10hm max.
Resistance	96 ± -5 hours, the sample is allowed to stand under normal	Insulation resistance: 10M-ohm min.
	temperature and humidity conditions within an hour, then,	Bounce: ON bounce 20 msec max.
	measurement shall be made within an hour.	OFF bounce 20 msec max.
	*Water drops shall be removed.	Withstanding voltage: Item 4-3
	water drops shan of removed.	Operating force: -30 to $+30\%$ of
7-2 Heat Resistance	After testing at +85+/-3 °C for 96 +/-5 hours, the sample is	initial force
7-2 Heat Resistance	allowed to stand under normal temperature and humidity	Travel: Item 5-3
	conditions within an hour, then, measurement shall be	Traver. Rem 3-3
	made within an hour.	
	made within an nour.	
7-3 Resistance to	After testing at -40+/-3 $^{\circ}$ C for 96 +/-5 hours, the sample is	-
Low Temperature		
Low Temperature	conditions within an hour, then, measurement shall be	
	made within an hour.	
	*Water drops shall be removed.	
7-4 Temperature	Following continuous five cycles of the temperature cycling test	-
Cycling	set forth below:	
Cycning	set forth below.	
	85+/-2°C	
	-40+/-3°C	
	120min 120min	
	4	
	10 to 15min 10 to 15min	
	1 cycle	
		SSUE
		(21.Oct))
		2016
		MO/NEERIN"
		File No. 1385
		1303

/9\

8. USE CONDITIONS 8-1 Operating temperature range: -40 to +60°C. No freeze and condensation.

(Temperature range which the switch is electrically ON and OFF.)

8-2 Using Environment

- 1) Do not expose the switch to corrosive gas such as sulfur gas, and salty wind.
- 2) Visible dust must be cleared.
- 3) As the switch may deform and change its quality, please do not apply excessive force to the switch.

9. STORAGE CONDITIONS

9-1 Storage temperature: -25 to 85° C. Storage Relative humidity: 10 to 75%. No freeze and condensation. $\triangle 6$ 9-2 Using Environment

- 1) Do not expose the switch to corrosive gas such as sulfur gas, and salty wind.
- 2) Visible dust must be cleared.
- 3) As the switch may deform and change its quality, please do not apply excessive force to the switch.
- 9-3 Storage Method
 - 1) Store the switches in the following condition: Seal up with plastic bags in a taping state, $\triangle 6$
 - 2) Do not stack too many switches for strafe. Shall be free from high temperature and high humidity.
 - 3) The operating part of the switch should be free position in storage.
- 9-4 Retention period: 1 year $\triangle 6$

10. PRECAUTIONS IN USE

- 10-1 Do not clean the switch with a solvent or the like.
- 10-2 Never use the product beyond the rated current and voltage.
- 10-3 Do not apply excessive load to the terminals and the operating part.
- 10-4 Larger stress than specified and/or shock shall not be applied to the operating part.
- 10-5 The stress shall be not applied to the upper face of the switch.
- 10-6 The switch will be broken, if you give larger stress than specified while operating. Take most care not to give both upward and downward stress to the switch when you operate it.
- 10-7 As the switch may be broken, please do no apply a load of more than 5N to the switch bosses.
- 10-8 After mounting the switches on PWBs, please do not stack too many PWBs in order to avoid excessive load to the switch mounted area.
- 10-9 The dimensions of a pattern for mounting a printed circuit board shall refer to the recommended dimensions in the outline drawing.
- 10-10 Use of organic acid flux shall be avoided because it may cause corrosion of the switch. Please make sure the type of flux before you use it.
- 10-11 As this switch is designed for reflow soldering, if you place it at the edge of PWB for convenience, then flux may get into the sliding part of the switch during automatic dip soldering after being mounted, so do not apply auto dip after being mounted.
- 10-12 If the switch is given stress from the side, the cover may drop off and it may result in damages to switch functions. Therefore, please handle it with extreme care.
- 10-13 The operating part should be moved to the appointed position in order to ensure proper operation.
- 10-14 Do not give stress to the upper face of the switch while operating and use the switch under given stress.
- 10-15 If you use this product in one of the following environmental conditions, progress of sulfaration and oxidization on the contact part (silver) will be accelerated, which may cause contact failure. Therefore, be careful about the operation environment.

1) Around a sulfarate hot spring where sulfide gas is generated.

- 2) In case this product is always used in a place where exhaust gas from automobiles exist.
- 10-16 If you push the edge of the operating part, the switch might not operate properly. Therefore, pressure to the operating part shall be applied to the whole surface equally and avoid the pressured to the specific one portion.




Figure-4

File No.



MITSUMI ELECTRIC CO., LTD.

10-17 Unless provided for otherwise, the products have been designed and manufactured for application in equipment and devices which are sold to end users in the market, including audio-visual (AV) equipment, electrical home appliances, office machines, information and communication equipment, and amusement equipment. The products are not intended for use in, and must not be used for, any application for nuclear equipment, driving equipment for aerospace or any other unauthorized use. With the exception of the abovementioned prohibited applications, please contact our sales representative and/or evaluate the total system regarding applicability for applications involving high levels of safety and liability such as medical equipment, burglar alarm equipment, disaster prevention equipment and undersea equipment. Please also incorporate fail-safe design, protection and redundant circuitry, malfunction protection, and/or fire protection into the complete system to ensure safety and reliability of the total system.



File No.

1385

11. MANUFACTURING LOCATION

<Sales Section>

MITSUMI ELECTRIC CO.,LTD.

2-11-2 Tsurumaki, Tama-shi, Tokyo, Japan

- <Management Section>
 - MITSUMI ELECTRIC CO., LTD., Kyushu Business Division

1049 Tateiwa, Iizuka-shi, Fukuoka, Japan

- <Manufacturing Section>
- QINGDAO MITSUMI ELECTRIC CO., LTD.
- No.3 Industrial Area, Chang Jiang Road Qingdao Economic & Technical Development Zone,
- -Qingdao, The people's Republic of China


QINGDAO MITSUMI ELECTRONICS CO., LTD. arrow 7


No.2, Dayangzhou Road, Qingdao West Coast Export Processing Zone, Qingdao city,

Shandong Province, People's Republic of China $ext{ } ext{ } ext{$

12. TAPE PACKING SPECIFICATION

- 12-1 Carrier tape dimensions are shown below.
- 12-2 Taping Procedure
 - 1) Tape winding direction is in clockwise. (When pulling the tape toward, feeding holes should be located on the right side.)
 - 2) Feeding holes shall not be covered with the cover tape. The cover tape shall not be run off the edge of the carrier tape.
 - 3) 100 to 190 mm from the end of tiller tape part shall be empty and 100 to 140 mm from the end of leader tape part shall be empty. Leader part consists of the part which unstuck with cover-tape (20 to 30 mm) and the cover tape shall be extended 150 to 200 mm.
 - 4) After reeling, stick the leader part of cover tape to the side of the reel with adhesive tape (30 to 50 mm)
 - 5) Peeling strength of cover-tape from carrier-tape is 0.1to 1.3N at 165 to 180deg. angle in reverse.
 - 6) Switch shall be packed in single direction.
 - 7) 5000 switches shall be pack in a reel.
 - 8) The label which indicates our model number, part number, contained quantity and inspection number shall be stuck on the side of the reel.
 - 9) The switch shall drop by itself when it is pushed with a force of 0.1 to 0.2 from the back after peeling the cover tape.





MITSUMI ELECTRIC CO., LTD.

