

# 0153-01XX PCB Terminal Blocks > PCB Terminal Blocks

Date:2022-06-09Version:V1



The web catalog is for reference only. Dinkle remains the right of product modification and engineering change of the design. The final product is made according to engineering drawing.

#### **Product Description**

Pitch : 5.00mm, 300V, 20A

#### General information

| Short description                      | PCB Terminal Blocks, Push-in Design |
|--|-------------------------------------|
| Category                               | PCB Terminal Blocks                 |
| Pitch (mm)                             | 5.00                                |
| Color                                  | Black (default)                     |
| Connection method                      | Push in design                      |
| Type of locking                        | Without                             |
| Soldering method                       | Wave soldering                      |
| Length (mm)                            | 5.00*(P-1)+6.5                      |
| Width (mm)                             | 16                                  |
| Height (mm)                            | 18                                  |
| Pin demensions (Thickness x Width)(mm) | 0.7x1.2                             |
| PCB hole diameter (mm)                 | 1.0x1.8                             |
| Number of positions                    | 02P~24P                             |
| Level                                  | Single level                        |

#### Material information



| Insulation material                          | PA                |
|--|-------------------|
| Insulation material group                    | Ι                 |
| Flame retardant rating , compliant with UL94 | VO                |
| Insulation resistance                        | 0500MΩ at DC 500V |
| Conductor material                           | COPPER ALLOY      |
| Plating of conductor surface                 | Tin PLATED        |

#### Connection data-IEC

| Rated voltage (V)   | 320     |
|---|---------|
| Rated current (A)   | 24      |
| Rated voltage (II/2)(V)   | 500     |
| Rated voltage (III/2) (V)   | 320     |
| Rated voltage (III/3)(V)  | 250     |
| Rated impulse voltage (II/2)(KV)  | 4       |
| Rated impulse voltage (III/2)(KV)   | 4       |
| Rated impulse voltage (III/3)(KV)   | 4       |
| Conductor cross section solid. min (mm <sup>2</sup> )   | 0.2     |
| Conductor cross section solid.max (mm <sup>2</sup> )  | 2.5     |
| Conductor cross section stranded. min (mm <sup>2</sup> )  | 0.2     |
| Conductor cross section stranded. max (mm <sup>2</sup> )  | 2.5     |
| Conductor cross section flexible, with min ferrule without plastic sleeve (mm <sup>2</sup> )            | 0.2     |
| Conductor cross section flexible, with max ferrule without plastic sleeve (mm <sup>2</sup> )            | 2.5     |
| Conductor cross section flexible, with min ferrule with plastic sleeve (mm <sup><math>2</math></sup> )  | 0.2     |
| Conductor cross section flexible, with max ferrule with plastic sleeve ( $mm^2$ )                       | 2.5     |
| 2 conductors with same cross section flexible, min twin ferrules with plastic sleeve (mm <sup>2</sup> ) | 0.5     |
| 2 conductors with same cross section flexible, max twin ferrules with plastic sleeve (mm <sup>2</sup> ) | 1.5     |
| Slotted screwdriver size (Blade thickness x Width)(mm)  | 0.6x3.5 |
| Stripping Length (mm)   | 12~14   |

#### Connection data-UL

| Rated voltage (UL/CUL Group B)(V) | 300 |
|-----------------------------------|-----|
| Rated current (UL/CUL Group B)(A) | 20  |



| Rated voltage (UL/CUL Group D)(V)                | 300 |
|--|-----|
| Rated current (UL/CUL Group D)(A)                | 10  |
| Min. solid wire connection (AWG) acc. to UL/CUL  | 24  |
| Max. solid wire connection AWG acc. to UL/CUL    | 12  |
| Min. stranded wire connection AWG acc. to UL/CUL | 24  |
| Max. stranded wire connection AWG acc. to UL/CUL | 12  |

#### Environment & Safety

| Finger protection (YES or NO)   | YES |
|---------------------------------|-----|
| Operating temperature. max (°C) | 120 |
| Operating temperature. min (°C) | -40 |

#### **UL** Recognized

| Wire Range (Group B)(AWG)              | 24~12 |
|--|-------|
| Rated voltage (Group B)(V)             | 300   |
| Rated current (Group B)(A)             | 20    |
| Wire Range (Group D)(AWG)              | 24~12 |
| Rated voltage (Group D)(V)             | 300   |
| Rated current (Group D)(A)             | 10    |
| ······································ |       |

### CUL Recognized


| Wire Range (Group B)(AWG)  | 24~12 |
|----------------------------|-------|
| Rated voltage (Group B)(V) | 300   |
| Rated current (Group B)(A) | 20    |
| Wire Ranget (Group D)(AWG) | 24~12 |
| Rated voltage (Group D)(V) | 300   |
| Rated current (Group D)(A) | 10    |

#### VDE Approval

| Wire Range (mm <sup>2</sup> ) | 0.2~2.5 |
|-------------------------------|---------|
| Rated voltage (V)             | 320     |
| Rated current (A)             | 24      |

## Drawings





## Approvals





CE

