

Cable marker - MM-WMT 8,4 (17X10)R C1 WH/BK - 1116194

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Cable marker, Roll, white, unlabeled, can be labeled with: THERMOMARK GO, mounting type: insert, cable diameter range: 5 ... 8.4 mm, lettering field size: 16 mm x 7.4 mm, Number of individual labels: 260

Product Description

Prepunched MM-WMT... conductor markers made of polyester are slid onto the conductors and cannot break off.

Your advantages

- The pre-punched geometry enables easy and convenient use
- Thanks to the innovative material composition, each label can be printed which results in zero wastage
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- No visible difference between retrospective marking and existing markings created with a desktop roll printer
- The conductor is simply pushed through the two punch-outs on the marker. In this way, the marker is aligned on the conductor.
- The special hole geometry for different conductor gauges ensures strong axial support
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing



Key Commercial Data

Packing unit	1 pc
GTIN	4 063151 042028
GTIN	4063151042028
Custom tariff number	96121010
Country of origin	China

Technical data

Dimensions

Length (b)	10.4 mm
Width (a)	44.4 mm



Cable marker - MM-WMT 8,4 (17X10)R C1 WH/BK - 1116194

Technical data

Dimensions

Cable dameter		5 mm 8.4 mm
---------------	--	-------------

Ambient conditions

Ambient temperature (operation) -40 °C 120 °C

General

Color	white
Components	free from silicone, halogen, and cadmium
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	260
Marking mounting type	insert

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 11.0	27281102
eCl@ss 9.0	27400401

Phoenix Contact 2021 © - all rights reserved http://www.phoenixcontact.com