

Cable marker - MM-WML 5 (24X10)R C1 WH/BK - 1116196

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Cable marker, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO: without print, mounting type: adhesive, lettering field size: 22 x 9.5 mm, Number of individual labels: 235

Product Description

MM-WML... vinyl polymer self-adhesive labels are available as prepunched material for wire marking.

Your advantages

- The pre-punched geometry enables easy and convenient use
- Thanks to the innovative material composition, each label can be printed which results in zero wastage
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- No visible difference between retrospective marking and existing markings created with a desktop roll printer
- The transparent protective foil is wound over the marking and provides permanent protection against contamination and abrasion
- The wrap-around labels do not add bulk, which means that the cable can still be drawn through cable ducts, for example
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing



Key Commercial Data

Packing unit	1 pc
GTIN	4 063151 039899
GTIN	4063151039899
Weight per Piece (excluding packing)	40.000 g
Custom tariff number	96121010
Country of origin	China

Technical data

Dimensions



Cable marker - MM-WML 5 (24X10)R C1 WH/BK - 1116196

Technical data

Dimensions

Length (b)	24 mm
Width (a)	25.4 mm
Cable diameter	≤ 5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C 80 °C
I Recommended storage conditions	21 °C / 50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Color	white/black
Components	Free from silicone and cadmium
Material	Vinyl polymer
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	without print
Number of individual labels	235
Marking mounting type	adhesive

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 11.0	27281102
eCl@ss 9.0	27400401

Approvals

Approvals

Approvals

cULus Recognized

Ex Approvals



Cable marker - MM-WML 5 (24X10)R C1 WH/BK - 1116196

Approvals

Approval details

cULus Recognized



http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

MH48542

Phoenix Contact 2021 © - all rights reserved http://www.phoenixcontact.com