

SUNON

SPECIFICATION FOR APPROVAL

CUSTOMER Sunon Inc.

MOTOR TYPE

MagLev Motor Fan **DESCRIPTION**

DIMENSIONS 17X17X3 mm

MODEL UF3H3-500

SUNON SPEC. NO. D01000881F-01

CUSTOMER UF3H3-500 TC

APPROVAL NO. **APPROVED BY**

CUSTOMER (AUTHORIZED)

					SPEC.NO	D01000881F-01	
	Alice-			ISSUE DATE	10.19.2018		
	chang	chang CHECKED Chin-jung	Chin-jung APP	APPROVED	Chin-jung	EDITION	0
	10/19				REVISION DATE		
				E.SPEC	E30900094		

建準電機工業股份有限公司

SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.

NO. 30, LN. 296, XINYA RD., QIANZHEN DIST., TEL:886-7-8135888

KAOHSIUNG CITY 80673, TAIWAN (R.O.C) FAX:886-7-8230505/8230606/8231010

URL:http://www.sunon.com E-mail: sunon@email.sunon.com.tw



DC BRUSHLESS FAN MODEL: UF3H3-500

CHARACTERISTICS

1. Motor Design : Single phase, 6-poles Brushless DC motor

2. Insulation Resistance : More than 20M ohm between internal stator and

lead wire(+) measured at DC 100V.

3. Dielectric Strength : Applied AC 500V for one minute or AC 600V for

2 seconds between housing and lead wire(+)

4. Noise Level : Measured in a semi-anechoic chamber

with background noise level below 15

dB(A). The fan is running in free air with the

microphone at a distance of one meter

from the fan intake.

5. Input Power, Current & Speed : Measured after continuous 10 minute

operation at rated voltage in clean air, and

at ambient temperature of 25 degrees C.

6. Tolerance +20% / -30% on rated power and current.

7. Air Performance : Measured by a double chamber. The values

are recorded when the fan speed has stabilized

at rated voltage.

建準電機工業股份有限公司	SPEC.NO	D01000881F-01	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.19.2018	EDITION	0
MACHINE INDUSTRY CO., LTD.	PAGE	2 OF 12		



SPECIFICATIONS

MODEL: UF3H3-500

1-1. Rated Voltage : 3 VDC

1-2. Operating Voltage Range : 2.0~3.5 VDC

1-3. Starting Voltage : 2.0 VDC (25 deg. C POWER ON/OFF)

1-4. Rated Speed : 13000 RPM ± 30%

1-5. Air Delivery : 16.27 l/min

1-6. Static Pressure : 21.21 Pa

1-7. Rated Current : 37 mA

1-8. Rated Power : 0.1 WATTS

1-9. Noise Level : 21.8 dB(A) @ 1M

32.0 dB(A) @ 0.3M

1-10. Direction of Rotation : Counter-clockwise viewed from front of fan blade

1-11. Operating Temperature : -10 to +70 deg. C

1-12. Storage Temperature : -40 to +70 deg. C

1-13. Bearing System : Vapo bearing system

1-14. Weight : 1.27 g

1-15. Safety : CE Approvals

1-16. Protection :

☑ Automatic Restart Capability

Note: In a situation where the fan is locked by an external force while the electricity is on, an increase in coil temperature will be prevented by temporarily turning off the electrical power to the motor. The fan will automatically restart when the locked rotor condition is released.

☑Polarity Protection

1-17. IP Class: IP55 : According to IEC 60529 (or IEC 34-5) IP standard, the average

temperature is 23~24°C and humidity is 67% RH for Dust Water Test. The fan needs to be test and Spray Put in dust box for 8 hours for Dust Test and be sprayed low pressure jets of water from all directions for Spray Water Test. After these 2 tests, which executing by regular standard, the fan will be measured the performance is normal or not. PS. There are different applicative environments and systems by different customers, so please put the product in the most suitable

environment to measure the performances.

建準電機工業股份有限公司 SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.


SPEC.NO	D01000881F-01	REVISION DATE	
ISSUE DATE	10.19.2018	EDITION	0
PAGE	3 OF 12		



MODEL: UF3H3-500

PERFORMANCE CURVES

STATIC PRESSURE



建準電機工業股份有限公司	SPEC.NO	D01000881F-01	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.19.2018	EDITION	0
MACHINE INDUSTRY CO., LTD.	P A G E	4 OF 12		



MATERIAL

2-1. Frame : Thermoplastic LCP of UL 94V-0

2-2. Impeller : Thermoplastic LCP of UL 94V-0


2-3. Lead Wire : UL10064,32 awg,+RED,-BLACK

UL10064,32 awg,YELLOW:3rd Wire

DIMENSIONS

Note: SUNON recommends the screw and torque as below. Please contact SUNON, if any new requirement is requested.

Screw Type (Pan head) Torque		Screw Spec		
Machine screw	0.5 x 0.7 V af am	Size	Standard	
	0.5∼0.7 Kgf-cm	M1.7	JIS B1111-1974	




Note: The glues on the impeller is for impeller balance.

Please don't remove it.



Marking (By laser):
SUNON
UF3H3-500 TC:Model name
Production serial number:0Y17xxxxxx
0:Printing Plant Code
Y:Manufacture Plant
17:Year,2017=17
xxxxxx: Producing Lot No.
QR code :Content according to
SUNON QR code specification
TC:CUSTOMER NUMBER



Sunon standard sample exclude the connector. If there is any request for connector, please advise in advance.

About recommend connector, SUNON recommend the following models for SUNON Mighty Mini Fon/Blower:

1.(JST) SUR series connector: 02SUR-32S / 03SUR-32S / 04SUR-32S.

Best Mounting Direction: Any orientation.

UNIT: mm

建準電機工業股份有限公司	SPEC.NO	D01000881F-01	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.19.2018	EDITION	0
MACHINE INDUSTRY CO., LTD.	P A G E	5 OF 12		

ΔV	1 +	3. 0	o v	N	ORM			3	M
	and state (1955 and 1940 time on 19			a de sei riso su las sos ma pa		e dan dan dan san sali siya	and the are use the la	. 40 000 000 000 000 000 000	
	-	Ţ	1 T2	2 T3	T 4	T 5	T ₆	· · · · · · · · · · · · · · · · · · ·	.

T=1 Rotation

$$T=T1+T2+T3+T4+T5+T6=(1 Rotation)$$


$$T= \frac{60}{\text{rpm}}$$


建準電機工業股份有限公司	SPEC.NO	D01000881F-01	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.19.2018	EDITION	0
MACHINE INDUSTRY CO., LTD.	P A G E	6 OF 12		



FAN 3rd WIRE SIGNAL

• F Type (Frequency Generator)





★Electrical Characteristics : (at $Ta = 25^{\circ}C$, $V_{CC}=3V$)

Parameter		Ratings	Unit	
Farameter	min	typ.	max	Omt
FG Supply Voltage(V+)			3.5	Voltage
FG Output Current (If)			4	mA
FG Output (VL)			0.5	Voltage
FG Output (VH)		V+		Voltage

建準電機工業股份有限公司	SPEC.NO	D01000881F-01	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.19.2018	EDITION	0
MACHINE INDUSTRY CO., LTD.	PAGE	7 OF 12		



I .SAFETY

- 1. DO NOT use or operate this fan in excess of the limitations set forth in this specification. SUNON is not responsible for the non-performance of this fan and/or any damages resulting from its use, if it is not used or operated in accordance with the specifications.
- 2. SUNON recommends adding a protection circuit to the product or application in which this fan is installed, such as a thermo-fuse, or current-fuse or thermo-protector. The failure to use such a device may result in smoke, fire, electric shock by insulation degradation in cases of motor lead short circuit, overload, or over voltage, and/or other failure.
- 3. SUNON recommends installing a protection device to the product or application in which this fan is installed if there is a possibility of reverse-connection between VDC (+) and GND (-). The failure to install such a device may result in smoke, fire, and/or destruction, although these conditions may not manifest immediately.
- 4. This fan must be installed and used in compliance with all applicable safety standards and regulations.
- 5. Use proper care when handling and/or installing this fan. Improper handling or installation of this fan may cause damage that could result in unsafe conditions.
- 6. Use proper care during installation and/or wiring. Failure to use proper care may cause damage to certain components of the fan including, but not limited to, the coil and lead wires, which could result in smoke and/or fire.
- 7. DO NOT use power or ground PWM to control the fan speed. If the fan speed needs to be adjusted, please contact SUNON to customize the product design for your application.
- 8. For critical or extreme environments, including non stop operation, please contact SUNON and we will gladly provide assistance with your product selection to ensure an appropriate cooling product for your application.

建準電機工業股份有限公司	SPEC.NO	D01000881F-01	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.19.2018	EDITION	0
MACHINE INDUSTRY CO., LTD.	P A G E	8 OF 12		



II. SPECIFICATION MODIFICATION

- 1. SUNON offers engineering assistance on fan installation and cooling system design.
- 2. All changes, modifications and/or revisions to the specifications, if any, are incorporated in the attached specifications.
- 3. No changes, modifications and/or revisions to these specifications are effective absent agreement, by both SUNON and the customer, in writing.
- 4. This fan will be shipped in accordance with the attached specification unless SUNON and the customer have agreed otherwise, in writing, as specified in Paragraph 3, above.

III. OTHER

- 1. When building your device, please examine thoroughly any variation of EMC, temperature rise, life data, quality, etc. of this product by shock/drop/vibration testing, etc. If there are any problems or accidents in connection with this product, it should be mutually discussed and examined.
- 2. Use proper care when handling this fan. Components such as fan holders or bearings may be damaged, if touched with fingers or other objects. Additionally, static electricity (ESD) may damage the internal circuits of the fan.
- 3. DO NOT operate this fan in proximity to hazardous materials such as organic silicon, cyanogens, formalin, phenol, or corrosive gas environments including, but not limited to, H2S, SO2, NO2, or Cl2.
- 4. SUNON recommends that you protect this fan from exposure to outside elements such as dust, condensation, humidity or insects. Exposure of this fan to outside elements such as dust, condensation, humidity or insects may affect its performance and may cause safety hazards. SUNON does not warrant against damage to the product caused by outside elements.

Re: The term can be excluded, if the fan has been with IP design and meets customer's IP requirement.

建準電機工業股份有限公司	SPEC.NO	D01000881F-01	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.19.2018	EDITION	0
MACHINE INDUSTRY CO., LTD.	PAGE	9 OF 12		



- 5. This fan must be installed properly and securely. Improper mounting may cause harsh resonance, vibration, and noise.
- 6. Fan guards may prevent injury during handling or installation of the fan and are available for sale with this fan.
- 7. Unless otherwise noted, all testing of this fan is conducted at 25°C ambient temperature and sixty-five percent (65%) relative humidity.
- 8. DO NOT store this fan in an environment with high humidity. This fan must be stored in accordance with the attached specifications regarding storage temperature. If this fan is stored for more than 6 months, SUNON recommends functional testing before using.
- 9. SUNON reserves the right to use components from multiple sources at its discretion. The use of components from other sources will not affect the specifications as described herein.
- 10. The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy Test Reports (L10 and MTTF Report) that relate to this fan are only for reference.

VI. WARRANTY

This fan is warranted against all defects which are proved to be fault in our workmanship and material for one year from the date of our delivery. The sole responsibility under the warranty shall be limited to the repair of the fan or the replacement thereof, at SUNON's sole discretion. SUNON will not be responsible for the failures of its fans due to improper handing, misuse or the failure to follow specifications or instructions for use. In the event of warranty claim, the customer shall immediately notify SUNON for verification. SUNON will not be responsible for any consequential damage to the customer's equipment as a result of any fans proven to be defective.

建準電機工業股份有限公司	SPEC.NO	D01000881F-01	REVISION DATE	
SUNONWEALTH ELECTRIC	ISSUE DATE	10.19.2018	EDITION	0
MACHINE INDUSTRY CO., LTD.	P A G E	10 OF 12		



Declaration of Restricted Materials

Control declaration of environment- related substances/ materials

1. In accordance with the Restriction of Hazardous Substances (RoHS) Directive 2011/65/EU and specific market requirements, SUNON Halogen-Free Product have complied with law and discipline not to employ the forbidden substances, and restrict the allowable concentration of some limited substances deliberately in our components.

No		Substance	Criteria
1	CFCs & HCFCs (ozone depleting substances)		Forbidden
2	Chlorinated Organic Solvent		Forbidden
		Plastic (Frame, Impeller, wire harness, etc.)	<100ppm
	Lead and its compounds	Solder	<1000ppm
3		Steel alloy	<3500ppm
		Aluminium alloy	<4000ppm
		Copper alloy	<4wt%
		Solder	<20ppm
4	Cadmium and its	Parts composed of metals containing zinc	<100nnm
4	compounds	(e.g. brass, zinc for die casting)	<100ppm
		Plastic	<5ppm
5	PBBs and PBDEs		Forbidden
6	PCB and PCT		Forbidden
7	CP, Short-chain Chlorina	ted paraffins C10-13, Cl≥48 wt%	Forbidden
8	Mirex		Forbidden
9	PCN	Forbidden	
10	Hexavalent Chromium co	mpounds	<100ppm
11	Mercury and its compoun	Forbidden	
12	Asbestos	Forbidden	
13	Organic Tin compounds		Forbidden
14	Azo compounds		Forbidden
15	TBBP-A in external case	plastic parts of products (PCB is exempted)	<1000ppm
16	Nickel in external case parts, which are likely to result in prolonged skin exposure		<1000ppm
17			<1000ppm
18	Di-butyl Phthalate (DBP)		<1000ppm
19	Benzyl butyl Phthalate (BBP)		<1000ppm
20			<1000ppm
21	Di-isobutyl Phthalate (DIBP)		<1000ppm
	Brominated/chlorinated flame retardants (other than PBBs or PBDEs),		Br<900ppm
22	applicatable item: frame,	Cl<900ppm	
	insulator.	Br+Cl<1500ppm	
23	PAHs and its 16 compounds in unusual contact material		BaP < 20ppm
		Total <200ppm	
	PCB and electroplating material, PFOS content complianced with		PFOS ≤1000ppm;
24	2006/122/EC	coating material	
		$PFOS \leq 1 \mu g/m^2$	

建準電機工業股份有限公司	SPEC.NO	D01000881F-01	REVISION DATE	
	ISSUE DATE	10.19.2018	EDITION	0
MACHINE INDUSTRY CO., LTD.	P A G E	11 OF 12		









Don't cut the fan or lead wires




Handle with care!



Don't push the fan blade.







Don't pull fan with lead wires.







Don't dump fans on top of each others and keep away from humid area.





建準電機工業股份有限公司			
SUNONWEALTH ELECTRIC			
MACHINE INDUSTRY CO., LT	D.		

	SPEC.NO	D01000881F-01	REVISION DATE	
	ISSUE DATE	10.19.2018	EDITION	0
).	PAGE	12 OF 12		