

Micro Commercial Components



Micro Commercial Components 20736 Marilla Street Chatsworth CA 91311

Phone: (818) 701-4933 (818) 701-4939

Min

Max

2N6107

Features

- Halogen free available upon request by adding suffix "-HF" Lead Free Finish/RoHS Compliant (Note1) ("P" Suffix designates RoHS Compliant. See ordering information)
- Epoxy meets UL 94 V-0 flammability rating
- Moisure Sensitivity Level 1
- Marking:2N6107
- Mounting Torgue: 5 in-lbs Maximum

Maximum Ratings*

Symbol	Rating	Unit			
V_{CEO}	Collector-Emitter Voltage	V			
V_{CBO}	Collector-Base Voltage	tor-Base Voltage 80			
V_{EBO}	Emitter-Base Voltage	5.0	V		
lc	Collector Current, Continuous Peak	7.0 10	А		
l _B	Base Current	3.0	Α		
TJ	Operating Junction Temperature	-55 to +150	°C		
T _{STG}	Storage Temperature	-55 to +150	°C		

Thermal Characteristics

Symbol	Rating	Max	Unit
P_{D}	Total Device Dissipation	40	W
	Derate above 25°C	0.32	W/oC
R _{JC}	Thermal Resistance, Junction to Case	3.125	°C/W

Electrical Characteristics @ 25°C Unless Otherwise Specified

Parameter

OFF CHARACTERISTICS				
$V_{CEO(sus)}$	Collector-Emitter Breakdown Voltage (Note 2)			
	(├=100mAdc, ⊧=0)	70		Vdc
ρεο	Collector Cutoff Current			
	$(V_{CB}=60Vdc, I_{E}=0)$		1.0	mAdc
I _{CEX}	Collector Cutoff Current			
	$(V_{CE}=80Vdc, V_{EB(off)}=1.5Vdc)$		100	μΑ
	(V _{CE} =70Vdc, V _{EB(off)} =1.5Vdc, T _C =125 ^O C)		2.0	mA
I _{EBO}	Emitter Cutoff Current			
	$(V_{EB}=5.0Vdc, \ c=0)$		1.0	mAdc
22				

ON CHARACTERISTICS(1)

Symbol


011 011/110/1	OTENIOTIOS			
h _{FE}	DC Current Gain			
	$(V_{CE}=4.0Vdc, I_{C}=2.0Adc)$	30	150	
	(V _{CE} =4.0Vdc, I _C =7.0Adc)	2.3		
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage			Vdc
	$(l_c=7.0Adc, l_B=3.0Adc)$		3.5	vuc
V _{BE(on)}	Base-Emitter On Voltage			Vdc
	(b=7.0Adc, V _{oc} =4.0Vdc)		3.0	vac

*Indicates JEDEC Registered Data

Notes: 1. High Temperature Solder Exemption Applied, see EU Directive Annex 7.

2. Pulse Test: Pulse Width<300us, Duty Cycle<2.0%

PNP Silicon Complementary Power Transistor



DIMENSIONS					
	INCHES		N	MM	
DIM	MIN	MAX	MIN	MAX	NOTE
Α	.560	.625	14.22	15.88	
В	.380	.420	9.65	10.67	
С	.140	.190	3.56	4.82	
D	.020	.045	0.51	1.14	
F	.139	.161	3.53	4.09	Ø
G	.190	.110	2.29	2.79	
Н		.250		6.35	
J	.012	.025	0.30	0.64	
K	.500	.580	12.70	14.73	
L	.045	.060	1.14	1.52	
N	.190	.210	4.83	5.33	
Q	.100	.135	2.54	3.43	
R	.080	.115	2.04	2.92	
S	.045	.055	1.14	1.39	
T	.230	.270	5.84	6.86	
U		.050		1.27	
V	.045		1.15		





Symbol	Parameter	Min	Max	Units	
DYNAMI	DYNAMIC CHARACTERISTICS				
f _⊤	Current Gain- Bandwidth Product ⁽²⁾ $(I_C=500\text{mAdc}, V_{CE}=4.0\text{Vdc}, f=1.0\text{MHz})$	10		MHz	
Cob	Output Capacitance (V _{CE} =10Vdc, $ mathbb{t}_{=}$ =0, f=1.0MHz)		250	pF	
h _{fe}	Small-Signal Current Gain (I_C =0.5Adc, V_{CE} =4.0Vdc, f=50KHz)	20			

⁽²⁾ f_T=|hfe| X f_{test}




Figure 1. Power Derating




Figure 2. Turn-On Time




Figure 3. Turn-Off Time




Figure 4. Capacitance

2 of 3

Revision: C 2013/01/01



Micro Commercial Components

Ordering Information:

Device	Packing
Part Number-BP	Bulk; 1Kpcs/Box

Note: Adding "-HF" suffix for halogen free, eg. Part Number-BP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.