

Label - MM-EML (16,5X5)R C1 YE/BK - 1116201

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: adhesive, lettering field size: 16.5 x 6 mm, Number of individual labels: 335

Product Description

The MM-EML... polyester self-adhesive labels are available as pre-punched material for equipment marking.

Your advantages

- The pre-punched geometry enables easy and convenient use
- Thanks to the innovative material composition, each label can be printed which results in zero wastage
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- Mo visible difference between retrospective marking and existing markings created with a desktop roll printer
- The pre-punched self-adhesive labels are particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing



Key Commercial Data

Packing unit	1 pc
GTIN	4 063151 042219
GTIN	4063151042219
Custom tariff number	96121010
Country of origin	China

Technical data

Dimensions

Length (b)	6 mm



Label - MM-EML (16,5X5)R C1 YE/BK - 1116201

Technical data

Width (a)	16.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C 150 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Color	yellow/black
Components	free from silicone, halogen, and cadmium
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	335
Marking mounting type	adhesive

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 9.0	27400629
CO1@33 3.0	27400023

Approvals

Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized



http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

MH48542



Phoenix Contact 2021 © - all rights reserved http://www.phoenixcontact.com