

**Micro Commercial Components** 



**Micro Commercial Components** 20736 Marilla Street Chatsworth CA 91311 Phone: (818) 701-4933 (818) 701-4939 Fax:


## Features

- Lead Free Finish/Rohs Compliant ("P"Suffix designates
- Compliant. See ordering information) Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1 Power dissipation:  $P_{CM} = 0.2W$
- Collector current:  $I_{\rm C} = 0.15$ A
- Thermal Resistance From Junction To Ambient: 625°C/W
- Operating and storage junction temperature range
- T, T<sub>stg</sub>: -55℃ to + 150℃ Halogen free available upon request by adding suffix "-HF" Electrical Characteristics @ 25℃ Unless Otherwise Snecified

LIUUUIUU	Licen Iear Onaracter 15063 @ 20 🔘 Onicas Other Wise Specificu						
Symbol	Parameter	Min	Тур	Max	Unit		
V <sub>CEO</sub>	Collector-Emitter Voltage (I <sub>C</sub> =1mA,I <sub>B</sub> =0)	50			V		
V <sub>CBO</sub>	Collector-Base Voltage (I <sub>c</sub> =0.1mA, I <sub>E</sub> =0)	50			V		
$V_{\text{EBO}}$	Emitter-Base Voltage (I <sub>E</sub> =0.1mA, I <sub>C</sub> =0)	5.0			V		
I <sub>CBO</sub>	Collector cut-off Current $(V_{CB}=50V, I_{E}=0)$			0.1	μA		
I <sub>EBO</sub>	Emitter cut-off Current (V <sub>EB</sub> =5V, I <sub>C</sub> =0)			0.1	μA		
h <sub>FE</sub>	DC current gain (V <sub>CE</sub> =6V, I <sub>C</sub> =2mA)	120		400			
V <sub>CE(sat)</sub>	Collector-Emitter Saturation Voltage $(I_C=100 \text{mA}, I_B=10 \text{mA})$			0.25	V		
$C_{ob}$	Collector output capacitance (V <sub>CB</sub> =10Vdc, I <sub>E</sub> =0,f=1MHz)			3.5	pF		
f⊤	Transition Frequency (V <sub>CE</sub> =10Vdc, I <sub>C</sub> =1.0mAdc)	80			MHz		

#### CLASSIFICATION OF h<sub>FE</sub>

RANK	Y	GR
RANGE	120-240	200-400



2SC2458-Y


2SC2458-GR

www.mccsemi.com

## 2SC2458-Y 2SC2458-GR



**Micro Commercial Components** 



www.mccsemi.com



### **Ordering Information :**

Device	Packing
Part Number-AP	Ammo Packing: 30Kpcs/Carton
Part Number-BP	Bulk: 100Kpcs/Carton

Note : Adding "-HF" suffix for halogen free, eg. Part Number-AP-HF

#### **\*\*\*IMPORTANT NOTICE\*\*\***

*Micro Commercial Components Corp.* reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. *Micro Commercial Components Corp*. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp*. and all the companies whose products are represented on our website, harmless against all damages.

#### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

#### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

# www.mccsemi.com