

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



CHARX connect, Vehicle charging inlet, Locking actuator right, For charging electric vehicles (EV) with alternating current (AC), For installation in electric vehicles (EV), AC type 2, IEC 62196-2, length: 2 m, Locking actuator: 24 V, 4-position, M6, Generation 4, A protective cap is supplied as standard for the AC contacts.

The figure shows a version of the product

#### **Product Description**

Vehicle charging inlet for charging with alternating current (AC), compatible with type 2 AC vehicle charging connectors (EVSE), for installation in electric vehicles for e-mobility (EV).

#### Your advantages

- Uniform, space-saving dimensions and screw connection points for all Phoenix Contact AC vehicle charging inlets
- Silver-plated surface of the power and signal contacts
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Material data available in the IMDS (International Material Data System of the automotive industry)
- Tested in accordance with selected tests of automotive standards LV124, LV214, LV215-2
- Manual emergency release of the locking actuator
- ☑ Integrated temperature sensors for monitoring the temperature at the power contacts



### **Key Commercial Data**

Packing unit	1 pc
GTIN	4 063151 463816
GTIN	4063151463816
Custom tariff number	85444290
Country of origin	Germany



### Technical data

### Product definition

Туре	Locking actuator right
Application	For charging electric vehicles (EV) with alternating current (AC)
	For installation in electric vehicles (EV)
Design	Generation 4
Standards/regulations	IEC 62196-2
Charging standard	AC type 2
Charging mode	Mode 2, 3
Note	A protective cap is supplied as standard for the AC contacts.
Note on the connection method	Crimp connection, cannot be disconnected

### **Dimensions**

Height	90 mm
Width	90 mm
Depth	111.4 mm
Bore dimensions	73 mm x 73 mm, 73 mm x 73 mm
Conductor length	2 m (AC sheathed cable)
	1 m (Locking actuator cables)
	1 m (Temperature sensors cables)
	1 m (Communications cables)

### Ambient conditions

Ambient temperature (operation)	-40 °C 60 °C
Ambient temperature (storage/transport)	-40 °C 85 °C
Max. altitude	4000 m (above sea level)
Degree of protection	IP55 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
	IP55 (Inner area of vehicle charging inlet)

### Electrical properties

Charging power (nominal operation)	8 kW
Type of charging current	AC single-phase
Number of power contacts	5 (L1, L2, L3, N, PE)
Rated current of power contacts	32 A AC
Rated voltage for power contacts	250 V AC
Number of signal contacts	2 (CP, PP)
Rated current for signal contacts	2 A
Rated voltage for signal contacts	30 V AC



### Technical data

### Electrical properties

Type of signal transmission	Pulse width modulation with modulated Powerline communication according to ISO/IEC 15118 / DIN SPEC 70121
Note on the connection method	Crimp connection, cannot be disconnected
Insulation resistance of neighboring contacts	> 200 MΩ
Resistor coding	4.7 kΩ (between PE and PP)
Temperature monitoring	AC contacts: PTC chain (DIN#EN#60738-1)

### Mechanical properties

Insertion/withdrawal cycles	> 10000
Insertion force	< 75 N
Withdrawal force	< 75 N

### Mounting

Restrictions to mounting position	Only 0 to 90 degree frontal inclination possible, see figure
Mounting position of the locking actuator	Right-side
Mounting hole diameter	6.70 mm (ø)
Required mounting screws	M6
Screws included in the scope of delivery	none

### Design

Design line	Generation 4
Housing color	black
Customer variations	On request

### Material

Material	Plastic
Flammability rating	V0
Material surface of contacts	Ag

### Locking

	Locking type	Locking in the inserted state with a locking mechanism
--	--------------	--

### AC cable

Cable structure	3 x 6 mm²
External cable diameter	13.8 mm ±0.3 mm
Cable resistance	$\leq 3.2 \Omega/km$
Outer sheath, material	Silicone
External sheath, color	orange
Minimum bending radius	3 x D
Cable weight	approx. 385 kg/km

Locking actuator cable



### Technical data

### Locking actuator cable

Cable structure	4 x 0.5 mm <sup>2</sup>
External cable diameter	1.6 mm -0.2 mm
Cable resistance	≤ 37.1 Ω/km
Outer sheath, material	PVC
Single wire, color	BU/RD, BU/GN, BU/YE, BU/BN
Minimum bending radius	15 mm
Cable weight	7 kg/km

### Temperature sensor cable

Cable structure	2 x 0.5 mm <sup>2</sup>
External cable diameter	1.6 mm -0.2 mm
Cable resistance	≤ 37.1 Ω/km
Outer sheath, material	PVC
Single wire, color	brown, gray
Minimum bending radius	15 mm
Cable weight	7 kg/km

### Cable communication

Cable structure	0.5 mm <sup>2</sup> + 0.5 mm <sup>2</sup>
External cable diameter	1.6 mm -0.2 mm
Cable resistance	≤ 37.1 Ω/km
Outer sheath, material	PVC
Single wire, color	black PP/CS
	white CP
Minimum bending radius	15 mm
Cable weight	7 kg/km

### Locking actuator

Number of positions of theconnectors	4
Operating voltage	24 V (Typical power supply at the motor)
Possible power supply range at the motor	22 V 26 V
Maximum voltage for locking detection	30 V
Typical motor current for locking	0.05 A
Reverse current of the motor	max. 0.5 A
Max. dwell time with reverse current	1 s
Recommended adaptation time	600 ms
Pause time after entry or exit path	3 s
Service life insertion cycles	> 10000 load cycles
Ambient temperature (operation)	-30 °C 50 °C



### Technical data


### Locking actuator

Cable length	0.5 m
Cable structure	4 x 0.5 mm <sup>2</sup>
Lock recognition	available
Mechanical emergency release	available


### Temperature monitoring, AC contacts

Type of sensor	PTC chain
Standards/regulations	DIN#EN 60738-1
Recommended measured current	$\leq$ 1 mA (U <sub>max</sub> = 16 V DC)
Tolerance at the sensor with the recommended measured current	±5K
Temperature range	-40 °C 130 °C

### Drawings



### Connection diagram




Pin assignment of Vehicle Inlet

Locking states of the locking actuator




### Block diagram




Block diagram of the locking actuator

### Dimensional drawing



### Dimensional drawing


### Schematic diagram



Temperature sensor technology resistance range at AC contacts





### Connection diagram



Installation positions








Terminology definition




Functional drawing



08/23/2021 Page 9 / 11



### Schematic diagram





### Classifications

### eCl@ss

eCl@ss 10.0.1	27144706
eCl@ss 11.0	27144706

### **ETIM**

ETIM 7.0	EC002898

Phoenix Contact 2021 © - all rights reserved http://www.phoenixcontact.com