

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



CHARX connect, Vehicle charging inlet, Locking actuator right, For charging electric vehicles (EV) with alternating current (AC), For installation in electric vehicles (EV), AC type 2, IEC 62196-2, length: 2 m, Locking actuator: 24 V, 4-position, M6, Generation 4, A protective cap is supplied as standard for the AC contacts.

The figure shows a version of the product

Product Description

Vehicle charging inlet for charging with alternating current (AC), compatible with type 2 AC vehicle charging connectors (EVSE), for installation in electric vehicles for e-mobility (EV).

Your advantages

- 11 Uniform, space-saving dimensions and screw connection points for all Phoenix Contact AC vehicle charging inlets
- Silver-plated surface of the power and signal contacts
- ☑ Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Material data available in the IMDS (International Material Data System of the automotive industry)
- Tested in accordance with selected tests of automotive standards LV124, LV214, LV215-2
- Manual emergency release of the locking actuator
- Integrated interlock during charging
- ☑ Integrated temperature sensors for monitoring the temperature at the power contacts

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	4 063151 464004
GTIN	4063151464004
Custom tariff number	85444290
Country of origin	Germany



Technical data

Product definition

Туре	Locking actuator right
Application	For charging electric vehicles (EV) with alternating current (AC)
	For installation in electric vehicles (EV)
Design	Generation 4
Standards/regulations	IEC 62196-2
Charging standard	AC type 2
Charging mode	Mode 2, 3
Note	A protective cap is supplied as standard for the AC contacts.
Note on the connection method	Crimp connection, cannot be disconnected

Dimensions

Height	90 mm
Width	90 mm
Depth	111.4 mm
Bore dimensions	73 mm x 73 mm, 73 mm x 73 mm
Conductor length	2 m (AC sheathed cable)
	1 m (Locking actuator cables)
	1 m (Temperature sensors cables)
	1 m (Communications cables)

Ambient conditions

Ambient temperature (operation)	-40 °C 60 °C
Ambient temperature (storage/transport)	-40 °C 85 °C
Max. altitude	4000 m (above sea level)
Degree of protection	IP55 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
	IP55 (Inner area of vehicle charging inlet)

Electrical properties

Charging power (nominal operation)	26 kW
Type of charging current	AC 3-phase
Number of power contacts	5 (L1, L2, L3, N, PE)
Rated current of power contacts	32 A AC
Rated voltage for power contacts	480 V AC
Number of signal contacts	2 (CP, PP)
Rated current for signal contacts	2 A
Rated voltage for signal contacts	30 V AC



Technical data

Electrical properties

Type of signal transmission	Pulse width modulation with modulated Powerline communication according to ISO/IEC 15118 / DIN SPEC 70121	
Note on the connection method	Crimp connection, cannot be disconnected	
Insulation resistance of neighboring contacts	> 200 MΩ	
Resistor coding	4.7 kΩ (between PE and PP)	
Temperature monitoring	AC contacts: PTC chain (DIN#EN#60738-1)	
Mechanical properties		
Insertion/withdrawal cycles	> 10000	
Insertion force	< 100 N	
Withdrawal force	< 100 N	
Mounting	· · · ·	
Restrictions to mounting position	Only 0 to 90 degree frontal inclination possible, see figure	
Mounting position of the locking actuator	Right-side	
Mounting hole diameter	6.70 mm (ø)	
Required mounting screws	M6	
Screws included in the scope of delivery	none	
Design		
Design line	Generation 4	
Housing color	black	
Customer variations	On request	
Material		
Material	Plastic	
Flammability rating	V0	
Material surface of contacts	Ag	
_ocking		
Locking type	Locking in the inserted state with a locking mechanism	
AC cable		
Cable structure	5 x 6 mm ²	
External cable diameter	15.9 mm ±0.3 mm	
Cable resistance	\leq 3.2 Ω/km	
Outer sheath, material	Silicone	
External sheath, color	orange	
Minimum bending radius	3 x D	
Cable weight	approx. 532 kg/km	

Locking actuator cable



Technical data

Locking actuator cable

Cable structure	4 x 0.5 mm ²
External cable diameter	1.6 mm -0.2 mm
Cable resistance	\leq 37.1 Ω /km
Outer sheath, material	PVC
Single wire, color	BU/RD, BU/GN, BU/YE, BU/BN
Minimum bending radius	15 mm
Cable weight	7 kg/km

Temperature sensor cable

Cable structure	2 x 0.5 mm²
External cable diameter	1.6 mm -0.2 mm
Cable resistance	\leq 37.1 Ω /km
Outer sheath, material	PVC
Single wire, color	brown, gray
Minimum bending radius	15 mm
Cable weight	7 kg/km

Cable communication

Cable structure	0.5 mm ² + 0.5 mm ²
External cable diameter	1.6 mm -0.2 mm
Cable resistance	\leq 37.1 Ω /km
Outer sheath, material	PVC
Single wire, color	black PP/CS
	white CP
Minimum bending radius	15 mm
Cable weight	7 kg/km

Locking actuator

Number of positions of theconnectors	4
Operating voltage	24 V (Typical power supply at the motor)
Possible power supply range at the motor	22 V 26 V
Maximum voltage for locking detection	30 V
Typical motor current for locking	0.05 A
Reverse current of the motor	max. 0.5 A
Max. dwell time with reverse current	1 s
Recommended adaptation time	600 ms
Pause time after entry or exit path	3 s
Service life insertion cycles	> 10000 load cycles
Ambient temperature (operation)	-30 °C 50 °C



Technical data


Locking actuator

Cable length	0.5 m
Cable structure	4 x 0.5 mm ²
Lock recognition	available
Mechanical emergency release	available

Temperature monitoring, AC contacts


Type of sensor	PTC chain
Standards/regulations	DIN#EN 60738-1
Recommended measured current	\leq 1 mA (U _{max} = 16 V DC)
Tolerance at the sensor with the recommended measured current	±5K
Temperature range	-40 °C 130 °C

Drawings




Locking states of the locking actuator

Connection diagram




Pin assignment of Vehicle Inlet






Block diagram of the locking actuator

Dimensional drawing




Dimensional drawing

Schematic diagram



Temperature sensor technology resistance range at AC contacts






Installation positions


08/23/2021 Page 7 / 11





Terminology definition






08/23/2021 Page 9 / 11



Schematic diagram



08/23/2021 Page 10 / 11



Classifications

eCl@ss

eCl@ss 10.0.1	27144706
eCl@ss 11.0	27144706

ETIM

ETIM 7.0 EC002898

Phoenix Contact 2021 © - all rights reserved http://www.phoenixcontact.com