

BCR12FM-12LB

600V - 12A - Triac

R07DS1104EJ0201 Rev.2.01 May 31, 2018

Medium Power Use

Features

I_{T (RMS)}: 12 A
 V_{DRM}: 600 V
 Tj: 150 °C


I_{FGTI}, I_{RGTI}, I_{RGT III}: 30 mA(20mA) ^{Note5}

Insulated Type

• Planar Passivation Type

• Viso: 2000V

Outline



Application

Motor control, Heater control, Power supply, Solid state relay, and other general purpose AC control applications.

Maximum Ratings

Parameter	Symbol	Voltage class	Unit
		12	
Repetitive peak off-state voltage ^{Note1}	V_{DRM}	600	V
Non-repetitive peak off-state voltage ^{Note1}	V_{DSM}	720	V

Parameter	Symbol	Ratings	Unit	Conditions
RMS on-state current	I _{T (RMS)}	12	Α	Commercial frequency, sine full wave
				360°conduction,
				Tc = 102°C (#BB0, #BH0) Note2
				Tc = 93°C (#BG0) Note2
Surge on-state current	I _{TSM}	120	Α	50 Hz sinewave 1 full cycle, peak value,
				non-repetitive
I ² t for fusion	l ² t	60	A ² s	Value corresponding to 1 cycle of half wave
				50 Hz, surge on-state current
Peak gate power dissipation	P_{GM}	5	W	
Average gate power dissipation	P _G (AV)	0.5	W	
Peak gate voltage	V_{GM}	10	V	
Peak gate current	l _{GM}	2	Α	
Junction Temperature	Tj	-40 to +150	°C	
Storage temperature	Tstg	-40 to +150	°C	
Isolation voltage Note7	Viso	2000	V	Ta=25°C, AC 1 minute,
				T ₁ • T ₂ • G terminal to case

Notes: 1. Gate open.

2. Please refer to the Ordering Information.

Electrical Characteristics


Parameter		Symbol	Min.	Тур.	Max.	Unit	Test conditions
Repetitive peak off-state cu	rrent	I _{DRM}	_	_	2.0	mA	Tj = 150°C, V _{DRM} applied
On-state voltage		V _{TM}	_	_	1.6	V	Tc = 25°C, I _{TM} = 20 A, instantaneous measurement
Gate trigger voltage ^{Note3}	I	V _{FGTI}	_	_	1.5	V	Tj = 25°C, V_D = 6 V, R_L = 6 Ω,
II	II	V_{RGTI}	_	_	1.5	V	$R_G = 330 \Omega$
	III	V _{RGTIII}	_	_	1.5	V	
Gate trigger curent ^{Note3}	I _{FGTI}	_	_	30 Note6	mA	$Tj = 25$ °C, $V_D = 6$ V, $R_L = 6$ Ω,	
	II	I _{RGTI}	_	_	30 Note6	mA	$R_G = 330 \Omega$
	III	I _{RGTIII}	_	_	30 Note6	mA	
Gate non-trigger voltage		V_{GD}	0.2	_	_	V	Tj = 125°C, V _D = 1/2 V _{DRM}
			0.1	_	_		Tj = 150°C, V _D = 1/2 V _{DRM}
Thermal resistance		R _{th (j-c)}	_	_	3.3	°C/W	Junction to case ^{Note4} (#BB0, #BH0) ^{Note2}
			_	_	4.0	°C/W	Junction to case ^{Note4} (#BG0) ^{Note2}
Critical-rate of rise of off-state commutation voltage ^{Note5}		(dv/dt)c	10	_	_	V/μs	Tj = 125°C
			1	_	_		Tj = 150°C


Notes: 3. Measurement using the gate trigger characteristics measurement circuit.


- 4. The contact thermal resistance $R_{th(c-f)}$ in case of greasing is 0.5°C/W .
- 5. Test conditions of the critical-rate of rise of off-state commutation voltage is shown in the table below.
- 6. High sensitivity (I_{GT} ≤ 20 mA) is also available. (I_{GT} item:1)
- 7. Make sure that your finished product containing this device meets your safe isolation requirements. For safety, it's advisable that heatsink is electrically floating.


Test conditions	Commutating voltage and current waveforms (inductive load)
 Junction temperature Tj = 125°C/150°C Rate of decay of on-state commutating current (di/dt)c = -6.0 A/ms Peak off-state voltage V_D = 400 V 	Supply Voltage Main Current Main Voltage (di/dt)c Time Main Voltage (dv/dt)c

Performance Curves










Package Dimensions

Ordering code: #BG0, #BH0

JEITA Package Code	RENESAS Code	Previous Code	MASS (Typ) [g]
-	PRSS0003AP-A	TO-220FPA	1.65
10.0±0.3 10.0±0.3 10.0±0.3 10.0±0.3 2.54±0.25	0.745±0.2 0.395±0.2 1.14±0.2 0.69±0.15 0.60 [±]	0.19 0.11	Unit: mi
	3.2±0.2		

Package Dimensions

Ordering code: #BB0 <To be EOLed>



Ordering Information

Orderable Part Number	Package	Quantity Note8	Remark	Status
BCR12FM-12LB#BG0	TO-220FPA	50 pcs./ tube	Straight type	Mass Production
BCR12FM-12LB-1#BG0	TO-220FPA	50 pcs./ tube	Straight type, Ig⊤item:1	
BCR12FM-12LB□□#BG0	TO-220FPA	50 pcs./ tube	□□:Lead form type	
BCR12FM12LB1□□#BG0	TO-220FPA	50 pcs./ tube	□□:Lead form type, I _{GT} item:1	
BCR12FM-12LB#BH0	TO-220FPA	50 pcs./ tube	Straight type	Under Development
BCR12FM-12LB-1#BH0	TO-220FPA	50 pcs./ tube	Straight type, Igт item:1	
BCR12FM-12LB□□#BH0	TO-220FPA	50 pcs./ tube	□□:Lead form type	
BCR12FM12LB1□□#BH0	TO-220FPA	50 pcs./ tube	□□:Lead form type, I _{GT} item:1	
BCR12FM-12LB#BB0	TO-220FP	50 pcs./ tube	Straight type	Not Recommended for
BCR12FM-12LB□□#BB0	TO-220FP	50 pcs./ tube	□□:Lead form type	New Design

Notes: 8. Please confirm the specification about the shipping in detail.

Notice

- 1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information
- 2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other disputes involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawing, chart, program, algorithm, application
- 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 4. You shall not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics products.
- 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (space and undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas

- 6. When using the Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat radiation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions or failure or accident arising out of the use of Renesas Electronics products beyond such specified
- 7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please ensure to implement safety measures to guard them against the possibility of bodily injury, injury or damage caused by fire, and social damage in the event of failure or malfunction of Renesas Electronics products, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures by your own responsibility as warranty for your products/system. Because the evaluation of microcomputer software alone is very difficult and not practical, please evaluate the safety of the final products or systems manufactured by you.
- 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please investigate applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive carefully and sufficiently and use Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations
- 9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall not use Renesas Electronics products or technologies for (1) any purpose relating to the development, design, manufacture, use, stockpiling, etc., of weapons of mass destruction, such as nuclear weapons, chemical weapons, or biological weapons, or missiles (including unmanned aerial vehicles (UAVs)) for delivering such weapons, (2) any purpose relating to the development, design, manufacture, or use of conventional weapons, or (3) any other purpose of disturbing international peace and security, and you shall not sell, export, lease, transfer, or release Renesas Electronics products or technologies to any third party whether directly or indirectly with knowledge or reason to know that the third party or any other party will engage in the activities described above. When exporting, selling, transferring, etc., Renesas Electronics products or technologies, you shall comply with any applicable export control laws and regulations promulgated and administered by the governments of the
- 10. Please acknowledge and agree that you shall bear all the losses and damages which are incurred from the misuse or violation of the terms and conditions described in this document, including this notice, and hold Renesas Electronics harmless, if such misuse or violation results from your resale or making Renesas Electronics products available any third party.
- 11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.3.0-1 November 2016)



SALES OFFICES

Renesas Electronics Corporation

http://www.renesas.com

Refer to "http://www.renesas.com/" for the latest and detailed information

Renesas Electronics America Inc. 2801 Scott Boulevard Santa Clara, CA 95050-2549, U.S.A. Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited 9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3 Tel: +1-905-237-2004

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-585-100, Fax: +44-1628-585-900

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100191, P.R.China Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.

Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, P. R. China 200333 Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited

Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong Tel: +852-2265-6688, Fax: +852 2886-9022

Renesas Electronics Taiwan Co., Ltd. 13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd. 80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949 Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd. Unit 1207, Block B, Menara Amcorp, Amcorp Tel: +60-3-7955-9390, Fax: +60-3-7955-9510 p Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia

Renesas Electronics India Pvt. Ltd. No.777C, 100 Feet Road, HAL II Stage, Indiranagar, Bangalore, India Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd. 12F., 234 Teheran-ro, Gangnam-Gu, Seoul, 135-080, Korea Tel: +82-2-558-3737, Fax: +82-2-558-5141