


INT-A-PAK “Half-Bridge” (Ultrafast Speed IGBT), 108 A


INT-A-PAK

| PRODUCT SUMMARY | |
|------------------------------|-----------------|
| V_{CES} | 600 V |
| I_C DC | 108 A |
| $V_{CE(on)}$ at 100 A, 25 °C | 2.6 V |
| Speed | 8 kHz to 30 kHz |
| Package | INT-A-PAK |
| Circuit | Half bridge |

FEATURES

- Generation 5 Non Punch Through (NPT) technology
- Ultrafast: optimized for hard switching speed
- Low $V_{CE(on)}$
- 10 μ s short circuit capability
- Square RBSOA
- Positive $V_{CE(on)}$ temperature coefficient
- HEXFRED® antiparallel diode with ultrasoft reverse recovery characteristics
- Industry standard package
- Al_2O_3 DBC
- UL approved file E78996 
- Designed for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


**RoHS
COMPLIANT**

BENEFITS

- Benchmark efficiency for UPS and welding application
- Rugged transient performance
- Direct mounting on heatsink
- Very low junction to case thermal resistance

| ABSOLUTE MAXIMUM RATINGS | | | | |
|--------------------------------------|------------|--|-------------|-------|
| PARAMETER | SYMBOL | TEST CONDITIONS | MAX. | UNITS |
| Collector to emitter voltage | V_{CES} | | 600 | V |
| Continuous collector current | I_C | $T_C = 25\text{ °C}$ | 108 | A |
| | | $T_C = 80\text{ °C}$ | 74 | |
| Pulsed collector current | I_{CM} | | 200 | |
| Clamped inductive load current | I_{LM} | | 200 | |
| Diode continuous forward current | I_F | $T_C = 25\text{ °C}$ | 106 | |
| | | $T_C = 80\text{ °C}$ | 69 | |
| Gate to emitter voltage | V_{GE} | | ± 20 | |
| Maximum power dissipation | P_D | $T_C = 25\text{ °C}$ | 390 | W |
| | | $T_C = 80\text{ °C}$ | 219 | |
| Isolation voltage | V_{ISOL} | Any terminal to case, $t = 1\text{ min}$ | 2500 | V |
| Operating junction temperature range | T_J | | -40 to +150 | °C |
| Storage temperature range | T_{Stg} | | -40 to +150 | |



| ELECTRICAL SPECIFICATIONS ($T_J = 25\text{ }^\circ\text{C}$ unless otherwise specified) | | | | | | |
|---|---------------|---|------|------|-----------|-------|
| PARAMETER | SYMBOL | TEST CONDITIONS | MIN. | TYP. | MAX. | UNITS |
| Collector to emitter breakdown voltage | $V_{BR(CES)}$ | $V_{GE} = 0\text{ V}, I_C = 500\text{ }\mu\text{A}$ | 600 | - | - | V |
| Collector to emitter voltage | $V_{CE(on)}$ | $V_{GE} = 15\text{ V}, I_C = 50\text{ A}$ | - | 1.95 | 2.1 | |
| | | $V_{GE} = 15\text{ V}, I_C = 100\text{ A}$ | - | 2.6 | 2.85 | |
| | | $V_{GE} = 15\text{ V}, I_C = 50\text{ A}, T_J = 125\text{ }^\circ\text{C}$ | - | 2.21 | 2.44 | |
| | | $V_{GE} = 15\text{ V}, I_C = 100\text{ A}, T_J = 125\text{ }^\circ\text{C}$ | - | 3.05 | 3.38 | |
| Gate threshold voltage | $V_{GE(th)}$ | $V_{CE} = V_{GE}, I_C = 500\text{ }\mu\text{A}$ | 3 | 4.6 | 6 | |
| Collector to emitter leakage current | I_{CES} | $V_{GE} = 0\text{ V}, V_{CE} = 600\text{ V}$ | - | 0.01 | 0.1 | mA |
| | | $V_{GE} = 0\text{ V}, V_{CE} = 600\text{ V}, T_J = 150\text{ }^\circ\text{C}$ | - | 3.7 | 10 | |
| Diode forward voltage drop | V_{FM} | $I_C = 50\text{ A}$ | - | 1.35 | 1.66 | V |
| | | $I_C = 100\text{ A}$ | - | 1.57 | 1.96 | |
| | | $I_C = 50\text{ A}, T_J = 125\text{ }^\circ\text{C}$ | - | 1.27 | 1.50 | |
| | | $I_C = 100\text{ A}, T_J = 125\text{ }^\circ\text{C}$ | - | 1.57 | 1.89 | |
| Gate to emitter leakage current | I_{GES} | $V_{GE} = \pm 20\text{ V}$ | - | - | ± 200 | nA |

| SWITCHING CHARACTERISTICS ($T_J = 25\text{ }^\circ\text{C}$ unless otherwise specified) | | | | | | |
|---|--------------|---|------------|------|------|-------|
| PARAMETER | SYMBOL | TEST CONDITIONS | MIN. | TYP. | MAX. | UNITS |
| Turn-on switching loss | E_{on} | $I_C = 100\text{ A}, V_{CC} = 360\text{ V}, V_{GE} = 15\text{ V}, R_g = 4.7\text{ }\Omega, L = 200\text{ }\mu\text{H}, T_J = 25\text{ }^\circ\text{C}$ | - | 0.6 | - | mJ |
| Turn-off switching loss | E_{off} | | - | 1.1 | - | |
| Total switching loss | E_{tot} | | - | 1.7 | - | |
| Turn-on switching loss | E_{on} | $I_C = 100\text{ A}, V_{CC} = 360\text{ V}, V_{GE} = 15\text{ V}, R_g = 4.7\text{ }\Omega, L = 200\text{ }\mu\text{H}, T_J = 125\text{ }^\circ\text{C}$ | - | 0.8 | - | |
| Turn-off switching loss | E_{off} | | - | 1.3 | - | |
| Total switching loss | E_{tot} | | - | 2.1 | - | |
| Turn-on delay time | $t_{d(on)}$ | | - | 197 | - | ns |
| Rise time | t_r | | - | 50 | - | |
| Turn-off delay time | $t_{d(off)}$ | | - | 225 | - | |
| Fall time | t_f | - | 72 | - | | |
| Reverse bias safe operating area | RBSOA | $T_J = 150\text{ }^\circ\text{C}, I_C = 200\text{ A}, R_g = 27\text{ }\Omega, V_{GE} = 15\text{ V to }0$ | Fullsquare | | | |
| Short circuit safe operating area | SCSOA | $T_J = 150\text{ }^\circ\text{C}, V_{CC} = 400\text{ V}, V_P = 600\text{ V}, R_g = 27\text{ }\Omega, V_{GE} = 15\text{ V to }0$ | 10 | - | - | |
| Diode reverse recovery time | t_{rr} | $I_F = 50\text{ A}, di_F/dt = 200\text{ A}/\mu\text{s}, V_{CC} = 400\text{ V}, T_J = 25\text{ }^\circ\text{C}$ | - | 116 | 140 | ns |
| Diode peak reverse current | I_{rr} | | - | 11 | 15 | A |
| Diode recovery charge | Q_{rr} | | - | 600 | 1050 | nC |
| Diode reverse recovery time | t_{rr} | $I_F = 50\text{ A}, di_F/dt = 200\text{ A}/\mu\text{s}, V_{CC} = 400\text{ V}, T_J = 125\text{ }^\circ\text{C}$ | - | 152 | 190 | ns |
| Diode peak reverse current | I_{rr} | | - | 16 | 20 | A |
| Diode recovery charge | Q_{rr} | | - | 1215 | 1900 | nC |

| THERMAL AND MECHANICAL SPECIFICATIONS | | | | | | |
|--|--------------------------|------|------|------|---------------------------|--|
| PARAMETER | SYMBOL | MIN. | TYP. | MAX. | UNITS | |
| Operating junction and storage temperature range | T_J, T_{Stg} | -40 | - | 150 | $^\circ\text{C}$ | |
| Junction to case per leg | IGBT | - | 0.23 | 0.32 | $^\circ\text{C}/\text{W}$ | |
| | Diode | - | 0.38 | 0.64 | | |
| Case to sink per module | R_{thCS} | - | 0.1 | - | | |
| Mounting torque | case to heatsink | - | - | 4 | Nm | |
| | case to terminal 1, 2, 3 | - | - | 3 | | |
| Weight | | - | 185 | - | g | |




Fig. 1 - Typical IGBT Output Characteristics
 $T_J = 25^\circ\text{C}$, $t_p = 500 \mu\text{s}$




Fig. 4 - Typical Collector to Emitter Voltage vs. Junction Temperature,
 $V_{GE} = 15 \text{ V}$, $500 \mu\text{s}$ pulse width




Fig. 2 - Typical IGBT Output Characteristics
 $T_J = 125^\circ\text{C}$, $t_p = 500 \mu\text{s}$




Fig. 5 - Diode Forward Characteristics, $t_p = 500 \mu\text{s}$




Fig. 3 - Typical Transfer Characteristics
 $V_{CE} = 20 \text{ V}$, $t_p = 500 \mu\text{s}$




Fig. 6 - Maximum Collector Current vs. Case Temperature




Fig. 7 - Typical Energy Loss vs. I_C , $T_J = 125\text{ }^\circ\text{C}$, $L = 200\text{ }\mu\text{H}$, $V_{CC} = 360\text{ V}$, $R_g = 4.7\text{ }\Omega$, $V_{GE} = 15\text{ V}$




Fig. 10 - Typical Switching Time vs. R_g , $T_J = 125\text{ }^\circ\text{C}$, $L = 200\text{ }\mu\text{H}$, $V_{CC} = 360\text{ V}$, $I_{CE} = 100\text{ A}$, $V_{GE} = 15\text{ V}$




Fig. 8 - Typical Switching Time vs. I_C , $T_J = 125\text{ }^\circ\text{C}$, $L = 200\text{ }\mu\text{H}$, $V_{CC} = 360\text{ V}$, $R_g = 4.7\text{ }\Omega$, $V_{GE} = 15\text{ V}$




Fig. 11 - Typical Diode I_{rr} vs. I_F , $T_J = 125\text{ }^\circ\text{C}$




Fig. 9 - Typical Energy Loss vs. R_g , $T_J = 125\text{ }^\circ\text{C}$, $L = 200\text{ }\mu\text{H}$, $V_{CC} = 360\text{ V}$, $I_{CE} = 100\text{ A}$, $V_{GE} = 15\text{ V}$




Fig. 12 - Typical Diode I_{rr} vs. R_g , $T_J = 125\text{ }^\circ\text{C}$, $I_F = 100\text{ A}$




Fig. 13 - Typical Diode I_{RR} vs. dI_F/dt ,
 $T_J = 125^\circ\text{C}$, $V_{CC} = 360\text{ V}$, $I_F = 150\text{ A}$, $V_{GE} = 15\text{ V}$




Fig. 15 - Typical Switching Losses vs. Junction Temperature,
 $L = 200\ \mu\text{H}$, $R_g = 10\ \Omega$, $V_{CC} = 360\text{ V}$, $V_{GE} = 15\text{ V}$




Fig. 14 - Typical Switching Losses vs. Gate Resistance,
 $T_J = 125^\circ\text{C}$, $L = 200\ \mu\text{H}$, $R_g = 10\ \Omega$,
 $V_{CC} = 360\text{ V}$, $V_{GE} = 15\text{ V}$




Fig. 16 - Typical Switching Losses vs. Collector to Emitter Current,
 $T_J = 125^\circ\text{C}$, $R_{g1} = 4.7\ \Omega$, $R_{g2} = 0\ \Omega$, $V_{CC} = 360\text{ V}$, $V_{GE} = 15\text{ V}$




Fig. 17 - Maximum Transient Thermal Impedance, Junction to Case (IGBT)





Fig. 18 - Maximum Transient Thermal Impedance, Junction to Case (HEXFRED®)

ORDERING INFORMATION TABLE

| | | | | | | | | | |
|-------------|------------|----------|----------|------------|----------|----------|-----------|----------|------------|
| Device code | VS- | G | B | 100 | T | S | 60 | N | PbF |
| | ① | ② | ③ | ④ | ⑤ | ⑥ | ⑦ | ⑧ | ⑨ |

- 1** - Vishay Semiconductors product
- 2** - Insulated Gate Bipolar Transistor (IGBT)
- 3** - B = IGBT Generation 5 NPT
- 4** - Current rating (100 = 100 A)
- 5** - Circuit configuration (T = Half-bridge)
- 6** - Package indicator (S = INT-A-PAK)
- 7** - Voltage rating (60 = 600 V)
- 8** - Speed/type (N = Ultrafast IGBT)
- 9** - Lead (Pb)-free


CIRCUIT CONFIGURATION

LINKS TO RELATED DOCUMENTS

| | |
|------------|--|
| Dimensions | www.vishay.com/doc?95543 |
|------------|--|



INT-A-PAK IGBT

DIMENSIONS in millimeters (inches)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.