

Multilayer Ceramic Chip Capacitor

NOVACI	AP + SYFER + VOLTRONICS					
Part Number	: 1812JA250561J	KTSYX	Description:	1812 250Vac (Y2), 305Vac (X1), 50/60Hz / 1000Vdc 560pF ±5% C0G/NP0 (1B) to AEC- Q200		
Approval	Approval IEC/EN60384-14:2013+A1			~		
Specifications:						
			<			
Certification:	TÜV R60153659 / ID1111	233476		T		
	UL/cUL E228790-20201127		+2			
Classification:	IEC/EN 60384-14:2013+A	1 Class Y2 / X1	~	12- L4 L3		
	UL/cUL FOWX2, FOWX8			Letter		
			Component I	Marking and Certification Bodies:		
Material Group I	: CTI >= 600		SYX			
Mechanical Specification						
Size Code		Wechanical	1812			
Length (L1) in mm ("				$4.95 \pm 0.35 (0.195 \pm 0.014)$		
Width (W) in mm (")				$3.2 \pm 0.30 (0.126 \pm 0.012)$		
Thickness (T) in mm	(")		2.54 Max (0.1 Max)			
	n Band (L2,L3) in mm (")		0.35 (0.014)			
	on Band (L2,L3) in mm (")		0.80 (0.030)			
Minimum Band Gap			4.0 (0.158)			
Termination Material				Nickel Barrier, Sn Plated Solder (RoHS compliant)		
Solderability				IEC-60068-2-58		
Packaging				7" Reel Horizontal Orientation, 500 per reel		
	G	eneral Electri	cal Specificati	on		
Rated Voltage			Class Y2 (250Vac), Class X1 (305Vac), 50/60Hz, 5kV impulse			
Humidity Grade			Grade III (IEC/EN60384-14:2013 Annex 1)			
Maximum DC Working Voltage			1000Vdc certified / (2500Vdc outside scope of any specification)			
Nominal Capacitance Value			560pF			
Capacitance Tolerance			±5%			
Tangent of Loss Angle (Tan δ)			≤0.0015			
Capacitance and Tan δ Test Conditions			1.0Vrms @ 1MHz			
Voltage Proof			100% test: 4000Vdc 1s min / 5s max			
(50mA max charging current for DC tests)			AQL test: 4000Vdc / 3000Vac 60s min / 5kV 1.2x50µs impulse			
Min Insulation Resistance (IR)			100.00GOhm @ 100Vdc			
			C0G/NP0 (1B) to AEC-Q200			
Rated Temperature Range			-55°C / +125°C			
Maximum Capacitance Change over Temperature Range			No DC Voltage Rated DC Voltage	0±30ppm/°C -		
Climatic Category (IEC)			55/125/56			
Ageing Characteristic			Zero			
Knowles Precision Devices Sales						
	pe-sales@knowles.com	This datasheet is for a standard item and is confirmed valid on the date generated, the latest published for this part may differ and is available at http://www.knowlescapacitors.com or by contacting us.				
Asia: KPD-Asia-sales@knowles.com			ined on this drawing is Data is correct to the best of our knowledge, errors and			
USA: KPD-NA-sales@knowles.com any form or disclosed			be copied in whole or part in third party without the consent	omissions excepted.		
of Knowles		of Knowles and any cus specification.	tomer mentioned within this	Date: Thursday, September 02, 2021 20210902 193333541UTC		
20210902 193333541UTC						



Multilayer Ceramic Chip Capacitor

NOVACAP + SYFER + VOLTRONICS									
Part Number: 181	2JA250561J	KTSYX	Description:	1812 250Vac (Y2), 305Vac (X1), 50/60Hz / 1000Vdc 560pF ±5% C0G/NP0 (1B) to AEC- Q200					
Environmental									
RoHS Compliant to 2011/6	5/EC as amende	d by 2015/863/EU	Compliant						
REACH Compliant			211 compliant						
California Proposition 65			No exposure risk						
Board Layout									
Knowles' conventional 2-terminal chip capacitors can generally be mounted using pad designs in accordance with international specification IPC-7351, Generic Requirements for Surface Mount Design and Land Pattern Standards, but there are some other factors that have been shown to reduce mechanical stress, such as reducing the pad width to less than the chip width. In addition, the position of the chip on the board should be considered. Some high voltage parts may require modifications to the board layout and/or the addition of a conformal coating to prevent flashover. Refer to application note AN0043 for further information.				IPC-7351 pad design Image: 1812 C 5.35mm 0.211" Y 1.25mm 0.049" X 3.40mm 0.134"					
Packaging									
Tape packaging informa Tape and reel packing o capacitors for automatic with IEC60286-3.	of surface moun	ting chip		Product identifying label Plastic carrier tape Top tape 8 or 12mm 178mm (7") or nominal 330mm (13") dia. reel					
Soldering									
Reflow solder in accord Recommended reflow p IPC/JEDEC J-STD-020 Wave soldering is also p taken for case sizes 12 ² thickness >1.0mm. Trial Hand soldering is not re component damage thro	orofile as laid do possible, but ca 10 and larger ar Is are encourag	wn in re must be nd component ied. nd can lead to	Temperature	Max Tr Min Preheat area Time					
Application notes with mounting and handling guidance are available on request.									
Compex	DLI .	Johanson MFG	Novacap	Syfer Voltronics					
Knowles Precision Devices - Sales Europe: KPD-Europe-sales@knowles.com Asia: KPD-Asia-sales@knowles.com USA: KPD-NA-sales@knowles.com www.knowlescapacitors.com									