


Data Sheet AS09008PO-11-WR-R

## **Specifications**

| Parameters   | Values   | Units |
|--|--|-------|
| Rated Input Power  | 5  | Watts |
| Max Input Power  | 8  | Watts |
| Impedance  | 8 ± 15%  | Ohms  |
| Sensitivity (SPL @ 1W/50cm)<br>At 0.8, 1.0, 1.2, 1.5 kHz | 85 ± 3   | dB    |
| Resonant Frequency                                       | 180 ± 20%  | Hz    |
| Frequency Range  | Fo ~ 10,000  | Hz    |
| Frame Material   | Steel  | -     |
| Magnet Material  | Ferrite  | -     |
| Weight   | 98   | Grams |
| Buzz, Rattle, etc.                                       | Must be normal at sine wave Fo-<br>20kHz, 6.32                     | -     |
| Polarity   | Cone will move forward with positive+ current to positive terminal | -     |
| Storage Temperature                                      | -20 ~ +65  | °C    |
| Operating Temperature                                    | -20 ~ +65  | °C    |

# Frequency Response (measured with 2.83V @ 50cm)





## **Reliability Testing**

| Type of Test              | <b>Test Specifications</b>   |
|---------------------------|--|
| High Temperature Test     | 96 hours at +65°C ± 3°C followed by three hours in normal room temperature                           |
| Low Temperature Test      | 96 hours at -20°C ± 3°C followed by three hours in normal room temperature                           |
| Humidity Test             | 96 hours at +40°C ± 3°C with relative humidity at 90% followed by 6 hours in normal room temperature |
| Temperature Cycle Testing | The part shall be subjected to 5 cycles using the following procedure:  +65°C    +25°C               |
| Vibration Test            | Frequency 30 ± 15Hz, Amplitude 1.5mm for 3hr   |
| Drop Test                 | 100cm free fall onto concrete, x2  |
| Load Test                 | Rated power for 96hrs  |


After each test, the speaker's SPL shall be ±3 dB of the original SPL

### **Dimensions**





## **Packaging**



units: cm Remark: 40pcs per tray

2 trays for unit, 1 unit per carton

Total:100 pcs per box Size:45\*31\*21cm

### **Specifications Revisions**

This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

©2019, PUI Audio Inc.

| Revision | Description               | Date     | Customer Approval<br>(Date & Signature) |
|----------|---------------------------|----------|---|
| -        | Released from Engineering | 5/1/2020 |   |
|          |                           |          |   |
|          |                           |          |   |

#### Note:

- 1. Unless otherwise specified:
  - A. All dimensions are in millimeters.
  - B. Default tolerances are  $\pm 0.5$ mm and angles are  $\pm 3^{\circ}$ .
- 2. Specification to change or withdraw without notice.
- 3. Speaker face has been treated for water resistance.
- 4. This part is RoHS 2015/863/EU Compliant.