

SAID-M12B-5-9SMT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration





Weidmüller is now one of the industry's leading international providers of connectors. An important mainstay in this product family are the circular connectors, which Weidmüller groups under the product name SAI. In the development of SAI products, Weidmüller engineers have always concentrated on achieving rational, cost-effective installation concepts, and – in cooperation with major users – have supplied the markets with well-conceived products which set standards in terms of functionality and quality across the globe. The best examples are the new power distributors with S and T coded M12. These modules are characterised by particularly high currents and voltages. This enables them to also be used, for example, with three-phase motors.

General ordering data

| Туре | SAID-M12B-5-9SMT | | |
|------------|---|--|--|
| Order No. | <u>2422120000</u> | | |
| Version | Built-in plugs, M12, Socket connector, No. o poles: 5 | | |
| GTIN (EAN) | 4050118430950 | | |
| Qty. | 25 pc(s). | | |
| | | | |



SAID-M12B-5-9SMT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold

Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com

Technical data

| Net weight | 3.44 g | | |
|-------------------------|--------------------|--|--|
| Environmental Product | : Compliance | | |
| REACH SVHC | Lead 7439-92-1 | | |
| Technical data of PCB բ | olug-in connector | | |
| Coding | A | Housings | M12 socket |
| No. of poles | 5 | Shield connection | No |
| Rated voltage | 60 V | Rated voltage (text) | 250 V (4-pole) / 60 V (5-pole) / 30 V (8-pole) |
| Rated current | 4 A | Rated current | 4 A (4- and 5-pole) / 2 A (8-pole) |
| Temperature range | -2595 °C | Protection degree | IP67 |
| Contact surface | Au (Gold) | Housing main material | LCP |
| Connection thread | M12 | Tightening torque | M12: 0.8 Nm |
| Insulation strength | 100 ΜΩ | Pollution severity | 3 (2 within the sealed area) |
| Plugging cycles | ≥ 100 | Contact material | CuZn |
| Lock nut material | Nickel-plated CuZn | Material of the flange-mounted housing | Nickel-plated CuZn |
| Material data | | | |
| Contact material | CuZn | Contact surface | Au (Gold) |
| System parameters | | | |
| Insulation strength | 100 ΜΩ | No. of poles | 5 |
| Pin series quantity | 1 | Plugging cycles | ≥ 100 |
| Protection degree | IP67 | | |
| Classifications | | | |
| ETIM 6.0 | EC000438 | eClass 6.2 | 27-26-07-02 |
| eClass 9.1 | 27-44-02-05 | | |

ROHS

Downloads

Brochure/Catalogue

Conform

FL FIELDWIRING EN



SAID-M12B-5-9SMT

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 16 D-32758 Detmold

Germany


Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com

Drawings

Dimensioned drawing



PCB design



Pole scheme

