SAIE-M12S-4-F10TL



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com

Similar to illustration





Weidmüller is now one of the industry's leading international providers of connectors. An important mainstay in this product family are the circular connectors, which Weidmüller groups under the product name SAI. In the development of SAI products, Weidmüller engineers have always concentrated on achieving rational, cost-effective installation concepts, and – in cooperation with major users – have supplied the markets with well-conceived products which set standards in terms of functionality and quality across the globe. The best examples are the new power distributors with S and T coded M12. These modules are characterised by particularly high currents and voltages. This enables them to also be used, for example, with three-phase motors.

General ordering data

SAIE-M12S-4-F10TL		
<u>2422580000</u>		
Built-in plugs, M12, M 12, No. of poles: 4		
4050118431414		
10 pc(s).		

SAIE-M12S-4-F10TL

Technical data



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com

Dimensions and weights			
Net weight	13.4 g		
Environmental Produc	t Compliance		
REACH SVHC	Lead 7439-92-1		
Technical data of PCB	plug-in connector		
Coding	A	Housing surface	nickel-plated
Housings	M12 pin	Mounting height	10 mm
Mounting thread	M12	No. of poles	4
Shield connection	No	Type of mounting	Front mounting
Rated voltage	250 V	Rated voltage (text)	250 V (4-pole) / 60 V (5- pole)
Rated current	4 A	Rated current	4 A
Temperature range	-3080 °C	Protection degree	IP67
Contact surface	Au (Gold)	Housing main material	CuZn, nickel-plated
Connection thread	M12	Tightening torque	M12: 0.8 Nm
Mounting thread	M 12	Mounting torque range	1.2 Nm
Insulation strength	100 ΜΩ	Pollution severity	3 (2 within the sealed area)
Plugging cycles	≥ 100	Contact material	CuZn
Lock nut material	Nickel-plated CuZn	Material of the flange-mounted housing	Nickel-plated CuZn
Material data			
Contact material	CuZn	Contact surface	Au (Gold)
System parameters			
Insulation strength	100 MΩ	No. of poles	4
Pin series quantity	1	Plugging cycles	≥ 100
Protection degree	IP67		- 100
Classifications			
ETIM 6.0	EC002638	eClass 6.2	27-26-07-02
eClass 9.0	27-44-03-09	eClass 9.1	27-44-03-09
	27-44-03-03	601035 3.1	27-44-03-03
Approvals			
ROHS	Conform		
Downloads			
Brochure/Catalogue	FL FIELDWIRING EN		
Engineering Data	STEP		

SAIE-M12S-4-F10TL

Drawings



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com

