
3mm (T1) Package Discrete LED NEUTRAL WHITE

BIVAR




- ♦ Industry Standard 3mm (T1) Package
- RoHS Compliant
- Water Clear Lens
- **♦** 5000K Color Temperature
- Multiple Intensity and Viewing Angle Options
- Available in Flange and Standard LED Body styles
- Ideal for Status Indication and Display



Bivar's 3mm T1 Package 3UWC Series LED may be used in almost any application. They are offered in 5000K color temperature and come in multiple intensity, viewing angle, and body styles. Bivar offers a water clear LED lens for maximum light output. The Standard LED is ideal for vertical spacer and holder assemblies.

| Part Number | Material | Emitted Color | Color Temperature | Lens Appearance | Viewing Angle | | |
|-------------|----------------|---------------|-------------------|-----------------|---------------|--|--|
| 3UWC1.030N | InGaN/Sapphire | WHITE | 5000K | Water Clear | 30° | | |

Part Number Designation










3mm (T1) Package Discrete LED NEUTRAL WHITE



Outline Dimensions



Recommended Mounting Hole Size = $\emptyset.032^{+.003}_{-.002}$

Outline Drawings Notes:

1. All dimensions are in inches [millimeters].

2. Standard tolerance: ±0.010" unless otherwise noted.

3. Tolerance of overall epoxy outline: ±0.020" unless otherwise noted.

4. Epoxy meniscus may extend to 0.060" max.

3mm (T1) Package Discrete LED **NEUTRAL WHITE**



Absolute Maximum Ratings

T_A = 25°C unless otherwise noted

| Power Dissipation | 120 mW | | |
|--|-------------|--|--|
| Forward Current (DC) | 30 mA | | |
| Peak Forward Current ¹ | 100 mA | | |
| Reverse Voltage | 5 V | | |
| Operating Temperature Range | -25 ~ +80°C | | |
| Storage Temperature Range | -30 ~ +80°C | | |
| Lead Soldering Temperature (3 mm from the base of the epoxy bulb) ² | 260°C | | |

Notes: 1. 10% Duty Cycle, Pulse Width ≤ 0.1 msec.


Electrical / Optical Characteristics


 $T_A = 25^{\circ}C \& I_F = 20 \text{ mA}$ unless otherwise noted

| Part Number | | Forward Voltage (V) ¹ | | | Recommend Forward Current (mA) | | Reverse Current (µA) | nt CCT (Ke | | (Kelvin) | | Luminous Intensity Iv (mcd) | | Viewing Angle 2 Θ ½ (deg) |
|-------------|-----|-------------------------------------|-----|-----|--------------------------------------|-----|----------------------------|------------|------|----------|------|--------------------------------|------|------------------------------------|
| | MIN | TYP | MAX | MIN | TYP | MAX | MAX | MIN | TYP | MAX | MIN | TYP | MAX | TYP |
| 3UWC1.030N | 2.7 | 3.2 | 3.6 | / | 20 | 1 | 10 | / | 5000 | / | 3000 | 5000 | 8000 | 30 |

Notes: 1. Tolerance of forward voltage: ±0.05V.

Directivity Radiation — Relative Luminous Intensity vs. Radiation Angle Ta = 25°C unless other noted





^{2.} Solder time less than 5 seconds at temperature extreme.

3mm (T1) Package Discrete LED NEUTRAL WHITE



Typical Electrical / Optical Characteristics

T_A = 25°C unless otherwise noted




Fig.1 Forward Current vs. Forward Voltage




Fig. 2 Relative Luminous Intensity vs. Forward Current




Fig. 3 Reverse Current vs. Reverse Voltage




Fig. 4 Relative Luminous Intensity vs. Wavelength




Fig. 5 Relative Luminous Intensity vs. Ambient Temperature





Fig. 6 Maximum Forward Current vs. Ambient Temperature

Bivar reserves the right to make changes at any time without notice

3mm (T1) Package Discrete LED NEUTRAL WHITE




Recommended Soldering Conditions



| Recommended Lead Free Wave Soldering Profile | | | | | | |
|--|---|--|--|--|--|--|
| Preheat Temperature: 100°C Max. | Peak Temperature: 260°C Max. | | | | | |
| Preheat Time: 20 ~ 50 Seconds | Solder Time Above 217°C: 5 Seconds Max. | | | | | |
| Note: Turn off top heater at preheat to prevent the lamp body directly exposed to the heat source. | | | | | | |

Packaging and Labeling Plan



Bivar reserves the right to make changes at any time without notice